

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1306665

Luminaire Tested: LDSQA3D02R309024DE010 3LSQPHR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1306665
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R309024DE010 3LSQPHR1MMS
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , 3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 249.0 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.49 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1306665

CATALOG NUMBER: LDSQA3D02R309024DE010 3LSQPHR1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1306665

CATALOG NUMBER: LDSQA3D02R309024DE010 3LSQPHR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	97
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96	94	94	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89
5	102	97	93	90	101	96	93	90	95	91	89	93	90	88	92	89	88	87	87	87
6	100	94	90	87	99	93	90	87	92	89	86	91	88	86	90	87	85	84	84	84
7	97	91	87	84	96	91	87	84	90	86	84	88	86	83	88	85	83	82	82	82
8	95	89	85	82	94	88	84	82	87	84	82	86	83	81	86	83	81	80	80	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	176976	176976	176976
5°	172431	171238	169821
10°	145517	141040	138749
15°	87687	85244	86813
20°	29746	34346	39624
25°	5473	8570	10109
30°	1869	2088	2347
35°	547	673	715
40°	135	247	202
45°	49	49	49
50°	54	0	54
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 52.5°
Luminance: 57 cd/sqm

TEST NUMBER: P1306665

CATALOG NUMBER: LDSQA3D02R309024DE010 3LSQPHR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.9	35.7
10°-20°	129.9	52.2
20°-30°	27.5	11.0
30°-40°	2.5	1.0
40°-50°	0.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	246.2	98.9
0°-40°	248.7	99.9
0°-60°	249.0	100.0
0°-90°	249.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	249.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1028	1028	1028	1028	1028	
5°	997	995	990	988	982	90
15°	492	490	478	489	487	130
25°	29	32	45	53	53	21
35°	3	3	3	4	3	2
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1306665

CATALOG NUMBER: LDSQA3D02R309024DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1027.6	1027.6	1027.6	1027.6	1027.6
1°	1027.8	1026.8	1025.3	1027.4	1025.9
2°	1025.7	1023.1	1021.0	1023.1	1022.5
3°	1019.3	1017.1	1015.6	1016.7	1016.7
4°	1009.6	1007.2	1006.0	1006.2	1002.9
5°	997.4	995.4	990.5	987.5	982.3
6°	979.3	974.6	968.6	963.7	957.0
7°	954.9	947.6	939.0	930.4	922.0
8°	915.6	912.1	900.5	894.8	886.4
9°	878.7	870.3	857.8	848.4	843.9
10°	832.1	819.6	806.5	799.0	793.4
11°	776.9	764.2	753.7	742.8	734.2
12°	712.1	701.3	689.3	682.0	671.9
13°	635.2	633.7	620.2	617.8	616.5
14°	569.3	563.3	550.0	553.6	554.5
15°	491.8	490.1	478.1	489.2	486.9
17.5°	308.1	308.7	316.2	333.8	339.4
20°	162.3	167.2	187.4	208.7	216.2
22.5°	65.7	76.6	97.2	111.6	121.3
25°	28.8	32.2	45.1	53.0	53.2
27.5°	16.3	16.5	21.7	22.5	23.0
30°	9.4	9.7	10.5	11.2	11.8
32.5°	5.2	5.6	5.8	6.7	6.7
35°	2.6	3.2	3.2	3.9	3.4
37.5°	1.5	1.7	1.9	1.9	1.7
40°	0.6	0.9	1.1	1.1	0.9
42.5°	0.2	0.4	0.4	0.4	0.6
45°	0.2	0.2	0.2	0.2	0.2
47.5°	0.2	0.2	0.0	0.2	0.2
50°	0.2	0.0	0.0	0.0	0.2
52.5°	0.2	0.0	0.0	0.0	0.2
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1306665

CATALOG NUMBER: LDSQA3D02R309024DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)