

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1306645

Luminaire Tested: LDSQA3D02R259024DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1306645
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R259024DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 2400K CCT AND, 90CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 280.0 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.45 / 0.41
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1306645
CATALOG NUMBER: LDSQA3D02R259024DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270°



TEST NUMBER: P1306645
 CATALOG NUMBER: LDSQA3D02R259024DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	110	108	107	106	105	103	103	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	85	84	84	84	84
7	97	91	87	85	96	91	87	84	90	86	84	89	86	84	88	85	83	82	82	82	82
8	95	89	85	82	94	88	85	82	87	84	82	87	84	82	86	83	81	80	80	80	80
9	93	86	83	80	92	86	82	80	85	82	80	85	82	80	84	81	79	78	78	78	78
10	91	84	81	78	90	84	80	78	83	80	78	83	80	78	82	79	77	77	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	231674	231674	231674
5°	213611	214095	214545
10°	165856	166450	167360
15°	81964	85405	85458
20°	27601	29452	28151
25°	11421	12694	11763
30°	4494	5648	4534
35°	1177	2313	1219
40°	427	922	427
45°	49	268	49
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 268 cd/sqm



TEST NUMBER: P1306645

CATALOG NUMBER: LDSQA3D02R259024DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.0	38.9
10°-20°	131.8	47.1
20°-30°	32.2	11.5
30°-40°	6.3	2.2
40°-50°	0.7	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	273.0	97.5
0°-40°	279.3	99.7
0°-60°	280.0	100.0
0°-90°	280.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	280.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1345	1345	1345	1345	1345	
5°	1236	1237	1238	1244	1241	109
15°	460	471	479	484	479	129
25°	60	63	67	64	62	31
35°	6	8	11	8	6	5
45°	0	1	1	1	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1306645

CATALOG NUMBER: LDSQA3D02R259024DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1345.2	1345.2	1345.2	1345.2	1345.2
1°	1340.0	1340.9	1341.1	1342.4	1339.8
2°	1327.8	1328.0	1328.6	1331.2	1328.8
3°	1305.2	1306.7	1306.9	1310.4	1311.0
4°	1274.5	1275.4	1277.1	1282.9	1277.7
5°	1235.6	1237.3	1238.4	1243.8	1241.0
6°	1187.5	1187.9	1190.3	1196.5	1192.6
7°	1138.5	1138.3	1138.5	1143.5	1142.4
8°	1079.4	1078.4	1081.8	1087.8	1091.9
9°	1017.8	1019.3	1021.4	1027.2	1022.5
10°	948.4	952.5	951.8	952.3	957.0
11°	868.5	869.8	870.0	874.5	873.9
12°	774.6	774.6	781.7	789.0	786.6
13°	679.9	686.5	681.8	683.3	692.8
14°	569.5	574.6	581.1	587.1	582.4
15°	459.7	470.7	479.0	483.8	479.3
17.5°	263.4	267.0	274.1	275.0	272.2
20°	150.6	155.1	160.7	159.0	153.6
22.5°	94.7	96.0	101.6	98.8	97.5
25°	60.1	63.4	66.8	64.0	61.9
27.5°	37.4	39.5	43.2	40.2	37.8
30°	22.6	24.5	28.4	24.3	22.8
32.5°	11.8	14.6	17.8	14.8	11.8
35°	5.6	7.9	11.0	7.9	5.8
37.5°	3.4	4.3	6.7	4.3	3.4
40°	1.9	2.8	4.1	2.8	1.9
42.5°	0.9	1.5	1.9	1.5	1.1
45°	0.2	0.6	1.1	0.6	0.2
47.5°	0.0	0.0	0.6	0.2	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1306645
CATALOG NUMBER: LDSQA3D02R259024DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)