

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1306678

Luminaire Tested: LDSQA3D02R359024DE010 3LSQCDR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1306678
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R359024DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 271.0 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.58 / 0.52
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1306678

CATALOG NUMBER: LDSQA3D02R359024DE010 3LSQCDR1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1306678

CATALOG NUMBER: LDSQA3D02R359024DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96	95	94
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	96	94	93	92	91
3	107	102	99	96	105	101	98	95	99	96	94	96	94	92	94	92	91	89	88	87
4	104	98	94	91	102	97	93	90	95	92	89	93	91	88	92	89	88	86	85	84
5	100	94	90	87	99	93	90	87	92	88	86	90	87	85	89	86	84	83	82	81
6	97	91	86	83	96	90	86	83	89	85	83	88	84	82	86	84	82	80	79	78
7	94	88	83	80	93	87	83	80	86	82	80	85	82	79	84	81	79	77	76	75
8	91	85	80	77	91	84	80	77	83	80	77	82	79	77	81	79	76	74	73	72
9	89	82	78	75	88	81	77	75	81	77	74	80	77	74	79	76	74	71	70	69
10	86	79	75	72	85	79	75	72	78	75	72	78	74	72	77	74	72	69	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	140172	140172	140172
5°	135919	136887	137630
10°	124217	126840	129009
15°	89327	93232	93999
20°	45471	47762	47872
25°	17254	17615	17140
30°	6702	7776	6523
35°	2292	3616	2166
40°	764	1394	719
45°	49	463	49
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 463 cd/sqm

TEST NUMBER: P1306678

CATALOG NUMBER: LDSQA3D02R359024DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.7	27.2
10°-20°	137.3	50.7
20°-30°	49.3	18.2
30°-40°	9.6	3.6
40°-50°	1.1	0.4
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	260.3	96.1
0°-40°	269.9	99.6
0°-60°	271.0	100.0
0°-90°	271.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	271.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	814	814	814	814	814	
5°	786	788	792	796	796	73
15°	501	509	523	526	527	133
25°	91	92	93	92	90	48
35°	11	12	17	13	10	8
45°	0	1	2	1	0	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1306678

CATALOG NUMBER: LDSQA3D02R359024DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	813.9	813.9	813.9	813.9	813.9
1°	811.6	812.6	812.9	814.4	812.6
2°	808.1	808.8	809.6	810.9	810.1
3°	801.5	802.8	804.7	806.4	806.4
4°	794.4	796.1	798.5	801.5	801.3
5°	786.2	788.4	791.8	795.5	796.1
6°	775.9	778.5	784.1	789.2	790.1
7°	765.0	768.9	774.2	781.7	783.7
8°	752.1	755.1	762.8	771.6	773.8
9°	733.2	737.7	747.6	755.8	757.0
10°	710.3	713.5	725.3	733.9	737.7
11°	680.6	685.4	696.9	705.7	708.3
12°	642.9	649.7	663.2	669.7	671.8
13°	602.1	607.9	618.4	626.3	628.0
14°	556.1	561.7	572.7	579.1	577.6
15°	501.0	509.3	522.9	526.5	527.2
17.5°	370.0	375.4	387.4	393.2	397.3
20°	248.1	253.3	260.6	264.4	261.2
22.5°	150.9	155.2	159.1	158.8	157.8
25°	90.8	91.7	92.7	92.1	90.2
27.5°	53.0	55.4	58.6	56.5	53.2
30°	33.7	35.6	39.1	35.4	32.8
32.5°	17.8	22.5	26.2	21.2	18.7
35°	10.9	12.4	17.2	12.7	10.3
37.5°	6.7	7.7	10.7	7.5	6.0
40°	3.4	4.9	6.2	4.5	3.2
42.5°	1.1	2.4	3.4	2.1	1.1
45°	0.2	0.6	1.9	0.6	0.2
47.5°	0.0	0.0	0.9	0.2	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1306678

CATALOG NUMBER: LDSQA3D02R359024DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)