

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1306830

Luminaire Tested: LDSQA3D05R309024DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1306830
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R309024DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 568.0 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1306830
CATALOG NUMBER: LDSQA3D05R309024DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1306830

CATALOG NUMBER: LDSQA3D05R309024DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	99	99	99	97
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	95	94	94	94
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	95	94	92	95	94	92	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	93	91	89	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	87	91	89	87	91	89	87	86
6	99	93	89	86	98	92	89	86	91	88	85	90	87	85	89	86	84	89	86	84	83
7	96	90	86	83	95	90	86	83	89	85	83	87	85	82	87	84	82	87	84	82	81
8	94	88	84	81	93	87	83	81	86	83	80	85	82	80	84	82	80	84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	82	80	78	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	80	78	76	80	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	379114	379114	379114
5°	369861	370327	372385
10°	315885	314416	312562
15°	194933	192651	193364
20°	73677	74080	74007
25°	22670	24855	23677
30°	9128	11594	9486
35°	2691	4920	2796
40°	1102	1978	1102
45°	219	658	219
50°	0	107	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 658 cd/sqm



TEST NUMBER: P1306830
 CATALOG NUMBER: LDSQA3D05R309024DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.2	34.2
10°-20°	287.5	50.6
20°-30°	71.3	12.6
30°-40°	13.4	2.4
40°-50°	1.7	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	552.9	97.3
0°-40°	566.3	99.7
0°-60°	568.0	100.0
0°-90°	568.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	568.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2201	2201	2201	2201	2201	
5°	2139	2138	2142	2146	2154	194
15°	1093	1083	1080	1089	1084	289
25°	119	127	131	130	125	69
35°	13	17	23	17	13	11
45°	1	1	3	2	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1306830
 CATALOG NUMBER: LDSQA3D05R309024DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2201.3	2201.3	2201.3	2201.3	2201.3
1°	2202.2	2200.4	2200.4	2197.7	2202.6
2°	2194.2	2192.4	2195.5	2193.3	2199.5
3°	2182.3	2180.1	2184.5	2185.8	2188.9
4°	2164.6	2162.8	2167.7	2170.3	2178.7
5°	2139.4	2138.5	2142.1	2145.6	2154.0
6°	2105.0	2103.6	2105.8	2110.3	2115.6
7°	2055.0	2052.4	2054.2	2055.0	2056.4
8°	1991.9	1987.9	1985.7	1990.5	1993.2
9°	1910.6	1906.2	1901.3	1899.5	1905.7
10°	1806.3	1799.7	1797.9	1793.5	1787.3
11°	1685.3	1680.0	1678.7	1670.7	1667.2
12°	1546.6	1543.9	1547.0	1542.2	1540.4
13°	1413.6	1396.8	1394.6	1385.3	1380.5
14°	1256.4	1240.9	1240.4	1235.6	1242.2
15°	1093.3	1082.7	1080.5	1088.9	1084.5
17.5°	697.1	704.2	702.4	698.0	690.5
20°	402.0	397.1	404.2	406.0	403.8
22.5°	214.3	216.0	217.3	222.6	226.2
25°	119.3	127.2	130.8	130.3	124.6
27.5°	74.2	79.1	85.7	81.3	76.4
30°	45.9	49.9	58.3	50.4	47.7
32.5°	24.7	31.4	37.5	31.4	25.6
35°	12.8	16.8	23.4	17.2	13.3
37.5°	8.4	9.7	15.0	9.7	8.4
40°	4.9	6.2	8.8	6.2	4.9
42.5°	2.2	3.5	4.9	3.5	2.2
45°	0.9	1.3	2.7	1.8	0.9
47.5°	0.0	0.4	1.3	0.4	0.0
50°	0.0	0.0	0.4	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1306830
CATALOG NUMBER: LDSQA3D05R309024DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)