

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1308304

Luminaire Tested: LDSQA3D17R359027DE010 3LSQPHR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1308304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D17R359027DE010 3LSQPHR1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , 3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1396.0 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1308304
CATALOG NUMBER: LDSQA3D17R359027DE010 3LSQPHR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1308304
 CATALOG NUMBER: LDSQA3D17R359027DE010 3LSQPHR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	91	90	89
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	88	87	86
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	83
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82	81	80
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80	79	78
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77	76	75
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	75	74	73
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	73	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	792104	792104	792104
5°	778498	776839	775179
10°	713491	692033	675210
15°	510895	494599	488608
20°	236902	245058	253653
25°	56210	79982	83403
30°	16506	18892	21279
35°	3784	6076	5571
40°	809	1619	1079
45°	292	292	292
50°	322	0	322
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 52.5°
 Luminance: 339 cd/sqm



TEST NUMBER: P1308304

CATALOG NUMBER: LDSQA3D17R359027DE010 3LSQPHR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	412.9	29.6
10°-20°	738.2	52.9
20°-30°	222.1	15.9
30°-40°	21.2	1.5
40°-50°	1.4	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1373.2	98.4
0°-40°	1394.4	99.9
0°-60°	1396.0	100.0
0°-90°	1396.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1396.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4599	4599	4599	4599	4599	
5°	4503	4502	4494	4488	4484	418
15°	2865	2844	2774	2762	2740	757
25°	296	326	421	439	439	190
35°	18	24	29	31	26	17
45°	1	1	1	1	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1308304
 CATALOG NUMBER: LDSQA3D17R359027DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4599.3	4599.3	4599.3	4599.3	4599.3
1°	4596.9	4596.9	4594.5	4594.5	4589.7
2°	4586.1	4587.3	4582.5	4581.3	4577.7
3°	4569.3	4565.7	4565.7	4563.3	4560.9
4°	4542.8	4535.6	4533.2	4534.4	4529.6
5°	4503.1	4501.9	4493.5	4487.5	4483.9
6°	4459.9	4451.4	4433.4	4417.8	4414.2
7°	4394.9	4376.9	4361.3	4328.8	4324.0
8°	4315.6	4286.7	4253.0	4207.3	4204.9
9°	4218.2	4171.3	4124.4	4063.0	4041.4
10°	4079.9	4036.6	3957.2	3903.1	3861.0
11°	3907.9	3853.8	3761.2	3696.3	3661.4
12°	3713.1	3662.6	3554.4	3495.5	3446.2
13°	3463.0	3420.9	3319.9	3255.0	3216.5
14°	3173.2	3142.0	3045.8	3016.9	3003.7
15°	2865.4	2843.8	2774.0	2762.0	2740.4
17.5°	2109.1	2073.0	2033.3	2040.5	2047.8
20°	1292.6	1343.1	1337.1	1363.6	1384.0
22.5°	644.5	709.4	785.2	830.9	853.7
25°	295.8	325.9	420.9	438.9	438.9
27.5°	149.1	156.3	198.4	202.0	211.6
30°	83.0	89.0	95.0	105.8	107.0
32.5°	42.1	49.3	51.7	57.7	55.3
35°	18.0	24.0	28.9	31.3	26.5
37.5°	8.4	10.8	15.6	14.4	10.8
40°	3.6	4.8	7.2	6.0	4.8
42.5°	2.4	2.4	3.6	2.4	2.4
45°	1.2	1.2	1.2	1.2	1.2
47.5°	1.2	1.2	0.0	1.2	1.2
50°	1.2	0.0	0.0	0.0	1.2
52.5°	1.2	0.0	0.0	0.0	1.2
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1308304
CATALOG NUMBER: LDSQA3D17R359027DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)