

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1307087

Luminaire Tested: LDSQA3D10R129024DE010 3LSQPHRLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1307087
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D10R129024DE010 3LSQPHRLD1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 2400K CCT AND, 90CRI , 3LSQPHRLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 770.0 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1307087

CATALOG NUMBER: LDSQA3D10R129024DE010 3LSQPHRLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1307087

CATALOG NUMBER: LDSQA3D10R129024DE010 3LSQPHRLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	113	111		114	112	111	109		108	107	106		104	104	103		101	101	100
2	113	110	108	106		111	108	106	104		105	104	102		103	101	100		100	99	98
3	110	107	104	102		109	105	103	101		103	101	99		101	99	98		99	98	96
4	108	104	101	98		107	103	100	98		101	99	97		99	97	96		98	96	95
5	106	102	98	96		105	101	98	96		99	97	95		98	96	94		97	95	93
6	104	99	96	94		103	99	96	94		98	95	93		96	94	93		95	93	92
7	102	98	94	92		101	97	94	92		96	93	92		95	93	91		94	92	91
8	101	96	93	91		100	95	93	90		95	92	90		94	92	90		93	91	90
9	99	94	91	89		98	94	91	89		93	91	89		93	90	89		92	90	88
10	98	93	90	88		97	93	90	88		92	90	88		91	89	88		91	89	87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1953676
5°	1262339
10°	356159
15°	100703
20°	42117
25°	18642
30°	9526
35°	5025
40°	2158
45°	585
50°	643
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 643 cd/sqm

TEST NUMBER: P1307087

CATALOG NUMBER: LDSQA3D10R129024DE010 3LSQPHRLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	514.5	66.8
10°-20°	186.6	24.2
20°-30°	50.0	6.5
30°-40°	15.7	2.0
40°-50°	3.0	0.4
50°-60°	0.3	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	751.1	97.5
0°-40°	766.8	99.6
0°-60°	770.0	100.0
0°-90°	770.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	770.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11344	
5°	7302	514
15°	565	187
25°	98	50
35°	24	16
45°	2	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1307087

CATALOG NUMBER: LDSQA3D10R129024DE010 3LSQPHRLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	11343.9
1°	11152.5
2°	10614.0
3°	9692.6
4°	8548.6
5°	7301.8
6°	6002.2
7°	4839.1
8°	3723.9
9°	2771.4
10°	2036.6
11°	1500.6
12°	1129.6
13°	875.9
14°	694.0
15°	564.8
17.5°	359.0
20°	229.8
22.5°	148.4
25°	98.1
27.5°	67.0
30°	47.9
32.5°	33.5
35°	23.9
37.5°	16.8
40°	9.6
42.5°	4.8
45°	2.4
47.5°	2.4
50°	2.4
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1307087

CATALOG NUMBER: LDSQA3D10R129024DE010 3LSQPHRLD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)