

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1307654

Luminaire Tested: LDSQA3D02R359027DE010 3LSQPHR1MMS

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1307654  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D02R359027DE010 3LSQPHR1MMS  
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , 3LSQPHR1MMS TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 264.0 lumens  
Efficiency: N/A  
Efficacy: 73.3 lumens/watt  
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1307654  
CATALOG NUMBER: LDSQA3D02R359027DE010 3LSQPHR1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1307654  
 CATALOG NUMBER: LDSQA3D02R359027DE010 3LSQPHR1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100	
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95	93	
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	95	93	92	90	
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	93	90	89	87	
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	90	88	86	85	
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	88	85	83	82	
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	85	83	81	80	
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	83	80	78	77	
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	81	78	76	75	
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	81	78	76	75	
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	79	76	74	73	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	149799	149799	149799
5°	147225	146914	146603
10°	134937	130880	127697
15°	96620	93535	92394
20°	44811	46350	47963
25°	10622	15126	15772
30°	3122	3580	4017
35°	715	1156	1051
40°	157	315	202
45°	49	49	49
50°	54	0	54
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 52.5°  
 Luminance: 57 cd/sqm



TEST NUMBER: P1307654

CATALOG NUMBER: LDSQA3D02R359027DE010 3LSQPHR1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.1	29.6
10°-20°	139.6	52.9
20°-30°	42.0	15.9
30°-40°	4.0	1.5
40°-50°	0.3	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	259.7	98.4
0°-40°	263.7	99.9
0°-60°	264.0	100.0
0°-90°	264.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	264.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	870	870	870	870	870	
5°	852	851	850	849	848	79
15°	542	538	525	522	518	143
25°	56	62	80	83	83	36
35°	3	4	6	6	5	3
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1307654  
 CATALOG NUMBER: LDSQA3D02R359027DE010 3LSQPHR1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	869.8	869.8	869.8	869.8	869.8
1°	869.3	869.3	868.9	868.9	868.0
2°	867.3	867.5	866.6	866.4	865.7
3°	864.1	863.4	863.4	863.0	862.5
4°	859.1	857.7	857.3	857.5	856.6
5°	851.6	851.4	849.8	848.6	848.0
6°	843.4	841.8	838.4	835.5	834.8
7°	831.1	827.7	824.8	818.6	817.7
8°	816.1	810.7	804.3	795.7	795.2
9°	797.7	788.8	780.0	768.4	764.3
10°	771.6	763.4	748.4	738.1	730.2
11°	739.0	728.8	711.3	699.0	692.4
12°	702.2	692.6	672.2	661.0	651.7
13°	654.9	646.9	627.8	615.6	608.3
14°	600.1	594.2	576.0	570.5	568.0
15°	541.9	537.8	524.6	522.3	518.2
17.5°	398.9	392.0	384.5	385.9	387.3
20°	244.5	254.0	252.9	257.9	261.7
22.5°	121.9	134.2	148.5	157.1	161.5
25°	55.9	61.6	79.6	83.0	83.0
27.5°	28.2	29.6	37.5	38.2	40.0
30°	15.7	16.8	18.0	20.0	20.2
32.5°	8.0	9.3	9.8	10.9	10.5
35°	3.4	4.5	5.5	5.9	5.0
37.5°	1.6	2.0	3.0	2.7	2.0
40°	0.7	0.9	1.4	1.1	0.9
42.5°	0.5	0.5	0.7	0.5	0.5
45°	0.2	0.2	0.2	0.2	0.2
47.5°	0.2	0.2	0.0	0.2	0.2
50°	0.2	0.0	0.0	0.0	0.2
52.5°	0.2	0.0	0.0	0.0	0.2
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1307654  
CATALOG NUMBER: LDSQA3D02R359027DE010 3LSQPHR1MMS

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)