

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1307668

Luminaire Tested: LDSQA3D02R409027DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1307668
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R409027DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 323.0 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.69 / 0.6
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1307668
CATALOG NUMBER: LDSQA3D02R409027DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1307668

CATALOG NUMBER: LDSQA3D02R409027DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	94	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	90	90	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	87	87	87	85
5	100	93	89	86	98	93	88	85	91	87	85	89	86	84	88	85	83	83	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	80	80	79
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	80	77	77	77	76
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	75	75	73
9	87	80	76	73	86	80	75	73	79	75	72	78	75	72	77	74	72	72	72	71
10	85	77	73	70	84	77	73	70	76	72	70	76	72	70	75	72	70	70	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	132284	132284	132284
5°	131130	131960	132599
10°	127400	127172	129148
15°	110830	112613	114004
20°	72742	74153	75125
25°	25939	27440	25806
30°	5648	7636	5707
35°	1808	3154	1766
40°	562	967	517
45°	49	341	49
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 341 cd/sqm



TEST NUMBER: P1307668

CATALOG NUMBER: LDSQA3D02R409027DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.8	22.2
10°-20°	167.3	51.8
20°-30°	75.0	23.2
30°-40°	8.1	2.5
40°-50°	0.8	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	314.1	97.3
0°-40°	322.2	99.8
0°-60°	323.0	100.0
0°-90°	323.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	323.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	768	768	768	768	768	
5°	758	761	763	764	767	72
15°	622	626	632	635	639	165
25°	136	141	144	147	136	73
35°	9	10	15	10	8	7
45°	0	0	1	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1307668

CATALOG NUMBER: LDSQA3D02R409027DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	768.1	768.1	768.1	768.1	768.1
1°	766.5	768.1	769.5	768.3	769.9
2°	765.8	767.6	769.7	768.6	769.9
3°	764.0	766.3	768.6	767.9	769.2
4°	761.5	763.3	766.7	766.7	768.8
5°	758.5	760.6	763.3	764.5	767.0
6°	755.4	756.5	758.5	760.8	764.2
7°	751.3	751.3	753.8	756.0	760.6
8°	745.6	745.1	746.9	749.9	754.0
9°	738.5	736.9	738.3	742.6	748.8
10°	728.5	727.2	727.2	732.6	738.5
11°	715.6	715.1	715.3	720.6	728.5
12°	698.0	698.5	698.5	704.4	714.2
13°	678.3	678.0	680.1	686.7	693.3
14°	654.1	655.5	657.6	663.5	670.3
15°	621.6	626.2	631.6	635.3	639.4
17.5°	522.7	527.2	534.7	537.7	538.6
20°	396.9	403.5	404.6	410.5	409.9
22.5°	266.1	265.7	266.6	267.3	267.5
25°	136.5	140.6	144.4	146.9	135.8
27.5°	59.4	66.4	71.4	64.8	60.0
30°	28.4	32.3	38.4	32.5	28.7
32.5°	15.5	18.0	24.3	17.7	15.2
35°	8.6	10.0	15.0	9.8	8.4
37.5°	5.0	5.5	8.2	5.5	4.8
40°	2.5	3.2	4.3	3.2	2.3
42.5°	0.9	1.6	2.3	1.6	0.9
45°	0.2	0.5	1.4	0.5	0.2
47.5°	0.0	0.0	0.7	0.0	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1307668
CATALOG NUMBER: LDSQA3D02R409027DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)