

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1307695

Luminaire Tested: LDSQA3D02R559027DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1307695
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R559027DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 296.0 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.81
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1307695
CATALOG NUMBER: LDSQA3D02R559027DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1307695
 CATALOG NUMBER: LDSQA3D02R559027DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	86	86	86	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	81	81	81	80
5	96	88	83	79	94	87	82	79	85	81	78	84	80	77	82	79	77	77	77	77	75
6	91	83	78	74	90	83	78	74	81	77	74	80	76	73	79	75	73	73	73	73	71
7	87	79	74	70	86	79	73	70	77	73	69	76	72	69	75	72	69	69	69	69	67
8	84	75	70	66	83	75	70	66	74	69	66	73	69	65	72	68	65	65	65	65	64
9	80	72	66	63	79	71	66	63	70	66	62	69	65	62	69	65	62	62	62	62	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	59	59	59	58

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	67046	67046	67046
5°	66282	66092	65746
10°	69480	68640	68168
15°	68324	67593	67361
20°	62240	62479	62277
25°	49920	50699	49920
30°	28657	29372	29611
35°	8179	9839	8410
40°	2091	3013	2136
45°	219	1047	170
50°	0	188	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 1047 cd/sqm



TEST NUMBER: P1307695

CATALOG NUMBER: LDSQA3D02R559027DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.0	12.5
10°-20°	105.5	35.6
20°-30°	116.2	39.3
30°-40°	34.7	11.7
40°-50°	2.7	0.9
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	258.6	87.4
0°-40°	293.3	99.1
0°-60°	296.0	100.0
0°-90°	296.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	296.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	389	389	389	389	389	
5°	383	383	382	381	380	37
15°	383	380	379	378	378	106
25°	263	263	267	266	263	115
35°	39	41	47	43	40	32
45°	1	2	4	2	1	2
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1307695
 CATALOG NUMBER: LDSQA3D02R559027DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	389.3	389.3	389.3	389.3	389.3
1°	389.1	389.1	388.7	388.4	389.1
2°	388.0	388.0	386.8	386.6	387.3
3°	385.5	385.3	384.3	383.7	384.1
4°	383.4	383.0	382.3	381.2	381.4
5°	383.4	382.8	382.3	380.7	380.3
6°	385.3	384.8	383.9	382.3	381.8
7°	388.4	387.5	386.6	384.6	384.1
8°	391.8	391.2	389.3	387.3	386.4
9°	395.3	393.7	391.4	389.3	389.1
10°	397.3	395.0	392.5	390.0	389.8
11°	397.1	395.0	392.1	389.8	389.6
12°	396.2	393.2	390.7	388.0	388.2
13°	393.0	390.3	387.8	385.7	385.3
14°	388.7	386.2	383.9	381.8	382.1
15°	383.2	380.5	379.1	377.5	377.8
17.5°	363.9	363.2	363.9	362.1	362.7
20°	339.6	338.9	340.9	340.0	339.8
22.5°	305.7	306.6	310.5	309.3	307.3
25°	262.7	262.7	266.8	266.4	262.7
27.5°	206.8	208.4	210.9	212.1	209.3
30°	144.1	147.7	147.7	150.0	148.9
32.5°	80.5	88.2	90.0	91.1	86.6
35°	38.9	41.4	46.8	42.7	40.0
37.5°	18.6	19.8	25.2	20.5	19.1
40°	9.3	10.7	13.4	11.1	9.5
42.5°	3.9	5.7	7.0	5.7	3.9
45°	0.9	2.3	4.3	2.3	0.7
47.5°	0.0	0.2	2.0	0.5	0.0
50°	0.0	0.0	0.7	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1307695
CATALOG NUMBER: LDSQA3D02R559027DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)