

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1309339

Luminaire Tested: LDSQA3D17R129030DE010 3LSQCDR1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1309339
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D17R129030DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1355.0 lumens
Efficiency: N/A
Efficacy: 59.2 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1309339

CATALOG NUMBER: LDSQA3D17R129030DE010 3LSQCDR1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1309339

CATALOG NUMBER: LDSQA3D17R129030DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98			
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	97			
3	110	107	104	102	109	105	103	101	103	101	99	101	99	98	99	98	96	95			
4	108	104	101	98	107	103	100	98	101	99	97	99	97	96	98	96	95	94			
5	106	102	98	96	105	101	98	96	99	97	95	98	96	94	97	95	93	92			
6	104	99	96	94	103	99	96	94	98	95	93	96	94	93	95	93	92	91			
7	102	98	94	92	101	97	94	92	96	93	92	95	93	91	94	92	91	90			
8	101	96	93	91	100	95	93	90	95	92	90	94	92	90	93	91	90	89			
9	99	94	91	89	98	94	91	89	93	91	89	93	90	89	92	90	88	88			
10	98	93	90	88	97	93	90	88	92	90	88	91	89	88	91	89	87	87			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3437977
5°	2221376
10°	626768
15°	177210
20°	74098
25°	32818
30°	16744
35°	8851
40°	3777
45°	1023
50°	1125
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 1125 cd/sqm

TEST NUMBER: P1309339

CATALOG NUMBER: LDSQA3D17R129030DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	905.3	66.8
10°-20°	328.4	24.2
20°-30°	87.9	6.5
30°-40°	27.7	2.0
40°-50°	5.2	0.4
50°-60°	0.4	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1321.7	97.5
0°-40°	1349.4	99.6
0°-60°	1355.0	100.0
0°-90°	1355.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1355.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19962	
5°	12849	905
15°	994	328
25°	173	88
35°	42	28
45°	4	5
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1309339

CATALOG NUMBER: LDSQA3D17R129030DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	19962.4
1°	19625.5
2°	18677.9
3°	17056.5
4°	15043.4
5°	12849.2
6°	10562.4
7°	8515.6
8°	6553.0
9°	4876.9
10°	3584.0
11°	2640.6
12°	1987.8
13°	1541.4
14°	1221.3
15°	993.9
17.5°	631.7
20°	404.3
22.5°	261.1
25°	172.7
27.5°	117.9
30°	84.2
32.5°	59.0
35°	42.1
37.5°	29.5
40°	16.8
42.5°	8.4
45°	4.2
47.5°	4.2
50°	4.2
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1309339

CATALOG NUMBER: LDSQA3D17R129030DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)