

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1308041

Luminaire Tested: LDSQA3D09R709027DE010 3LSQCDR1MB

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1308041  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-31)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D09R709027DE010 3LSQCDR1MB  
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , 3LSQCDR1MB TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 808.0 lumens  
Efficiency: N/A  
Efficacy: 72.8 lumens/watt  
Spacing Criteria (0/90/45): 1 / 0.99 / 1.03  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1308041  
CATALOG NUMBER: LDSQA3D09R709027DE010 3LSQCDR1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P1308041

CATALOG NUMBER: LDSQA3D09R709027DE010 3LSQCDR1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	95	95	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	88	88	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	81	81	81	80
4	96	89	83	79	95	88	82	78	85	81	77	83	79	76	81	78	75	75	75	74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	70	70	68
6	86	77	71	67	85	76	71	66	75	70	66	73	69	65	72	68	65	65	65	63
7	82	72	66	62	80	71	66	61	70	65	61	69	64	61	68	64	60	60	60	59
8	78	68	61	57	76	67	61	57	66	61	57	65	60	57	64	60	56	56	56	55
9	74	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	53	53	51
10	70	60	54	50	69	59	53	50	58	53	49	58	53	49	57	52	49	49	49	48

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	134506	134506	134506
5°	129107	128398	128053
10°	124042	122958	122713
15°	121100	119388	119638
20°	115958	114840	114584
25°	107631	107897	106206
30°	98518	99870	96072
35°	80587	84476	77433
40°	46403	54069	47617
45°	658	22456	2338
50°	0	2385	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 22456 cd/sqm



TEST NUMBER: P1308041

CATALOG NUMBER: LDSQA3D09R709027DE010 3LSQCDR1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.7	8.6
10°-20°	188.8	23.4
20°-30°	259.4	32.1
30°-40°	235.2	29.1
40°-50°	54.7	6.8
50°-60°	0.3	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	517.9	64.1
0°-40°	753.1	93.2
0°-60°	808.0	100.0
0°-90°	808.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	808.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	781	781	781	781	781	
5°	747	745	743	741	741	70
15°	679	674	670	670	671	191
25°	566	569	568	562	559	260
35°	383	389	402	385	368	230
45°	3	31	92	40	10	33
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1308041  
 CATALOG NUMBER: LDSQA3D09R709027DE010 3LSQCDR1MB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	781.0	781.0	781.0	781.0	781.0
1°	780.3	779.0	779.6	780.3	781.0
2°	774.2	772.8	772.8	773.5	773.5
3°	766.7	763.9	763.9	763.2	763.2
4°	756.4	754.4	753.0	752.3	752.3
5°	746.8	744.8	742.7	741.4	740.7
6°	738.6	735.2	732.5	731.8	732.5
7°	729.1	727.0	724.3	722.2	722.9
8°	722.2	719.5	716.1	714.7	714.7
9°	716.1	713.4	709.9	707.2	708.6
10°	709.3	706.5	703.1	701.1	701.7
11°	704.5	701.1	697.0	695.6	696.3
12°	699.0	694.9	690.8	690.1	691.5
13°	692.2	688.1	684.0	684.0	685.3
14°	686.0	681.2	677.1	677.1	679.2
15°	679.2	674.4	669.6	669.6	671.0
17.5°	658.7	654.6	649.8	649.8	650.5
20°	632.7	630.7	626.6	624.5	625.2
22.5°	599.9	599.9	597.9	594.5	593.1
25°	566.4	569.2	567.8	562.3	558.9
27.5°	531.6	536.4	537.1	528.9	522.7
30°	495.4	499.5	502.2	492.7	483.1
32.5°	442.1	454.4	461.2	448.2	428.4
35°	383.3	388.8	401.8	384.7	368.3
37.5°	311.6	318.4	329.3	315.7	306.1
40°	206.4	233.7	240.5	233.7	211.8
42.5°	74.5	131.2	157.8	133.9	87.5
45°	2.7	30.7	92.2	39.6	9.6
47.5°	0.0	0.7	41.7	1.4	0.0
50°	0.0	0.0	8.9	0.0	0.0
52.5°	0.0	0.0	0.7	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1308041  
CATALOG NUMBER: LDSQA3D09R709027DE010 3LSQCDR1MB

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)