

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1308786

Luminaire Tested: LDSQA3D02R409030DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1308786
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R409030DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 346.0 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.69 / 0.6
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1308786
CATALOG NUMBER: LDSQA3D02R409030DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1308786
 CATALOG NUMBER: LDSQA3D02R409030DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	94	94	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	92	92	92	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	87	88	88	87	85
5	100	93	89	86	98	93	88	85	91	87	85	89	86	84	88	85	83	88	85	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	85	82	80	79
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	80	77	82	80	77	76
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	80	77	75	73
9	87	80	76	73	86	80	75	73	79	75	72	78	75	72	77	74	72	77	74	72	71
10	85	77	73	70	84	77	73	70	76	72	70	76	72	70	75	72	70	75	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	141705	141705	141705
5°	140483	141364	142039
10°	136476	136214	138347
15°	118729	120636	122116
20°	77929	79432	80476
25°	27782	29397	27649
30°	6065	8193	6105
35°	1955	3385	1892
40°	607	1034	540
45°	49	365	49
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 365 cd/sqm



TEST NUMBER: P1308786

CATALOG NUMBER: LDSQA3D02R409030DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.9	22.2
10°-20°	179.2	51.8
20°-30°	80.4	23.2
30°-40°	8.7	2.5
40°-50°	0.8	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	336.5	97.3
0°-40°	345.2	99.8
0°-60°	346.0	100.0
0°-90°	346.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	346.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	823	823	823	823	823	
5°	813	815	818	819	822	77
15°	666	671	677	680	685	177
25°	146	151	155	157	146	78
35°	9	11	16	10	9	7
45°	0	0	2	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1308786

CATALOG NUMBER: LDSQA3D02R409030DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	822.8	822.8	822.8	822.8	822.8
1°	821.1	822.8	824.3	823.0	824.7
2°	820.4	822.3	824.5	823.3	824.7
3°	818.4	820.8	823.3	822.6	824.0
4°	815.7	817.7	821.3	821.3	823.5
5°	812.6	814.8	817.7	818.9	821.6
6°	809.2	810.4	812.6	815.0	818.7
7°	804.8	804.8	807.4	809.9	814.8
8°	798.7	798.2	800.1	803.3	807.7
9°	791.1	789.4	790.9	795.5	802.1
10°	780.4	778.9	778.9	784.8	791.1
11°	766.5	766.0	766.3	771.9	780.4
12°	747.8	748.2	748.2	754.6	765.1
13°	726.6	726.3	728.5	735.6	742.6
14°	700.7	702.2	704.4	710.7	718.0
15°	665.9	670.8	676.6	680.5	684.9
17.5°	559.9	564.8	572.8	576.0	577.0
20°	425.2	432.2	433.4	439.8	439.1
22.5°	285.1	284.6	285.6	286.3	286.5
25°	146.2	150.6	154.7	157.4	145.5
27.5°	63.6	71.1	76.5	69.4	64.3
30°	30.5	34.6	41.2	34.8	30.7
32.5°	16.6	19.2	26.1	19.0	16.3
35°	9.3	10.7	16.1	10.5	9.0
37.5°	5.4	5.8	8.8	5.8	5.1
40°	2.7	3.4	4.6	3.4	2.4
42.5°	1.0	1.7	2.4	1.7	1.0
45°	0.2	0.5	1.5	0.5	0.2
47.5°	0.0	0.0	0.7	0.0	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1308786
CATALOG NUMBER: LDSQA3D02R409030DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)