

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1308804

Luminaire Tested: LDSQA3D02R509030DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1308804
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R509030DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 340.0 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.78
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1308804
CATALOG NUMBER: LDSQA3D02R509030DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1308804
 CATALOG NUMBER: LDSQA3D02R509030DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	64	70	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	90934	90934	90934
5°	89345	89085	88843
10°	86163	85236	85394
15°	79271	78273	78487
20°	70781	70121	70506
25°	55089	57407	54481
30°	29850	33330	29313
35°	9398	11206	9209
40°	2068	2900	1978
45°	49	877	49
50°	0	134	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 877 cd/sqm



TEST NUMBER: P1308804

CATALOG NUMBER: LDSQA3D02R509030DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	14.2
10°-20°	122.9	36.1
20°-30°	129.5	38.1
30°-40°	37.0	10.9
40°-50°	2.3	0.7
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	300.7	88.5
0°-40°	337.7	99.3
0°-60°	340.0	100.0
0°-90°	340.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	340.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	528	528	528	528	528	
5°	517	516	515	515	514	49
15°	445	442	439	440	440	124
25°	290	301	302	299	287	127
35°	45	48	53	45	44	35
45°	0	1	4	1	0	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1308804

CATALOG NUMBER: LDSQA3D02R509030DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	528.0	528.0	528.0	528.0	528.0
1°	528.2	528.5	528.0	528.5	527.3
2°	527.5	527.0	526.5	526.8	526.0
3°	524.8	524.6	523.6	523.9	522.9
4°	521.4	520.7	520.0	519.5	518.5
5°	516.8	516.3	515.3	514.9	513.9
6°	512.9	511.9	510.2	509.8	508.8
7°	507.8	507.3	505.1	504.6	504.2
8°	503.9	502.5	499.8	500.0	498.8
9°	498.8	496.9	494.2	494.2	494.4
10°	492.7	489.8	487.4	488.1	488.3
11°	484.7	482.8	479.1	480.8	480.8
12°	475.9	473.5	470.8	472.3	473.3
13°	465.7	463.8	461.4	462.8	462.3
14°	455.8	452.1	450.4	452.4	451.6
15°	444.6	441.7	439.0	439.7	440.2
17.5°	414.7	411.5	409.6	409.8	412.0
20°	386.2	385.0	382.6	383.5	384.7
22.5°	352.6	353.1	350.2	350.9	353.9
25°	289.9	300.6	302.1	298.7	286.7
27.5°	214.7	230.8	235.7	227.9	213.3
30°	150.1	154.4	167.6	152.7	147.4
32.5°	88.0	94.6	101.7	91.4	87.8
35°	44.7	47.9	53.3	45.2	43.8
37.5°	20.7	22.1	24.3	20.7	19.5
40°	9.2	10.9	12.9	10.5	8.8
42.5°	2.9	5.1	6.8	4.6	2.7
45°	0.2	1.2	3.6	1.2	0.2
47.5°	0.0	0.2	1.5	0.2	0.0
50°	0.0	0.0	0.5	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1308804
CATALOG NUMBER: LDSQA3D02R509030DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)