

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1308916

Luminaire Tested: LDSQA3D05R309030DE010 3LSQCA45R 1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1308916
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-76)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R309030DE010 3LSQCA45R 1MB
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , 3LSQCA45R 1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 594.0 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 4.07 / 0.66 / 1.44
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1308916
CATALOG NUMBER: LDSQA3D05R309030DE010 3LSQCA45R 1MB

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1308916

CATALOG NUMBER: LDSQA3D05R309030DE010 3LSQCA45R 1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	89	89	89	87
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	75	75	73
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	67	63	63	63	63	61
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	52	52	52	52	50
5	75	62	52	46	73	60	52	45	58	51	45	56	50	44	54	49	44	44	44	44	42
6	68	54	45	38	66	53	44	38	51	43	37	49	42	37	48	42	37	37	37	37	35
7	62	48	38	32	60	47	38	32	45	37	31	44	36	31	42	36	31	31	31	31	29
8	56	42	33	27	55	41	33	27	40	32	26	39	32	26	37	31	26	26	26	26	24
9	52	37	29	23	50	37	28	23	36	28	22	34	27	22	33	27	22	22	22	22	20
10	48	33	25	19	46	33	25	19	32	24	19	31	24	19	30	24	19	19	19	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	3961	3961	3961	3961	3961
5°	4236	4149	3890	3544	3458
10°	4634	4110	3410	3060	2973
15°	6775	4101	2853	2585	2674
20°	17063	4490	2199	2199	2474
25°	79203	5606	1710	1995	2280
30°	252142	7756	1293	1889	2287
35°	437520	9461	1051	1787	2313
40°	510253	9442	787	1799	2361
45°	523288	6698	852	1948	2557
50°	486643	3751	670	2009	2947
55°	413610	1952	751	2252	3303
60°	238873	517	861	2411	3617
65°	48739	0	1019	2853	4075
70°	755	252	1259	3273	4784
75°	665	333	1331	3327	5656
80°	496	496	1984	3967	6447
85°	0	988	3952	3952	7904

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 523288 cd/sqm



TEST NUMBER: P1308916

CATALOG NUMBER: LDSQA3D05R309030DE010 3LSQCA45R 1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2.1	0.3
10°-20°	6.0	1.0
20°-30°	34.3	5.8
30°-40°	160.0	26.9
40°-50°	226.2	38.1
50°-60°	139.2	23.4
60°-70°	21.2	3.6
70°-80°	3.4	0.6
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	42.3	7.1
0°-40°	202.3	34.1
0°-60°	567.7	95.6
0°-90°	594.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	594.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	23	23	23	23	23	
5°	24	24	22	20	20	2
15°	38	23	16	14	15	14
25°	417	30	9	10	12	256
35°	2081	45	5	8	11	1249
45°	2148	28	4	8	10	1629
55°	1378	6	2	8	11	1172
65°	120	0	2	7	10	216
75°	1	0	2	5	8	1
85°	0	0	2	2	4	0
90°	0	0	0	0	0	



TEST NUMBER: P1308916
 CATALOG NUMBER: LDSQA3D05R309030DE010 3LSQCA45R 1MB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	23.0	23.0	23.0	23.0	23.0	23.0	23.0	23.0	23.0	23.0	23.0
2.5°	23.5	23.5	24.0	24.0	23.5	24.0	24.0	24.0	23.0	22.5	21.5
5°	24.5	24.5	24.5	25.0	24.5	24.5	24.0	23.5	22.5	21.0	20.5
7.5°	25.5	25.5	25.0	25.5	25.0	25.0	24.0	23.0	21.5	20.0	19.0
10°	26.5	26.5	26.0	26.0	25.5	25.5	23.5	22.0	19.5	18.0	17.5
12.5°	29.5	29.5	29.0	28.5	27.5	27.0	23.0	20.5	17.5	16.0	15.5
15°	38.0	37.5	36.5	35.0	32.5	32.0	23.0	19.0	16.0	14.5	14.5
17.5°	52.0	51.5	50.0	46.0	41.5	40.0	23.0	17.0	14.0	13.0	13.0
20°	93.1	89.1	81.6	71.6	61.0	55.5	24.5	15.0	12.0	11.5	12.0
21°	121.6	117.6	108.1	91.6	73.1	67.0	25.5	14.5	11.5	11.0	12.0
22°	165.6	161.1	141.6	119.1	92.6	82.1	26.0	13.5	10.5	10.5	11.5
23°	231.2	223.7	190.6	154.6	115.6	100.6	27.0	13.0	10.0	10.5	11.0
24°	302.7	296.2	258.7	204.6	147.6	126.1	28.0	12.5	9.5	9.5	10.5
25°	416.8	409.3	342.7	258.2	187.1	151.6	29.5	11.5	9.0	9.0	10.5
26°	564.4	529.9	441.3	332.7	230.7	190.1	31.0	11.0	8.5	9.0	10.0
27°	704.5	676.0	576.4	426.8	285.2	233.7	33.0	10.5	8.0	8.5	10.0
28°	888.6	848.6	723.0	539.9	359.3	282.7	35.0	10.0	7.5	8.5	9.5
29°	1094.8	1038.7	887.1	667.0	442.8	337.7	37.0	9.5	7.0	8.0	9.5
30°	1267.9	1215.4	1063.8	817.6	538.9	410.3	39.0	9.0	6.5	8.0	9.5
31°	1471.1	1391.5	1207.9	945.2	621.4	482.8	41.0	8.0	6.0	7.5	9.0
32°	1635.7	1580.1	1385.0	1089.3	730.0	562.9	42.5	7.5	6.0	7.5	9.0
33°	1794.8	1720.2	1531.6	1227.4	828.1	645.0	44.0	7.0	5.5	7.0	9.0
34°	1946.9	1878.4	1670.2	1339.0	920.7	723.0	45.0	6.0	5.5	7.0	8.5
35°	2081.0	2001.4	1792.3	1448.0	1015.7	794.1	45.0	5.5	5.0	6.5	8.5
36°	2168.1	2111.0	1898.4	1555.6	1101.8	861.6	45.0	5.0	4.5	6.5	8.0
37°	2242.6	2176.1	1983.4	1638.2	1165.3	915.7	45.0	4.5	4.5	6.5	8.0
38°	2273.1	2216.1	2042.0	1711.2	1224.9	970.7	44.5	4.0	4.0	6.0	8.0
39°	2285.1	2234.1	2086.0	1763.8	1268.9	1007.7	43.5	3.5	4.0	6.0	8.0
40°	2269.6	2231.1	2108.5	1797.8	1303.9	1034.7	42.0	3.0	3.5	6.0	8.0
42.5°	2205.6	2180.1	2103.5	1831.8	1334.0	1054.8	36.5	2.0	3.5	5.5	8.0
45°	2148.5	2120.5	2053.0	1796.3	1294.9	1015.2	27.5	1.0	3.5	5.5	8.0
47.5°	2038.0	2020.5	1967.4	1705.7	1209.4	926.2	19.5	0.5	3.0	5.0	7.5
50°	1816.3	1799.8	1729.7	1481.1	1040.2	783.1	14.0	0.5	2.5	5.0	7.5
52.5°	1617.7	1600.2	1499.6	1231.4	799.1	573.9	9.0	0.5	2.5	5.0	7.5
55°	1377.5	1347.0	1214.9	934.7	566.4	384.8	6.5	0.5	2.5	4.5	7.5
57.5°	1019.7	975.2	857.1	637.5	326.2	208.7	3.5	0.5	2.5	4.5	7.5
60°	693.5	667.0	536.4	336.2	139.1	88.1	1.5	0.5	2.5	4.5	7.0
62.5°	420.3	386.8	269.7	143.1	60.0	40.0	0.0	1.0	2.5	4.5	7.0
65°	119.6	106.1	70.6	32.5	17.0	13.0	0.0	1.0	2.5	4.5	7.0
67.5°	4.0	4.0	4.0	3.5	2.5	2.5	0.5	1.0	2.5	4.5	6.5
70°	1.5	1.5	1.5	1.0	1.0	0.5	0.5	1.0	2.5	4.0	6.5
72.5°	1.0	1.0	1.0	1.0	0.5	0.5	0.5	1.0	2.0	3.5	6.0
75°	1.0	1.0	1.0	0.5	0.5	0.5	0.5	1.5	2.0	3.5	5.0
77.5°	1.0	1.0	1.0	0.5	0.5	0.5	0.5	1.5	2.0	3.0	5.0
80°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	1.5	2.0	3.0	4.0



TEST NUMBER: P1308916

CATALOG NUMBER: LDSQA3D05R309030DE010 3LSQCA45R 1MB

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
82.5°	0.5	0.5	0.5	0.0	0.0	0.0	0.5	1.5	2.0	2.0	3.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.5	1.5	2.0	1.5	2.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.5	1.5	1.5	1.5	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1308916

CATALOG NUMBER: LDSQA3D05R309030DE010 3LSQCA45R 1MB

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	23.0	23.0
2.5°	21.5	21.5
5°	20.0	20.0
7.5°	18.5	18.5
10°	17.0	17.0
12.5°	16.0	16.0
15°	14.5	15.0
17.5°	13.5	14.0
20°	13.0	13.5
21°	13.0	13.5
22°	12.5	13.0
23°	12.5	13.0
24°	12.0	12.5
25°	11.5	12.0
26°	11.5	12.0
27°	11.5	12.0
28°	11.0	12.0
29°	11.0	11.5
30°	11.0	11.5
31°	10.5	11.5
32°	10.5	11.5
33°	10.5	11.0
34°	10.0	11.0
35°	10.0	11.0
36°	10.0	11.0
37°	10.0	10.5
38°	10.0	11.0
39°	10.0	10.5
40°	10.0	10.5
42.5°	10.0	10.5
45°	10.0	10.5
47.5°	10.0	11.0
50°	10.0	11.0
52.5°	10.0	11.0
55°	10.0	11.0
57.5°	10.0	10.5
60°	10.0	10.5
62.5°	9.5	10.5
65°	9.5	10.0
67.5°	9.5	10.0
70°	9.0	9.5
72.5°	8.5	9.0
75°	7.5	8.5
77.5°	7.0	7.5
80°	6.0	6.5



TEST NUMBER: P1308916
CATALOG NUMBER: LDSQA3D05R309030DE010 3LSQCA45R 1MB

CANDELA DISTRIBUTION (continued):

	157.5°	180°
82.5°	5.0	5.0
85°	3.5	4.0
87.5°	2.0	2.0
90°	0.0	0.0

(END OF REPORT)