

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1310288

Luminaire Tested: LDSQA3D10R129035DE010 3LSQCBR1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1310288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D10R129035DE010 3LSQCBR1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 90CRI , 3LSQCBR1MW TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 928.0 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1310288

CATALOG NUMBER: LDSQA3D10R129035DE010 3LSQCBR1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1310288

CATALOG NUMBER: LDSQA3D10R129035DE010 3LSQCBR1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		0			
RCR																						
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102	100
1	116	114	113	111		114	112	111	109		108	107	106		104	104	103		101	101	100	98
2	113	110	108	106		111	108	106	104		105	104	102		103	101	100		100	99	98	97
3	110	107	104	102		109	105	103	101		103	101	99		101	99	98		99	98	96	95
4	108	104	101	98		107	103	100	98		101	99	97		99	97	96		98	96	95	94
5	106	102	98	96		105	101	98	96		99	97	95		98	96	94		97	95	93	92
6	104	99	96	94		103	99	96	94		98	95	93		96	94	93		95	93	92	91
7	102	98	94	92		101	97	94	92		96	93	92		95	93	91		94	92	91	90
8	101	96	93	91		100	95	93	90		95	92	90		94	92	90		93	91	90	89
9	99	94	91	89		98	94	91	89		93	91	89		93	90	89		92	90	88	88
10	98	93	90	88		97	93	90	88		92	90	88		91	89	88		91	89	87	87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2354559
5°	1521348
10°	429259
15°	121367
20°	50749
25°	22480
30°	11475
35°	6055
40°	2585
45°	706
50°	777
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 777 cd/sqm

TEST NUMBER: P1310288

CATALOG NUMBER: LDSQA3D10R129035DE010 3LSQCBR1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	620.0	66.8
10°-20°	224.9	24.2
20°-30°	60.2	6.5
30°-40°	18.9	2.0
40°-50°	3.6	0.4
50°-60°	0.3	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	905.2	97.5
0°-40°	924.1	99.6
0°-60°	928.0	100.0
0°-90°	928.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	928.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13672	
5°	8800	620
15°	681	225
25°	118	60
35°	29	19
45°	3	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1310288

CATALOG NUMBER: LDSQA3D10R129035DE010 3LSQCBR1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	13671.6
1°	13440.9
2°	12791.9
3°	11681.5
4°	10302.8
5°	8800.0
6°	7233.9
7°	5832.1
8°	4488.0
9°	3340.0
10°	2454.6
11°	1808.5
12°	1361.4
13°	1055.7
14°	836.5
15°	680.7
17.5°	432.6
20°	276.9
22.5°	178.8
25°	118.3
27.5°	80.8
30°	57.7
32.5°	40.4
35°	28.8
37.5°	20.2
40°	11.5
42.5°	5.8
45°	2.9
47.5°	2.9
50°	2.9
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1310288

CATALOG NUMBER: LDSQA3D10R129035DE010 3LSQCBR1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)