

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1308695

Luminaire Tested: LDSQA3D02R129030DE010 3LSQPHRLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1308695
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R129030DE010 3LSQPHRLD1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , 3LSQPHRLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 308.0 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1308695

CATALOG NUMBER: LDSQA3D02R129030DE010 3LSQPHRLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1308695

CATALOG NUMBER: LDSQA3D02R129030DE010 3LSQPHRLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	116	114	113	111	114	112	111	109	108	107	106		104	104	103		101	101	100	98
2	113	110	108	106	111	108	106	104	105	104	102		103	101	100		100	99	98	97
3	110	107	104	102	109	105	103	101	103	101	99		101	99	98		99	98	96	95
4	108	104	101	98	107	103	100	98	101	99	97		99	97	96		98	96	95	94
5	106	102	98	96	105	101	98	96	99	97	95		98	96	94		96	95	93	92
6	104	99	96	94	103	99	96	94	98	95	93		96	94	93		95	93	92	91
7	102	98	94	92	101	97	94	92	96	93	92		95	93	91		94	92	91	90
8	101	96	93	91	100	95	92	90	95	92	90		94	92	90		93	91	90	89
9	99	94	91	89	98	94	91	89	93	91	89		93	90	89		92	90	88	88
10	98	93	90	88	97	93	90	88	92	90	88		91	89	88		91	89	87	87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	781477
5°	504932
10°	142474
15°	40278
20°	16843
25°	7449
30°	3798
35°	2018
40°	854
45°	244
50°	268
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 268 cd/sqm

TEST NUMBER: P1308695

CATALOG NUMBER: LDSQA3D02R129030DE010 3LSQPHRLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.8	66.8
10°-20°	74.7	24.2
20°-30°	20.0	6.5
30°-40°	6.3	2.0
40°-50°	1.2	0.4
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	300.4	97.5
0°-40°	306.7	99.6
0°-60°	308.0	100.0
0°-90°	308.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	308.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4538	
5°	2921	206
15°	226	75
25°	39	20
35°	10	6
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1308695

CATALOG NUMBER: LDSQA3D02R129030DE010 3LSQPHRLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4537.6
1°	4461.0
2°	4245.6
3°	3877.0
4°	3419.5
5°	2920.7
6°	2400.9
7°	1935.6
8°	1489.5
9°	1108.5
10°	814.7
11°	600.2
12°	451.8
13°	350.4
14°	277.6
15°	225.9
17.5°	143.6
20°	91.9
22.5°	59.4
25°	39.2
27.5°	26.8
30°	19.1
32.5°	13.4
35°	9.6
37.5°	6.7
40°	3.8
42.5°	1.9
45°	1.0
47.5°	1.0
50°	1.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1308695

CATALOG NUMBER: LDSQA3D02R129030DE010 3LSQPHRLD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)