

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1308721

Luminaire Tested: LDSQA3D02R209030DE010 3LSQPHR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1308721
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R209030DE010 3LSQPHR1MMS
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , 3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 273.0 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.36 / 0.33
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1308721
CATALOG NUMBER: LDSQA3D02R209030DE010 3LSQPHR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1308721

CATALOG NUMBER: LDSQA3D02R209030DE010 3LSQPHR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	100	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	95	98	96	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	93	96	95	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	92	95	93	91
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	90	93	91	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	88	92	90	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	87	91	88	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85	89	87	85
10	95	90	87	85	95	90	87	85	89	86	84	88	86	84	88	86	84	84	88	86	83

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	350060	350060	350060
5°	302403	305221	306362
10°	182050	183746	192892
15°	62975	61495	66398
20°	16531	15560	15597
25°	3611	4352	4941
30°	1551	1551	1591
35°	862	757	820
40°	382	427	495
45°	122	170	170
50°	54	54	54
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 170 cd/sqm



TEST NUMBER: P1308721

CATALOG NUMBER: LDSQA3D02R209030DE010 3LSQPHR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.4	53.3
10°-20°	110.7	40.5
20°-30°	13.7	5.0
30°-40°	2.6	0.9
40°-50°	0.6	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	269.8	98.8
0°-40°	272.3	99.8
0°-60°	273.0	100.0
0°-90°	273.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	273.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2033	2033	2033	2033	2033	
5°	1749	1748	1766	1764	1772	144
15°	353	340	345	366	372	111
25°	19	22	23	24	26	13
35°	4	4	4	4	4	3
45°	0	1	1	1	1	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1308721
 CATALOG NUMBER: LDSQA3D02R209030DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2032.6	2032.6	2032.6	2032.6	2032.6
1°	2023.1	2020.6	2022.6	2018.5	2027.0
2°	1990.7	1988.3	1988.3	1985.9	1987.1
3°	1930.4	1934.3	1931.9	1926.8	1933.3
4°	1848.2	1852.6	1856.5	1856.7	1857.7
5°	1749.2	1748.0	1765.5	1764.3	1772.1
6°	1636.4	1634.9	1642.4	1655.1	1670.7
7°	1512.3	1494.6	1514.8	1540.3	1561.2
8°	1351.8	1356.4	1370.3	1400.4	1417.2
9°	1215.6	1188.6	1218.0	1254.0	1272.3
10°	1041.0	1019.1	1050.7	1088.6	1103.0
12.5°	655.2	636.3	646.5	686.4	692.7
15°	353.2	340.5	344.9	365.6	372.4
17.5°	180.2	168.8	166.4	179.5	181.0
20°	90.2	87.6	84.9	86.1	85.1
22.5°	41.8	45.5	45.0	42.6	45.5
25°	19.0	21.6	22.9	23.8	26.0
27.5°	11.7	11.2	12.9	13.9	14.1
30°	7.8	7.5	7.8	8.0	8.0
32.5°	5.6	5.4	5.1	5.1	5.4
35°	4.1	4.1	3.6	3.9	3.9
37.5°	2.9	2.9	2.7	2.9	2.9
40°	1.7	1.9	1.9	1.9	2.2
42.5°	1.0	1.2	1.2	1.2	1.2
45°	0.5	0.7	0.7	0.7	0.7
47.5°	0.2	0.2	0.2	0.5	0.5
50°	0.2	0.2	0.2	0.2	0.2
52.5°	0.2	0.0	0.0	0.0	0.2
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)