

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1308734

Luminaire Tested: LDSQA3D02R259030DE010 3LSQCDR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1308734
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R259030DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 318.0 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.45 / 0.41
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1308734
CATALOG NUMBER: LDSQA3D02R259030DE010 3LSQCDR1MB

Luminous Intensity Polar Plot



0% Up
100% Dn

— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1308734
 CATALOG NUMBER: LDSQA3D02R259030DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	97	97	97	94	94	94	91	91	91	88	88	88	85	85	85	82	82	82	79	79	79	76	76	76										
1	115	113	111	110	113	111	110	108	107	106	105	103	103	102	100	99	99	97	97	97	94	94	94	91	91	91	88	88	88	85	85	85	82	82	82	79	79	79	76	76	76													
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	91	91	91	88	88	88	85	85	85	82	82	82	79	79	79	76	76	76																
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	91	91	91	88	88	88	85	85	85	82	82	82	79	79	79	76	76	76	73	73	73																
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	88	88	88	85	85	85	82	82	82	79	79	79	76	76	76	73	73	73																			
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	84	84	84	81	81	81	78	78	78	75	75	75	72	72	72																			
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	85	84	84	84	81	81	81	78	78	78	75	75	75	72	72	72	69	69	69																			
7	97	91	87	85	96	91	87	84	90	86	84	89	86	84	88	85	83	82	82	82	79	79	79	76	76	76	73	73	73	70	70	70	67	67	67																			
8	95	89	85	82	94	88	85	82	87	84	82	87	84	82	86	83	81	80	80	80	77	77	77	74	74	74	71	71	71	68	68	68	65	65	65																			
9	93	86	83	80	92	86	82	80	85	82	80	85	82	80	84	81	79	78	78	78	75	75	75	72	72	72	69	69	69	66	66	66	63	63	63																			
10	91	84	81	78	90	84	80	78	83	80	78	83	80	78	82	79	77	76	76	76	73	73	73	70	70	70	67	67	67	64	64	64	61	61	61																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	263105	263105	263105
5°	242603	243156	243658
10°	188363	189045	190076
15°	93089	96994	97048
20°	31340	33448	31963
25°	12979	14423	13359
30°	5091	6403	5151
35°	1325	2607	1388
40°	495	1034	495
45°	49	292	49
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 292 cd/sqm



TEST NUMBER: P1308734

CATALOG NUMBER: LDSQA3D02R259030DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	38.9
10°-20°	149.7	47.1
20°-30°	36.6	11.5
30°-40°	7.1	2.2
40°-50°	0.8	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	310.1	97.5
0°-40°	317.2	99.7
0°-60°	318.0	100.0
0°-90°	318.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	318.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1528	1528	1528	1528	1528	
5°	1403	1405	1406	1413	1409	123
15°	522	534	544	549	544	147
25°	68	72	76	73	70	35
35°	6	9	12	9	7	6
45°	0	1	1	1	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1308734
 CATALOG NUMBER: LDSQA3D02R259030DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1527.7	1527.7	1527.7	1527.7	1527.7
1°	1521.9	1522.8	1523.1	1524.6	1521.6
2°	1508.0	1508.2	1508.9	1511.9	1509.2
3°	1482.3	1484.1	1484.3	1488.2	1488.9
4°	1447.5	1448.4	1450.4	1457.0	1451.1
5°	1403.3	1405.3	1406.5	1412.6	1409.4
6°	1348.7	1349.1	1351.8	1358.9	1354.5
7°	1293.0	1292.8	1293.0	1298.6	1297.4
8°	1225.9	1224.7	1228.6	1235.5	1240.1
9°	1155.9	1157.6	1160.1	1166.7	1161.3
10°	1077.1	1081.8	1081.0	1081.5	1086.9
11°	986.4	987.8	988.1	993.2	992.5
12°	879.7	879.7	887.8	896.1	893.4
13°	772.2	779.7	774.4	776.1	786.8
14°	646.8	652.6	659.9	666.8	661.4
15°	522.1	534.5	544.0	549.4	544.3
17.5°	299.1	303.3	311.3	312.3	309.1
20°	171.0	176.1	182.5	180.5	174.4
22.5°	107.6	109.1	115.4	112.2	110.8
25°	68.3	72.0	75.9	72.7	70.3
27.5°	42.5	44.9	49.0	45.6	42.9
30°	25.6	27.8	32.2	27.6	25.9
32.5°	13.4	16.6	20.2	16.8	13.4
35°	6.3	9.0	12.4	9.0	6.6
37.5°	3.9	4.9	7.6	4.9	3.9
40°	2.2	3.2	4.6	3.2	2.2
42.5°	1.0	1.7	2.2	1.7	1.2
45°	0.2	0.7	1.2	0.7	0.2
47.5°	0.0	0.0	0.7	0.2	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1308734
CATALOG NUMBER: LDSQA3D02R259030DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)