

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1308923

Luminaire Tested: LDSQA3D05R309030DE010 3LSQPHR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1308923
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R309030DE010 3LSQPHR1MMS
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , 3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 581.0 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.49 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1308923
CATALOG NUMBER: LDSQA3D05R309030DE010 3LSQPHR1MMS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1308923

CATALOG NUMBER: LDSQA3D05R309030DE010 3LSQPHR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	97	97	97	97	97	97	97	97	97	97	100															
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	97	97	97	97	97	97	97	97	97	97	97	97															
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96	94	94	94	94	94	94	94	94	94	94	94	94	94	94															
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92	92	92	92	92	92	92	92	92	92	92															
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89	89	89	89	89	89	89	89	89	89	89															
5	102	97	93	90	101	96	93	90	95	91	89	93	90	88	92	89	88	87	87	87	87	87	87	87	87	87	87	87	87	87	87															
6	100	94	90	87	99	93	90	87	92	89	86	91	88	86	90	87	85	84	84	84	84	84	84	84	84	84	84	84	84	84	84															
7	97	91	87	84	96	91	87	84	90	86	84	88	86	83	88	85	83	82	82	82	82	82	82	82	82	82	82	82	82	82	82															
8	95	89	85	82	94	88	84	82	87	84	82	86	83	81	86	83	81	80	80	80	80	80	80	80	80	80	80	80	80	80	80															
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78	78	78	78	78	78	78	78	78	78	78															
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76	76	76	76	76	76	76	76	76	76	76															

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	412955	412955	412955
5°	402328	399561	396259
10°	339528	329106	323754
15°	204615	198891	202547
20°	69406	80146	92444
25°	12751	19991	23601
30°	4375	4872	5469
35°	1261	1577	1682
40°	337	562	450
45°	122	122	122
50°	134	0	134
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 141 cd/sqm



TEST NUMBER: P1308923

CATALOG NUMBER: LDSQA3D05R309030DE010 3LSQPHR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.3	35.7
10°-20°	303.0	52.2
20°-30°	64.1	11.0
30°-40°	5.9	1.0
40°-50°	0.6	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.5	98.9
0°-40°	580.4	99.9
0°-60°	581.0	100.0
0°-90°	581.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	581.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2398	2398	2398	2398	2398	
5°	2327	2323	2311	2304	2292	210
15°	1148	1144	1116	1142	1136	303
25°	67	75	105	124	124	49
35°	6	8	8	9	8	5
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1308923

CATALOG NUMBER: LDSQA3D05R309030DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2397.8	2397.8	2397.8	2397.8	2397.8
1°	2398.3	2395.8	2392.3	2397.3	2393.8
2°	2393.3	2387.3	2382.3	2387.3	2385.8
3°	2378.3	2373.3	2369.8	2372.3	2372.3
4°	2355.7	2350.2	2347.2	2347.7	2340.2
5°	2327.2	2322.7	2311.2	2304.1	2292.1
6°	2285.1	2274.1	2260.1	2248.5	2233.0
7°	2228.0	2211.0	2190.9	2170.9	2151.4
8°	2136.3	2128.3	2101.3	2087.8	2068.2
9°	2050.2	2030.7	2001.6	1979.6	1969.0
10°	1941.5	1912.4	1881.9	1864.4	1851.3
11°	1812.8	1783.2	1758.7	1733.1	1713.1
12°	1661.5	1636.4	1608.4	1591.4	1567.8
13°	1482.2	1478.7	1447.1	1441.6	1438.6
14°	1328.4	1314.4	1283.3	1291.8	1293.8
15°	1147.6	1143.6	1115.5	1141.6	1136.0
17.5°	718.8	720.3	737.8	778.9	791.9
20°	378.7	390.2	437.3	486.9	504.4
22.5°	153.3	178.8	226.9	260.5	283.0
25°	67.1	75.1	105.2	123.7	124.2
27.5°	38.1	38.6	50.6	52.6	53.6
30°	22.0	22.5	24.5	26.0	27.5
32.5°	12.0	13.0	13.5	15.5	15.5
35°	6.0	7.5	7.5	9.0	8.0
37.5°	3.5	4.0	4.5	4.5	4.0
40°	1.5	2.0	2.5	2.5	2.0
42.5°	0.5	1.0	1.0	1.0	1.5
45°	0.5	0.5	0.5	0.5	0.5
47.5°	0.5	0.5	0.0	0.5	0.5
50°	0.5	0.0	0.0	0.0	0.5
52.5°	0.5	0.0	0.0	0.0	0.5
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1308923
CATALOG NUMBER: LDSQA3D05R309030DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)