

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1308972

Luminaire Tested: LDSQA3D05R509030DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1308972
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R509030DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 700.0 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.78
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1308972
CATALOG NUMBER: LDSQA3D05R509030DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1308972

CATALOG NUMBER: LDSQA3D05R509030DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95	95	95	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76	76	76	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	72	72	72	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	69	69	69	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	65	65	65	65
9	81	73	67	64	80	72	67	64	71	67	64	70	66	63	70	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	59	59	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	187206	187206	187206
5°	183945	183426	182908
10°	177398	175474	175824
15°	163196	161146	161591
20°	145722	144348	145173
25°	113408	118178	112173
30°	61430	68609	60336
35°	19364	23064	18943
40°	4272	5958	4047
45°	122	1827	122
50°	0	268	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 1827 cd/sqm



TEST NUMBER: P1308972

CATALOG NUMBER: LDSQA3D05R509030DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	14.2
10°-20°	253.0	36.1
20°-30°	266.5	38.1
30°-40°	76.1	10.9
40°-50°	4.7	0.7
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.1	88.4
0°-40°	695.3	99.3
0°-60°	700.0	100.0
0°-90°	700.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	700.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1087	1087	1087	1087	1087	
5°	1064	1063	1061	1060	1058	100
15°	915	909	904	905	906	255
25°	597	619	622	615	590	261
35°	92	99	110	93	90	72
45°	0	2	8	2	0	3
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1308972

CATALOG NUMBER: LDSQA3D05R509030DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1087.0	1087.0	1087.0	1087.0	1087.0
1°	1087.5	1088.0	1087.0	1088.0	1085.5
2°	1086.0	1085.0	1084.0	1084.5	1083.0
3°	1080.5	1080.0	1078.0	1078.5	1076.5
4°	1073.5	1072.0	1070.5	1069.5	1067.5
5°	1064.0	1063.0	1061.0	1060.0	1058.0
6°	1056.0	1054.0	1050.5	1049.5	1047.5
7°	1045.5	1044.5	1040.0	1039.0	1038.0
8°	1037.5	1034.5	1029.0	1029.5	1027.0
9°	1027.0	1022.9	1017.4	1017.4	1017.9
10°	1014.4	1008.4	1003.4	1004.9	1005.4
11°	997.9	993.9	986.4	989.9	989.9
12°	979.9	974.9	969.4	972.4	974.4
13°	958.9	954.9	949.8	952.8	951.8
14°	938.3	930.8	927.3	931.3	929.8
15°	915.3	909.3	903.8	905.3	906.3
17.5°	853.7	847.2	843.2	843.7	848.2
20°	795.1	792.6	787.6	789.6	792.1
22.5°	726.0	727.0	721.0	722.5	728.5
25°	596.8	618.9	621.9	614.9	590.3
27.5°	442.1	475.2	485.2	469.2	439.1
30°	308.9	318.0	345.0	314.4	303.4
32.5°	181.3	194.8	209.3	188.3	180.8
35°	92.1	98.6	109.7	93.1	90.1
37.5°	42.6	45.6	50.1	42.6	40.1
40°	19.0	22.5	26.5	21.5	18.0
42.5°	6.0	10.5	14.0	9.5	5.5
45°	0.5	2.5	7.5	2.5	0.5
47.5°	0.0	0.5	3.0	0.5	0.0
50°	0.0	0.0	1.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1308972
CATALOG NUMBER: LDSQA3D05R509030DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)