

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1310842

Luminaire Tested: LDSQA3D24R409035D010 3LSQCA45R 1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1310842
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-78)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D24R409035D010 3LSQCA45R 1MB
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , 3LSQCA45R 1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2222.0 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 3.99 / 0.73 / 1.54
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1310842
CATALOG NUMBER: LDSQA3D24R409035D010 3LSQCA45R 1MB

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ····· 90°-270°



TEST NUMBER: P1310842

CATALOG NUMBER: LDSQA3D24R409035D010 3LSQCA45R 1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 |
| 1 | 110 | 106 | 102 | 99 | 107 | 104 | 100 | 97 | 99 | 97 | 94 | 96 | 93 | 91 | 92 | 90 | 88 | 86 | 86 | 86 |
| 2 | 100 | 93 | 86 | 81 | 98 | 91 | 85 | 80 | 87 | 82 | 78 | 84 | 80 | 76 | 81 | 78 | 75 | 72 | 72 | 72 |
| 3 | 91 | 81 | 73 | 66 | 89 | 79 | 72 | 66 | 76 | 70 | 65 | 73 | 68 | 64 | 71 | 66 | 62 | 60 | 60 | 60 |
| 4 | 82 | 70 | 62 | 55 | 80 | 69 | 61 | 54 | 67 | 59 | 54 | 64 | 58 | 53 | 62 | 57 | 52 | 50 | 50 | 50 |
| 5 | 75 | 62 | 52 | 46 | 73 | 60 | 52 | 45 | 58 | 51 | 45 | 56 | 50 | 44 | 54 | 49 | 44 | 42 | 42 | 42 |
| 6 | 68 | 54 | 45 | 38 | 66 | 53 | 44 | 38 | 51 | 43 | 38 | 50 | 43 | 37 | 48 | 42 | 37 | 35 | 35 | 35 |
| 7 | 62 | 48 | 39 | 32 | 60 | 47 | 38 | 32 | 45 | 37 | 32 | 44 | 37 | 31 | 42 | 36 | 31 | 29 | 29 | 29 |
| 8 | 57 | 42 | 33 | 27 | 55 | 42 | 33 | 27 | 40 | 32 | 27 | 39 | 32 | 27 | 38 | 31 | 26 | 24 | 24 | 24 |
| 9 | 52 | 38 | 29 | 23 | 51 | 37 | 29 | 23 | 36 | 28 | 23 | 35 | 28 | 23 | 34 | 27 | 23 | 21 | 21 | 21 |
| 10 | 48 | 34 | 25 | 20 | 47 | 33 | 25 | 20 | 32 | 25 | 20 | 31 | 24 | 20 | 30 | 24 | 19 | 18 | 18 | 18 |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 45° | 90° | 135° | 180° |
|-----|---------|-------|-------|-------|-------|
| 0° | 19685 | 19685 | 19685 | 19685 | 19685 |
| 5° | 21869 | 21161 | 19397 | 17634 | 17288 |
| 10° | 26407 | 22489 | 17838 | 16054 | 15704 |
| 15° | 43291 | 24373 | 15280 | 14193 | 14549 |
| 20° | 114437 | 28793 | 12719 | 12719 | 13837 |
| 25° | 441280 | 35668 | 10090 | 11630 | 13568 |
| 30° | 952009 | 47469 | 8114 | 11355 | 13384 |
| 35° | 1432946 | 56198 | 6854 | 11164 | 13729 |
| 40° | 1614415 | 56430 | 5958 | 11466 | 14681 |
| 45° | 1731075 | 43743 | 5456 | 11934 | 15904 |
| 50° | 1701441 | 27329 | 4930 | 12566 | 17496 |
| 55° | 1496861 | 13482 | 4894 | 14082 | 19607 |
| 60° | 947466 | 2824 | 5614 | 15466 | 21803 |
| 65° | 193773 | 815 | 5827 | 16627 | 24125 |
| 70° | 4129 | 1007 | 6143 | 18480 | 27745 |
| 75° | 4059 | 2728 | 6787 | 20362 | 31208 |
| 80° | 4066 | 1984 | 8133 | 22216 | 36399 |
| 85° | 3952 | 3952 | 16203 | 24108 | 40311 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 47°
 Luminance: 1762332 cd/sqm



TEST NUMBER: P1310842

CATALOG NUMBER: LDSQA3D24R409035D010 3LSQCA45R 1MB

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 10.7 | 0.5 |
| 10°-20° | 35.2 | 1.6 |
| 20°-30° | 172.6 | 7.8 |
| 30°-40° | 561.4 | 25.3 |
| 40°-50° | 773.9 | 34.8 |
| 50°-60° | 539.1 | 24.3 |
| 60°-70° | 102.2 | 4.6 |
| 70°-80° | 18.5 | 0.8 |
| 80°-90° | 8.5 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 218.5 | 9.8 |
| 0°-40° | 779.9 | 35.1 |
| 0°-60° | 2092.8 | 94.2 |
| 0°-90° | 2222.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2222.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 45° | 90° | 135° | 180° | Flux |
|-----|------|-----|-----|------|------|------|
| 0° | 114 | 114 | 114 | 114 | 114 | |
| 5° | 126 | 122 | 112 | 102 | 100 | 13 |
| 15° | 243 | 137 | 86 | 80 | 82 | 88 |
| 25° | 2322 | 188 | 53 | 61 | 71 | 1196 |
| 35° | 6816 | 267 | 33 | 53 | 65 | 4119 |
| 45° | 7107 | 180 | 22 | 49 | 65 | 5405 |
| 55° | 4985 | 45 | 16 | 47 | 65 | 4261 |
| 65° | 476 | 2 | 14 | 41 | 59 | 841 |
| 75° | 6 | 4 | 10 | 31 | 47 | 6 |
| 85° | 2 | 2 | 8 | 12 | 20 | 2 |
| 90° | 0 | 0 | 0 | 0 | 0 | |



TEST NUMBER: P1310842

CATALOG NUMBER: LDSQA3D24R409035D010 3LSQCA45R 1MB

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 45° | 67.5° | 90° |
|-------|--------|--------|--------|--------|--------|--------|--------|-------|-------|-------|-------|
| 0° | 114.3 | 114.3 | 114.3 | 114.3 | 114.3 | 114.3 | 114.3 | 114.3 | 114.3 | 114.3 | 114.3 |
| 2.5° | 118.4 | 118.4 | 118.4 | 118.4 | 118.4 | 118.4 | 118.4 | 118.4 | 118.4 | 116.3 | 114.3 |
| 5° | 126.5 | 126.5 | 126.5 | 126.5 | 124.5 | 124.5 | 124.5 | 122.4 | 122.4 | 118.4 | 112.2 |
| 7.5° | 134.7 | 134.7 | 134.7 | 134.7 | 132.6 | 130.6 | 128.6 | 128.6 | 126.5 | 116.3 | 108.2 |
| 10° | 151.0 | 151.0 | 149.0 | 146.9 | 144.9 | 140.8 | 138.8 | 134.7 | 128.6 | 114.3 | 102.0 |
| 12.5° | 183.7 | 179.6 | 177.5 | 173.5 | 167.3 | 159.2 | 151.0 | 144.9 | 130.6 | 110.2 | 95.9 |
| 15° | 242.8 | 238.7 | 230.6 | 218.3 | 206.1 | 189.8 | 175.5 | 161.2 | 136.7 | 104.1 | 85.7 |
| 17.5° | 346.9 | 334.7 | 322.4 | 302.0 | 271.4 | 242.8 | 212.2 | 185.7 | 144.9 | 97.9 | 77.5 |
| 20° | 624.4 | 616.3 | 542.8 | 485.7 | 393.8 | 328.5 | 267.3 | 222.4 | 157.1 | 91.8 | 69.4 |
| 22.5° | 1287.6 | 1201.9 | 1081.5 | 885.6 | 689.7 | 508.1 | 369.3 | 279.6 | 169.4 | 83.7 | 61.2 |
| 25° | 2322.2 | 2187.5 | 1928.4 | 1550.9 | 1144.8 | 810.1 | 534.6 | 365.3 | 187.7 | 75.5 | 53.1 |
| 27.5° | 3516.0 | 3379.2 | 2977.2 | 2456.9 | 1793.7 | 1222.3 | 763.2 | 483.6 | 212.2 | 67.3 | 46.9 |
| 30° | 4787.2 | 4670.9 | 4160.8 | 3440.4 | 2528.3 | 1712.1 | 1022.3 | 604.0 | 238.7 | 59.2 | 40.8 |
| 31° | 5299.4 | 5150.5 | 4599.5 | 3832.2 | 2873.2 | 1914.1 | 1126.4 | 655.0 | 249.0 | 57.1 | 38.8 |
| 32° | 5770.8 | 5601.4 | 5030.1 | 4207.7 | 3152.7 | 2132.4 | 1240.7 | 699.9 | 257.1 | 53.1 | 36.7 |
| 33° | 6176.9 | 5979.0 | 5428.0 | 4562.8 | 3460.9 | 2336.5 | 1359.0 | 742.8 | 263.2 | 49.0 | 34.7 |
| 34° | 6521.8 | 6350.3 | 5758.6 | 4919.9 | 3734.3 | 2532.4 | 1475.4 | 785.6 | 267.3 | 46.9 | 32.6 |
| 35° | 6815.6 | 6660.5 | 6074.9 | 5191.3 | 4001.6 | 2722.2 | 1581.5 | 826.4 | 267.3 | 42.9 | 32.6 |
| 36° | 7013.5 | 6878.9 | 6348.3 | 5468.8 | 4226.1 | 2883.4 | 1671.2 | 863.2 | 267.3 | 38.8 | 30.6 |
| 37° | 7121.7 | 6991.1 | 6527.9 | 5697.4 | 4446.5 | 3042.5 | 1752.9 | 891.7 | 265.3 | 36.7 | 28.6 |
| 38° | 7176.8 | 7062.5 | 6660.5 | 5883.0 | 4599.5 | 3156.8 | 1824.3 | 914.2 | 263.2 | 32.6 | 28.6 |
| 39° | 7191.1 | 7095.2 | 6744.2 | 6017.7 | 4748.5 | 3271.1 | 1875.3 | 926.4 | 257.1 | 30.6 | 26.5 |
| 40° | 7180.9 | 7097.2 | 6789.1 | 6138.1 | 4862.7 | 3360.9 | 1912.0 | 930.5 | 251.0 | 26.5 | 26.5 |
| 41° | 7160.5 | 7095.2 | 6821.7 | 6221.8 | 4954.6 | 3418.0 | 1926.3 | 922.4 | 242.8 | 22.4 | 24.5 |
| 42° | 7142.1 | 7070.7 | 6836.0 | 6278.9 | 5017.8 | 3446.6 | 1924.3 | 906.0 | 230.6 | 20.4 | 24.5 |
| 43° | 7142.1 | 7060.5 | 6838.0 | 6315.7 | 5048.4 | 3448.6 | 1899.8 | 875.4 | 214.3 | 18.4 | 22.4 |
| 44° | 7129.9 | 7054.3 | 6848.2 | 6340.1 | 5056.6 | 3430.2 | 1861.0 | 842.8 | 195.9 | 16.3 | 22.4 |
| 45° | 7107.4 | 7027.8 | 6846.2 | 6342.2 | 5042.3 | 3385.4 | 1797.8 | 799.9 | 179.6 | 12.2 | 22.4 |
| 46° | 7064.6 | 6993.1 | 6827.8 | 6327.9 | 4999.5 | 3320.1 | 1722.3 | 757.1 | 161.2 | 10.2 | 20.4 |
| 47° | 6978.8 | 6923.7 | 6778.9 | 6278.9 | 4934.2 | 3224.1 | 1632.5 | 708.1 | 146.9 | 8.2 | 20.4 |
| 48° | 6831.9 | 6793.2 | 6695.2 | 6170.8 | 4809.7 | 3105.8 | 1536.6 | 655.0 | 132.6 | 8.2 | 20.4 |
| 49° | 6562.6 | 6532.0 | 6474.8 | 5997.3 | 4650.5 | 2960.9 | 1432.5 | 595.9 | 118.4 | 6.1 | 20.4 |
| 50° | 6350.3 | 6317.7 | 6201.4 | 5705.5 | 4422.0 | 2777.3 | 1318.2 | 536.7 | 102.0 | 4.1 | 18.4 |
| 51° | 6209.5 | 6156.5 | 5972.8 | 5366.8 | 4089.4 | 2532.4 | 1193.7 | 477.5 | 85.7 | 4.1 | 18.4 |
| 52° | 6032.0 | 5952.4 | 5723.9 | 5062.7 | 3785.3 | 2287.5 | 1059.1 | 418.3 | 75.5 | 4.1 | 18.4 |
| 53° | 5660.6 | 5632.1 | 5405.5 | 4736.2 | 3481.3 | 2052.8 | 920.3 | 369.3 | 65.3 | 4.1 | 18.4 |
| 54° | 5336.2 | 5293.3 | 4985.2 | 4283.2 | 3150.7 | 1791.6 | 777.5 | 326.5 | 55.1 | 4.1 | 18.4 |
| 55° | 4985.2 | 4901.5 | 4628.1 | 3901.6 | 2763.0 | 1550.9 | 640.7 | 281.6 | 44.9 | 4.1 | 16.3 |
| 56° | 4542.4 | 4468.9 | 4175.1 | 3493.5 | 2405.9 | 1306.0 | 536.7 | 230.6 | 34.7 | 4.1 | 16.3 |
| 57° | 4003.7 | 3936.3 | 3709.8 | 2991.5 | 2034.5 | 1067.2 | 436.7 | 185.7 | 26.5 | 4.1 | 16.3 |
| 58° | 3483.3 | 3407.8 | 3148.6 | 2509.9 | 1642.7 | 846.8 | 365.3 | 151.0 | 20.4 | 4.1 | 16.3 |
| 59° | 3083.3 | 2981.3 | 2646.7 | 2107.9 | 1285.6 | 642.8 | 289.8 | 120.4 | 14.3 | 4.1 | 16.3 |
| 60° | 2750.7 | 2667.1 | 2320.2 | 1754.9 | 1008.1 | 473.4 | 214.3 | 91.8 | 8.2 | 4.1 | 16.3 |
| 62.5° | 1593.7 | 1571.3 | 1259.0 | 904.0 | 475.5 | 220.4 | 106.1 | 42.9 | 4.1 | 6.1 | 16.3 |
| 65° | 475.5 | 414.2 | 322.4 | 191.8 | 122.4 | 73.5 | 38.8 | 14.3 | 2.0 | 6.1 | 14.3 |



TEST NUMBER: P1310842
 CATALOG NUMBER: LDSQA3D24R409035D010 3LSQCA45R 1MB

CANDELA DISTRIBUTION (continued):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 45° | 67.5° | 90° |
|-------|------|------|------|------|------|------|-----|-----|-----|-------|------|
| 67.5° | 14.3 | 14.3 | 14.3 | 14.3 | 14.3 | 14.3 | 8.2 | 4.1 | 2.0 | 6.1 | 14.3 |
| 70° | 8.2 | 6.1 | 6.1 | 6.1 | 6.1 | 4.1 | 4.1 | 2.0 | 2.0 | 6.1 | 12.2 |
| 72.5° | 6.1 | 6.1 | 6.1 | 6.1 | 4.1 | 4.1 | 4.1 | 2.0 | 4.1 | 6.1 | 10.2 |
| 75° | 6.1 | 4.1 | 4.1 | 4.1 | 4.1 | 2.0 | 2.0 | 2.0 | 4.1 | 6.1 | 10.2 |
| 77.5° | 4.1 | 4.1 | 4.1 | 4.1 | 2.0 | 2.0 | 2.0 | 2.0 | 4.1 | 6.1 | 10.2 |
| 80° | 4.1 | 4.1 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 6.1 | 8.2 |
| 82.5° | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 6.1 | 8.2 |
| 85° | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 2.0 | 6.1 | 8.2 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 2.0 | 2.0 | 6.1 | 6.1 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



TEST NUMBER: P1310842
 CATALOG NUMBER: LDSQA3D24R409035D010 3LSQCA45R 1MB

CANDELA DISTRIBUTION (continued):

| | 112.5° | 135° | 157.5° | 180° |
|-------|--------|-------|--------|-------|
| 0° | 114.3 | 114.3 | 114.3 | 114.3 |
| 2.5° | 110.2 | 108.2 | 106.1 | 106.1 |
| 5° | 106.1 | 102.0 | 102.0 | 100.0 |
| 7.5° | 100.0 | 95.9 | 95.9 | 95.9 |
| 10° | 93.9 | 91.8 | 91.8 | 89.8 |
| 12.5° | 85.7 | 85.7 | 85.7 | 85.7 |
| 15° | 79.6 | 79.6 | 81.6 | 81.6 |
| 17.5° | 71.4 | 73.5 | 77.5 | 79.6 |
| 20° | 65.3 | 69.4 | 73.5 | 75.5 |
| 22.5° | 61.2 | 65.3 | 71.4 | 73.5 |
| 25° | 55.1 | 61.2 | 69.4 | 71.4 |
| 27.5° | 51.0 | 59.2 | 65.3 | 69.4 |
| 30° | 46.9 | 57.1 | 63.3 | 67.3 |
| 31° | 46.9 | 55.1 | 63.3 | 67.3 |
| 32° | 44.9 | 53.1 | 63.3 | 65.3 |
| 33° | 44.9 | 53.1 | 63.3 | 65.3 |
| 34° | 42.9 | 53.1 | 61.2 | 65.3 |
| 35° | 42.9 | 53.1 | 61.2 | 65.3 |
| 36° | 40.8 | 51.0 | 61.2 | 65.3 |
| 37° | 40.8 | 51.0 | 61.2 | 65.3 |
| 38° | 38.8 | 51.0 | 61.2 | 65.3 |
| 39° | 38.8 | 51.0 | 61.2 | 65.3 |
| 40° | 38.8 | 51.0 | 61.2 | 65.3 |
| 41° | 36.7 | 51.0 | 61.2 | 65.3 |
| 42° | 36.7 | 51.0 | 61.2 | 65.3 |
| 43° | 36.7 | 49.0 | 61.2 | 65.3 |
| 44° | 36.7 | 49.0 | 61.2 | 65.3 |
| 45° | 34.7 | 49.0 | 61.2 | 65.3 |
| 46° | 34.7 | 49.0 | 61.2 | 65.3 |
| 47° | 34.7 | 49.0 | 61.2 | 65.3 |
| 48° | 34.7 | 49.0 | 61.2 | 65.3 |
| 49° | 34.7 | 49.0 | 61.2 | 65.3 |
| 50° | 32.6 | 46.9 | 61.2 | 65.3 |
| 51° | 32.6 | 46.9 | 61.2 | 65.3 |
| 52° | 32.6 | 46.9 | 61.2 | 65.3 |
| 53° | 32.6 | 46.9 | 61.2 | 65.3 |
| 54° | 30.6 | 46.9 | 61.2 | 65.3 |
| 55° | 30.6 | 46.9 | 61.2 | 65.3 |
| 56° | 30.6 | 46.9 | 61.2 | 63.3 |
| 57° | 30.6 | 46.9 | 59.2 | 63.3 |
| 58° | 30.6 | 44.9 | 59.2 | 63.3 |
| 59° | 30.6 | 44.9 | 59.2 | 63.3 |
| 60° | 30.6 | 44.9 | 59.2 | 63.3 |
| 62.5° | 28.6 | 44.9 | 57.1 | 61.2 |
| 65° | 26.5 | 40.8 | 57.1 | 59.2 |



TEST NUMBER: P1310842
CATALOG NUMBER: LDSQA3D24R409035D010 3LSQCA45R 1MB

CANDELA DISTRIBUTION (continued):

| | 112.5° | 135° | 157.5° | 180° |
|-------|--------|------|--------|------|
| 67.5° | 26.5 | 38.8 | 53.1 | 57.1 |
| 70° | 24.5 | 36.7 | 51.0 | 55.1 |
| 72.5° | 20.4 | 34.7 | 46.9 | 51.0 |
| 75° | 18.4 | 30.6 | 42.9 | 46.9 |
| 77.5° | 16.3 | 26.5 | 38.8 | 40.8 |
| 80° | 14.3 | 22.4 | 32.6 | 36.7 |
| 82.5° | 10.2 | 16.3 | 26.5 | 28.6 |
| 85° | 8.2 | 12.2 | 18.4 | 20.4 |
| 87.5° | 6.1 | 6.1 | 10.2 | 10.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)