

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1310378

Luminaire Tested: LDSQA3D13R359035DE010 3LSQCA45R 1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1310378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-77)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D13R359035DE010 3LSQCA45R 1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 90CRI , 3LSQCA45R 1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1108.0 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 4.01 / 0.66 / 1.41
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1310378
CATALOG NUMBER: LDSQA3D13R359035DE010 3LSQCA45R 1MW

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1310378

CATALOG NUMBER: LDSQA3D13R359035DE010 3LSQCA45R 1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	99	107	104	100	97	100	97	94	96	93	91	92	90	89	89	89	89	87
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	75	75	73
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	67	63	63	63	63	61
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	52	52	52	52	50
5	75	62	52	46	73	61	52	45	58	51	45	56	50	44	55	49	44	44	44	44	42
6	68	54	45	38	66	53	44	38	51	43	38	50	43	37	48	42	37	37	37	37	35
7	62	48	38	32	60	47	38	32	45	37	32	44	37	31	42	36	31	31	31	31	29
8	57	42	33	27	55	41	33	27	40	32	27	39	32	26	38	31	26	26	26	26	24
9	52	38	29	23	50	37	29	23	36	28	23	35	28	22	34	27	22	22	22	22	20
10	48	34	25	19	46	33	25	19	32	25	19	31	24	19	30	24	19	19	19	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	8783	8783	8783	8783	8783
5°	9508	9336	8644	7780	7607
10°	9968	9094	7695	6645	6645
15°	14264	8915	6240	5706	5884
20°	35739	9530	4948	4948	5498
25°	165931	12162	3801	4561	5131
30°	504423	16506	2983	4176	5171
35°	852502	19132	2523	3995	5046
40°	999305	18885	2023	4047	5396
45°	1052397	13396	1705	4384	5845
50°	1001740	8038	1608	4555	6430
55°	839410	3303	1802	5104	7507
60°	469927	689	2067	5856	8267
65°	81095	408	2038	6520	9373
70°	1511	504	2518	7050	10574
75°	1331	665	3327	7985	11978
80°	992	992	3967	8926	13885
85°	0	1976	7904	9880	15808

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 46°
 Luminance: 1059851 cd/sqm



TEST NUMBER: P1310378

CATALOG NUMBER: LDSQA3D13R359035DE010 3LSQCA45R 1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4.6	0.4
10°-20°	13.1	1.2
20°-30°	68.0	6.1
30°-40°	293.6	26.5
40°-50°	418.8	37.8
50°-60°	259.4	23.4
60°-70°	39.5	3.6
70°-80°	7.4	0.7
80°-90°	3.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	85.6	7.7
0°-40°	379.2	34.2
0°-60°	1057.4	95.4
0°-90°	1108.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1108.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	51	51	51	51	51	
5°	55	54	50	45	44	5
15°	80	50	35	32	33	29
25°	873	64	20	24	27	523
35°	4055	91	12	19	24	2435
45°	4321	55	7	18	24	3264
55°	2796	11	6	17	25	2381
65°	199	1	5	16	23	407
75°	2	1	5	12	18	2
85°	0	1	4	5	8	0
90°	0	0	0	0	0	



TEST NUMBER: P1310378

CATALOG NUMBER: LDSQA3D13R359035DE010 3LSQCA45R 1MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
0°	51.0	51.0	51.0	51.0	51.0	51.0	51.0	51.0	51.0	51.0	51.0
2.5°	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0	53.0	51.0	50.0
5°	55.0	55.0	54.0	54.0	54.0	54.0	54.0	54.0	52.0	50.0	47.0
7.5°	56.0	56.0	55.0	55.0	55.0	55.0	54.0	53.0	51.0	47.0	44.0
10°	57.0	57.0	57.0	57.0	56.0	55.0	54.0	52.0	49.0	44.0	41.0
12.5°	64.0	64.0	63.0	61.0	59.0	57.0	55.0	51.0	45.0	40.0	37.0
15°	80.0	79.0	77.0	74.0	70.0	65.0	61.0	50.0	41.0	35.0	33.0
17.5°	112.0	110.0	107.0	97.0	88.0	79.0	71.0	50.0	37.0	31.0	29.0
20°	195.0	196.0	175.0	151.0	131.0	109.0	89.0	52.0	33.0	27.0	26.0
22.5°	407.1	391.1	341.1	283.1	216.0	167.0	126.0	57.0	29.0	23.0	23.0
25°	873.2	812.2	691.1	522.1	368.1	261.1	183.0	64.0	26.0	20.0	21.0
27.5°	1594.3	1539.3	1296.3	976.2	648.1	394.1	248.1	73.0	23.0	17.0	19.0
30°	2536.5	2384.5	2067.4	1600.3	1083.2	603.1	333.1	83.0	19.0	15.0	18.0
31°	2830.6	2760.6	2374.5	1851.4	1269.3	716.1	369.1	86.0	18.0	15.0	17.0
32°	3179.7	3055.6	2709.6	2126.4	1458.3	817.2	412.1	89.0	17.0	13.0	17.0
33°	3491.7	3371.7	2950.6	2368.5	1649.3	932.2	458.1	90.0	15.0	13.0	16.0
34°	3819.8	3655.8	3238.7	2621.5	1845.4	1056.2	500.1	91.0	14.0	12.0	16.0
35°	4054.8	3890.8	3486.7	2821.6	2014.4	1166.2	548.1	91.0	13.0	12.0	15.0
36°	4236.9	4092.8	3700.8	3027.6	2182.5	1265.3	586.1	91.0	11.0	11.0	15.0
37°	4361.9	4224.9	3844.8	3204.7	2310.5	1353.3	620.1	91.0	10.0	11.0	15.0
38°	4422.9	4308.9	3983.8	3333.7	2434.5	1422.3	647.1	89.0	9.0	10.0	14.0
39°	4448.9	4355.9	4068.8	3442.7	2527.5	1482.3	667.1	87.0	8.0	10.0	14.0
40°	4444.9	4363.9	4116.9	3517.7	2602.5	1523.3	678.1	84.0	7.0	9.0	14.0
41°	4421.9	4351.9	4141.9	3581.7	2647.5	1551.3	681.1	81.0	6.0	9.0	13.0
42°	4395.9	4331.9	4149.9	3615.7	2676.6	1560.3	673.1	77.0	6.0	8.0	13.0
43°	4368.9	4309.9	4149.9	3626.8	2683.6	1554.3	660.1	70.0	5.0	8.0	13.0
44°	4346.9	4290.9	4136.9	3623.8	2668.6	1531.3	636.1	62.0	4.0	8.0	13.0
45°	4320.9	4265.9	4119.9	3604.7	2639.5	1492.3	606.1	55.0	3.0	7.0	13.0
46°	4274.9	4231.9	4089.8	3565.7	2593.5	1438.3	568.1	50.0	2.0	7.0	12.0
47°	4185.9	4148.9	4031.8	3507.7	2532.5	1374.3	529.1	45.0	2.0	7.0	12.0
48°	4006.8	4005.8	3915.8	3399.7	2435.5	1294.3	488.1	40.0	2.0	7.0	12.0
49°	3833.8	3815.8	3703.8	3209.7	2296.5	1198.2	445.1	36.0	1.0	7.0	12.0
50°	3738.8	3699.8	3515.7	2985.6	2118.4	1065.2	399.1	30.0	1.0	6.0	12.0
51°	3639.8	3583.7	3366.7	2783.6	1906.4	937.2	349.1	24.0	1.0	6.0	11.0
52°	3460.7	3407.7	3164.7	2590.5	1700.4	806.2	301.1	20.0	1.0	6.0	12.0
53°	3267.7	3191.7	2927.6	2378.5	1519.3	690.1	252.1	17.0	1.0	6.0	11.0
54°	3024.6	2990.6	2687.6	2118.4	1307.3	578.1	207.0	14.0	1.0	6.0	11.0
55°	2795.6	2745.6	2430.5	1852.4	1115.2	474.1	173.0	11.0	1.0	6.0	11.0
56°	2503.5	2428.5	2133.4	1608.3	920.2	382.1	146.0	9.0	1.0	6.0	11.0
57°	2155.4	2075.4	1842.4	1337.3	722.1	291.1	122.0	7.0	1.0	6.0	11.0
58°	1823.4	1754.4	1504.3	1032.2	544.1	202.0	101.0	5.0	1.0	5.0	11.0
59°	1575.3	1499.3	1251.3	794.2	378.1	149.0	76.0	4.0	1.0	6.0	11.0
60°	1364.3	1266.3	1007.2	615.1	270.1	107.0	56.0	2.0	2.0	6.0	11.0
62.5°	786.2	694.1	481.1	250.1	111.0	55.0	27.0	1.0	2.0	6.0	11.0
65°	199.0	177.0	115.0	54.0	31.0	19.0	10.0	1.0	2.0	5.0	10.0



TEST NUMBER: P1310378

CATALOG NUMBER: LDSQA3D13R359035DE010 3LSQCA45R 1MW

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
67.5°	7.0	7.0	7.0	6.0	5.0	4.0	2.0	1.0	2.0	5.0	10.0
70°	3.0	3.0	3.0	2.0	2.0	1.0	1.0	1.0	2.0	5.0	9.0
72.5°	2.0	2.0	2.0	2.0	1.0	1.0	1.0	1.0	3.0	5.0	8.0
75°	2.0	2.0	2.0	2.0	1.0	1.0	1.0	1.0	3.0	5.0	8.0
77.5°	2.0	2.0	1.0	1.0	1.0	1.0	1.0	1.0	3.0	4.0	7.0
80°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	3.0	4.0	6.0
82.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	3.0	4.0	5.0
85°	0.0	0.0	0.0	0.0	0.0	1.0	0.0	1.0	3.0	4.0	4.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	1.0	3.0	4.0	3.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1310378

CATALOG NUMBER: LDSQA3D13R359035DE010 3LSQCA45R 1MW

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
0°	51.0	51.0	51.0
2.5°	48.0	48.0	48.0
5°	45.0	45.0	44.0
7.5°	42.0	41.0	41.0
10°	38.0	38.0	38.0
12.5°	35.0	35.0	35.0
15°	32.0	33.0	33.0
17.5°	29.0	31.0	31.0
20°	27.0	29.0	30.0
22.5°	25.0	27.0	28.0
25°	24.0	26.0	27.0
27.5°	22.0	25.0	27.0
30°	21.0	24.0	26.0
31°	21.0	24.0	25.0
32°	20.0	24.0	25.0
33°	20.0	24.0	25.0
34°	20.0	23.0	25.0
35°	19.0	23.0	24.0
36°	19.0	23.0	24.0
37°	19.0	23.0	25.0
38°	19.0	23.0	24.0
39°	18.0	23.0	24.0
40°	18.0	23.0	24.0
41°	18.0	23.0	24.0
42°	18.0	23.0	24.0
43°	18.0	23.0	24.0
44°	18.0	22.0	24.0
45°	18.0	22.0	24.0
46°	18.0	23.0	24.0
47°	18.0	23.0	25.0
48°	18.0	22.0	24.0
49°	17.0	22.0	24.0
50°	17.0	22.0	24.0
51°	17.0	23.0	25.0
52°	17.0	23.0	25.0
53°	17.0	23.0	25.0
54°	17.0	23.0	24.0
55°	17.0	23.0	25.0
56°	17.0	23.0	24.0
57°	17.0	23.0	24.0
58°	17.0	22.0	24.0
59°	17.0	22.0	24.0
60°	17.0	22.0	24.0
62.5°	16.0	22.0	24.0
65°	16.0	21.0	23.0



TEST NUMBER: P1310378
CATALOG NUMBER: LDSQA3D13R359035DE010 3LSQCA45R 1MW

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
67.5°	15.0	21.0	22.0
70°	14.0	20.0	21.0
72.5°	13.0	19.0	20.0
75°	12.0	17.0	18.0
77.5°	10.0	15.0	17.0
80°	9.0	13.0	14.0
82.5°	7.0	11.0	12.0
85°	5.0	8.0	8.0
87.5°	2.0	4.0	4.0
90°	0.0	0.0	0.0

(END OF REPORT)