

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1310907

Luminaire Tested: LDSQA3D02R089040DE010 3LSQCDR1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1310907
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2408-211-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R089040DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R08 optic, 4000K CCT AND, 90CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 259.9 lumens
Efficiency: N/A
Efficacy: 53.0 lumens/watt
Spacing Criteria (0/90/45): 0.16 / 0.16 / 0.16
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 4.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1310907

CATALOG NUMBER: LDSQA3D02R089040DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1310907

CATALOG NUMBER: LDSQA3D02R089040DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	116	114	113	111	114	112	111	110	108	107	106	105	104	103	101	101	100	99	99	99
2	113	111	108	106	111	109	107	105	106	104	103	103	102	101	101	100	99	97	97	97
3	111	108	105	103	109	106	104	102	104	102	100	102	100	99	100	98	97	96	96	96
4	109	105	102	100	108	104	101	99	102	100	98	100	99	97	99	97	96	95	95	95
5	107	103	100	98	106	102	99	97	101	98	97	99	97	96	98	96	95	94	94	94
6	105	101	98	96	104	100	98	96	99	97	95	98	96	95	97	95	94	93	93	93
7	104	100	97	95	103	99	96	94	98	96	94	97	95	94	96	94	93	92	92	92
8	103	98	95	93	102	98	95	93	97	95	93	96	94	93	95	94	92	92	92	92
9	101	97	94	92	101	97	94	92	96	94	92	95	93	92	95	93	92	91	91	91
10	100	96	93	91	100	96	93	91	95	93	91	94	92	91	94	92	91	90	90	90

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1158180
5°	482959
10°	77716
15°	22269
20°	7514
25°	3306
30°	1830
35°	1282
40°	1147
45°	755
50°	536
55°	300
60°	344
65°	408
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 755 cd/sqm

TEST NUMBER: P1310907

CATALOG NUMBER: LDSQA3D02R089040DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.6	77.2
10°-20°	42.0	16.2
20°-30°	9.1	3.5
30°-40°	4.0	1.5
40°-50°	2.4	0.9
50°-60°	1.0	0.4
60°-70°	0.9	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	251.7	96.8
0°-40°	255.6	98.3
0°-60°	259.1	99.7
0°-90°	259.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	259.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6725	
5°	2794	201
15°	125	42
25°	17	9
35°	6	4
45°	3	2
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1310907

CATALOG NUMBER: LDSQA3D02R089040DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	6724.9
2.5°	5621.0
5°	2793.6
7.5°	1041.4
10°	444.4
12.5°	229.4
15°	124.9
17.5°	70.7
20°	41.0
22.5°	26.6
25°	17.4
27.5°	13.3
30°	9.2
32.5°	7.2
35°	6.1
37.5°	5.1
40°	5.1
42.5°	4.1
45°	3.1
47.5°	2.0
50°	2.0
52.5°	1.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)