

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1310983

Luminaire Tested: LDSQA3D02R309040DE010 3LSQCA30R 1MW

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1310983  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-62)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D02R309040DE010 3LSQCA30R 1MW  
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , 3LSQCA30R 1MW TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 287.0 lumens  
Efficiency: N/A  
Efficacy: 79.7 lumens/watt  
Spacing Criteria (0/90/45): 2.53 / 0.5 / 1.28  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1310983  
CATALOG NUMBER: LDSQA3D02R309040DE010 3LSQCA30R 1MW

### Luminous Intensity Polar Plot



— 0°-180°    - - - 45°-225°    - - - - 90°-270°



TEST NUMBER: P1310983

CATALOG NUMBER: LDSQA3D02R309040DE010 3LSQCA30R 1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	96	95	93	92
2	106	100	95	92	103	98	94	90	95	92	88	92	89	87	89	87	85	89	87	85	83
3	99	92	86	81	97	90	85	81	87	83	79	85	81	78	83	79	77	83	79	77	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	76	73	69	68
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	71	66	63	61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	65	61	57	55
7	76	65	58	53	74	64	57	53	63	57	52	61	56	52	60	55	52	60	55	52	50
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	56	51	47	45
9	67	55	48	43	65	55	48	43	53	47	43	52	47	43	52	46	43	52	46	43	41
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	48	43	39	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	2342	2342	2342	2342	2342
5°	7071	4720	2230	1003	813
10°	40957	10003	1749	455	315
15°	133224	22680	1212	89	53
20°	208458	35079	770	0	0
25°	229343	34281	399	0	0
30°	224002	24719	159	0	0
35°	216195	14065	63	0	0
40°	184375	5958	0	0	0
45°	108214	2241	73	0	73
50°	26284	429	80	80	214
55°	2282	0	150	240	300
60°	103	0	172	276	448
65°	122	122	326	326	530
70°	151	151	403	403	504
75°	0	200	532	532	532
80°	0	298	793	496	496
85°	0	593	1581	593	593

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 108214 cd/sqm



TEST NUMBER: P1310983

CATALOG NUMBER: LDSQA3D02R309040DE010 3LSQCA30R 1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2.5	0.9
10°-20°	39.4	13.7
20°-30°	100.2	34.9
30°-40°	99.9	34.8
40°-50°	40.5	14.1
50°-60°	2.8	1.0
60°-70°	0.6	0.2
70°-80°	0.6	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	142.2	49.5
0°-40°	242.1	84.3
0°-60°	285.4	99.4
0°-90°	287.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	287.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	14	14	14	14	14	
5°	41	27	13	6	5	9
15°	747	127	7	0	0	217
25°	1207	180	2	0	0	545
35°	1028	67	0	0	0	630
45°	444	9	0	0	0	339
55°	8	0	0	1	1	20
65°	0	0	1	1	1	0
75°	0	0	1	1	1	0
85°	0	0	1	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P1310983

CATALOG NUMBER: LDSQA3D02R309040DE010 3LSQCA30R 1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	67.5°
0°	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.6
2.5°	22.6	22.8	22.8	22.3	22.0	22.0	21.2	21.0	20.2	19.4	16.8
5°	40.9	40.1	39.1	39.1	36.7	35.4	33.6	31.5	29.9	27.3	19.4
7.5°	92.8	86.5	84.7	82.3	73.4	66.3	58.2	51.1	44.6	39.1	21.5
10°	234.2	221.9	211.6	190.9	165.0	140.0	117.0	90.2	71.9	57.2	23.1
12.5°	471.8	455.3	435.6	397.8	349.3	287.2	232.1	173.3	121.7	84.2	23.6
15°	747.2	719.1	688.4	640.4	561.0	471.8	372.4	278.8	195.4	127.2	23.1
17.5°	971.6	960.6	915.3	849.7	752.4	637.5	515.1	387.1	263.6	166.5	21.5
20°	1137.4	1129.8	1075.0	1005.2	895.6	763.9	608.4	454.7	311.0	191.4	19.1
22.5°	1217.4	1216.1	1176.5	1105.1	989.0	839.7	668.5	493.8	325.7	194.9	16.0
25°	1206.9	1211.6	1189.1	1136.1	1024.6	870.9	686.3	493.8	315.0	180.4	13.4
27.5°	1159.2	1162.3	1148.1	1107.5	1003.6	848.4	661.4	462.1	283.8	155.0	11.0
30°	1126.4	1127.7	1110.1	1066.6	956.4	797.0	602.7	403.3	236.6	124.3	8.1
32.5°	1086.5	1086.2	1065.8	1016.0	894.5	724.9	528.2	333.3	181.7	94.4	4.7
35°	1028.3	1021.7	993.9	936.5	802.2	627.8	433.0	253.9	130.9	66.9	2.9
37.5°	948.3	931.3	891.9	815.1	672.7	492.2	321.0	178.3	89.4	44.3	1.8
40°	820.1	802.0	748.5	655.1	508.8	354.3	216.4	116.2	56.4	26.5	1.0
42.5°	643.0	630.7	558.6	465.5	335.9	226.1	130.1	68.7	31.7	15.2	0.3
45°	444.3	428.3	371.6	292.7	201.7	125.4	72.9	35.9	18.1	9.2	0.0
47.5°	245.2	225.5	192.8	151.6	101.5	65.8	36.7	19.4	10.2	4.5	0.0
50°	98.1	97.3	77.4	55.1	38.8	29.9	18.4	10.5	5.2	1.6	0.3
52.5°	34.4	34.4	29.6	24.1	18.9	13.6	9.2	5.0	1.8	0.5	0.3
55°	7.6	8.4	7.9	7.3	7.1	6.0	3.9	1.8	0.5	0.0	0.3
57.5°	0.8	0.8	0.8	1.0	1.3	1.3	1.0	0.5	0.0	0.0	0.3
60°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.0	0.0	0.0	0.5
62.5°	0.3	0.3	0.3	0.3	0.3	0.0	0.0	0.0	0.3	0.3	0.5
65°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.5
67.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.5
70°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.8
72.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.8
75°	0.0	0.0	0.3	0.3	0.0	0.3	0.3	0.3	0.3	0.3	0.8
77.5°	0.0	0.0	0.0	0.0	0.3	0.3	0.3	0.3	0.3	0.3	0.5
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.3	0.3	0.3	0.5
82.5°	0.0	0.0	0.0	0.0	0.0	0.3	0.3	0.3	0.3	0.3	0.5
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.3	0.3	0.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.3	0.3	0.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1310983

CATALOG NUMBER: LDSQA3D02R309040DE010 3LSQCA30R 1MW

**CANDELA DISTRIBUTION (continued):**

	90°	112.5°	135°	157.5°	180°
0°	13.6	13.6	13.6	13.6	13.6
2.5°	13.6	10.8	8.9	7.9	7.6
5°	12.9	8.1	5.8	5.0	4.7
7.5°	11.5	6.0	3.9	3.1	2.9
10°	10.0	4.5	2.6	1.8	1.8
12.5°	8.4	3.4	1.6	0.8	0.5
15°	6.8	2.1	0.5	0.3	0.3
17.5°	5.2	1.3	0.0	0.0	0.0
20°	4.2	0.5	0.0	0.0	0.0
22.5°	3.1	0.3	0.0	0.0	0.0
25°	2.1	0.0	0.0	0.0	0.0
27.5°	1.3	0.0	0.0	0.0	0.0
30°	0.8	0.0	0.0	0.0	0.0
32.5°	0.3	0.0	0.0	0.0	0.0
35°	0.3	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.3	0.0	0.0	0.3	0.3
47.5°	0.3	0.3	0.3	0.5	0.5
50°	0.3	0.3	0.3	0.5	0.8
52.5°	0.5	0.3	0.5	0.8	0.8
55°	0.5	0.5	0.8	1.0	1.0
57.5°	0.5	0.5	0.8	1.0	1.0
60°	0.5	0.5	0.8	1.0	1.3
62.5°	0.8	0.8	0.8	1.0	1.0
65°	0.8	0.8	0.8	1.0	1.3
67.5°	0.8	0.8	0.8	1.0	1.3
70°	0.8	0.8	0.8	1.0	1.0
72.5°	1.0	0.8	0.8	1.0	1.0
75°	0.8	0.8	0.8	0.8	0.8
77.5°	0.8	0.8	0.5	0.8	0.8
80°	0.8	0.5	0.5	0.5	0.5
82.5°	0.8	0.5	0.5	0.5	0.5
85°	0.8	0.5	0.3	0.3	0.3
87.5°	0.8	0.5	0.3	0.3	0.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)