

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1311008

Luminaire Tested: LDSQA3D02R359040DE010 3LSQPHR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1311008
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R359040DE010 3LSQPHR1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 90CRI , 3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 304.0 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1311008
CATALOG NUMBER: LDSQA3D02R359040DE010 3LSQPHR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1311008
 CATALOG NUMBER: LDSQA3D02R359040DE010 3LSQPHR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	172498	172498	172498
5°	169527	169164	168801
10°	155380	150694	147039
15°	111258	107710	106408
20°	51592	53370	55239
25°	12238	17406	18167
30°	3599	4117	4634
35°	820	1325	1219
40°	180	360	225
45°	73	73	73
50°	80	0	80
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 52.5°
 Luminance: 85 cd/sqm



TEST NUMBER: P1311008

CATALOG NUMBER: LDSQA3D02R359040DE010 3LSQPHR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.9	29.6
10°-20°	160.8	52.9
20°-30°	48.4	15.9
30°-40°	4.6	1.5
40°-50°	0.3	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	299.0	98.4
0°-40°	303.7	99.9
0°-60°	304.0	100.0
0°-90°	304.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	304.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1002	1002	1002	1002	1002	
5°	981	980	978	977	976	91
15°	624	619	604	602	597	165
25°	64	71	92	96	96	41
35°	4	5	6	7	6	4
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1311008
 CATALOG NUMBER: LDSQA3D02R359040DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1001.6	1001.6	1001.6	1001.6	1001.6
1°	1001.1	1001.1	1000.5	1000.5	999.5
2°	998.7	999.0	997.9	997.6	996.9
3°	995.0	994.2	994.2	993.7	993.2
4°	989.3	987.7	987.2	987.4	986.4
5°	980.6	980.4	978.5	977.2	976.4
6°	971.2	969.4	965.4	962.0	961.2
7°	957.1	953.1	949.7	942.7	941.6
8°	939.8	933.5	926.2	916.2	915.7
9°	918.6	908.4	898.1	884.8	880.1
10°	888.5	879.0	861.7	850.0	840.8
11°	851.0	839.2	819.1	804.9	797.3
12°	808.6	797.6	774.0	761.2	750.5
13°	754.1	745.0	723.0	708.8	700.4
14°	691.0	684.2	663.3	657.0	654.1
15°	624.0	619.3	604.1	601.5	596.8
17.5°	459.3	451.4	442.8	444.4	445.9
20°	281.5	292.5	291.2	296.9	301.4
22.5°	140.4	154.5	171.0	180.9	185.9
25°	64.4	71.0	91.6	95.6	95.6
27.5°	32.5	34.0	43.2	44.0	46.1
30°	18.1	19.4	20.7	23.0	23.3
32.5°	9.2	10.7	11.3	12.6	12.0
35°	3.9	5.2	6.3	6.8	5.8
37.5°	1.8	2.4	3.4	3.1	2.4
40°	0.8	1.0	1.6	1.3	1.0
42.5°	0.5	0.5	0.8	0.5	0.5
45°	0.3	0.3	0.3	0.3	0.3
47.5°	0.3	0.3	0.0	0.3	0.3
50°	0.3	0.0	0.0	0.0	0.3
52.5°	0.3	0.0	0.0	0.0	0.3
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1311008
CATALOG NUMBER: LDSQA3D02R359040DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)