

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1311413

Luminaire Tested: LDSQA3D10R129040DE010 3LSQPHRLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1311413
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D10R129040DE010 3LSQPHRLD1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 4000K CCT AND, 90CRI , 3LSQPHRLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 949.0 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1311413

CATALOG NUMBER: LDSQA3D10R129040DE010 3LSQPHRLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1311413

CATALOG NUMBER: LDSQA3D10R129040DE010 3LSQPHRLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	100	99	98	98	98	98	98	98	98	98	98	98
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	98	98	98	98	98	98	98	98	98	98	98	97
3	110	107	104	102	109	105	103	101	103	101	99	101	99	98	99	98	96	96	96	96	96	96	96	96	96	96	96	96	95
4	108	104	101	98	107	103	100	98	101	99	97	99	97	96	98	96	95	95	95	95	95	95	95	95	95	95	95	95	94
5	106	102	98	96	105	101	98	96	99	97	95	98	96	94	97	95	93	93	93	93	93	93	93	93	93	93	93	93	92
6	104	99	96	94	103	99	96	94	98	95	93	96	94	93	95	93	92	92	92	92	92	92	92	92	92	92	92	92	91
7	102	98	94	92	101	97	94	92	96	93	92	95	93	91	94	92	91	91	91	91	91	91	91	91	91	91	91	91	90
8	101	96	93	91	100	95	93	90	95	92	90	94	92	90	93	91	90	90	90	90	90	90	90	90	90	90	90	90	89
9	99	94	91	89	98	94	91	89	93	91	89	93	90	89	92	90	88	88	88	88	88	88	88	88	88	88	88	88	88
10	98	93	90	88	97	93	90	88	92	90	88	91	89	88	91	89	87	87	87	87	87	87	87	87	87	87	87	87	87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2407845
5°	1555786
10°	438965
15°	124113
20°	51904
25°	22974
30°	11733
35°	6202
40°	2653
45°	706
50°	777
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 777 cd/sqm

TEST NUMBER: P1311413

CATALOG NUMBER: LDSQA3D10R129040DE010 3LSQPHRLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	634.1	66.8
10°-20°	230.0	24.2
20°-30°	61.6	6.5
30°-40°	19.4	2.0
40°-50°	3.6	0.4
50°-60°	0.3	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	925.7	97.5
0°-40°	945.1	99.6
0°-60°	949.0	100.0
0°-90°	949.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	949.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13981	
5°	8999	634
15°	696	230
25°	121	62
35°	30	19
45°	3	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1311413

CATALOG NUMBER: LDSQA3D10R129040DE010 3LSQPHRLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	13981.0
1°	13745.1
2°	13081.4
3°	11945.8
4°	10535.9
5°	8999.2
6°	7397.6
7°	5964.1
8°	4589.6
9°	3415.6
10°	2510.1
11°	1849.4
12°	1392.2
13°	1079.5
14°	855.4
15°	696.1
17.5°	442.4
20°	283.2
22.5°	182.9
25°	120.9
27.5°	82.6
30°	59.0
32.5°	41.3
35°	29.5
37.5°	20.6
40°	11.8
42.5°	5.9
45°	2.9
47.5°	2.9
50°	2.9
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1311413

CATALOG NUMBER: LDSQA3D10R129040DE010 3LSQPHRLD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)