

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1312496

Luminaire Tested: LDSQA3D13R129050DE010 3LSQCDR1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1312496
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D13R129050DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R12 optic, 5000K CCT AND, 90CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1187.0 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1312496

CATALOG NUMBER: LDSQA3D13R129050DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1312496

CATALOG NUMBER: LDSQA3D13R129050DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98	98	98
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	97	97	97
3	110	107	104	102	109	105	103	101	103	101	99	101	99	98	99	98	96	95	95	95
4	108	104	101	98	107	103	100	98	101	99	97	99	97	96	98	96	95	94	94	94
5	106	102	98	96	105	101	98	96	99	97	95	98	96	94	97	95	93	92	92	92
6	104	99	96	94	103	99	96	94	98	95	93	96	94	93	95	93	92	91	91	91
7	102	98	94	92	101	97	94	92	96	93	92	95	93	91	94	92	91	90	90	90
8	101	96	93	91	100	95	93	90	95	92	90	94	92	90	93	91	90	89	89	89
9	99	94	91	89	98	94	91	89	93	91	89	93	90	89	92	90	88	88	88	88
10	98	93	90	88	97	93	90	88	92	90	88	91	89	88	91	89	87	87	87	87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3011709
5°	1945960
10°	549052
15°	155244
20°	64916
25°	28751
30°	14676
35°	7758
40°	3327
45°	901
50°	991
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 991 cd/sqm

TEST NUMBER: P1312496

CATALOG NUMBER: LDSQA3D13R129050DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	793.1	66.8
10°-20°	287.7	24.2
20°-30°	77.0	6.5
30°-40°	24.2	2.0
40°-50°	4.6	0.4
50°-60°	0.4	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1157.8	97.5
0°-40°	1182.1	99.6
0°-60°	1187.0	100.0
0°-90°	1187.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1187.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17487	
5°	11256	793
15°	871	288
25°	151	77
35°	37	24
45°	4	5
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1312496

CATALOG NUMBER: LDSQA3D13R129050DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	17487.3
1°	17192.2
2°	16362.1
3°	14941.7
4°	13178.2
5°	11256.1
6°	9252.8
7°	7459.8
8°	5740.6
9°	4272.2
10°	3139.6
11°	2313.2
12°	1741.4
13°	1350.3
14°	1069.9
15°	870.7
17.5°	553.4
20°	354.2
22.5°	228.7
25°	151.3
27.5°	103.3
30°	73.8
32.5°	51.7
35°	36.9
37.5°	25.8
40°	14.8
42.5°	7.4
45°	3.7
47.5°	3.7
50°	3.7
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1312496

CATALOG NUMBER: LDSQA3D13R129050DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)