

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1310987

Luminaire Tested: LDSQA3D02R309040DE010 3LSQCDR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1310987
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R309040DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 337.0 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1310987
CATALOG NUMBER: LDSQA3D02R309040DE010 3LSQCDR1MB

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270°



TEST NUMBER: P1310987
 CATALOG NUMBER: LDSQA3D02R309040DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	99	99	99	97
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	95	94	94	94
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	95	94	92	95	94	92	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	93	91	89	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	87	91	89	87	91	89	87	86
6	99	93	89	86	98	92	89	86	91	88	85	90	87	85	89	86	84	89	86	84	83
7	96	90	86	83	95	90	86	83	89	85	83	87	85	82	87	84	82	87	84	82	81
8	94	88	83	81	93	87	83	81	86	83	80	85	82	80	84	82	80	84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	82	80	78	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	80	78	76	80	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	224923	224923	224923
5°	219437	219714	220941
10°	187418	186544	185442
15°	115662	114307	114735
20°	43711	43949	43913
25°	13454	14746	14043
30°	5429	6881	5628
35°	1598	2922	1661
40°	652	1169	652
45°	122	390	122
50°	0	80	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 390 cd/sqm



TEST NUMBER: P1310987

CATALOG NUMBER: LDSQA3D02R309040DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.2	34.2
10°-20°	170.6	50.6
20°-30°	42.3	12.6
30°-40°	7.9	2.4
40°-50°	1.0	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	328.1	97.3
0°-40°	336.0	99.7
0°-60°	337.0	100.0
0°-90°	337.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	337.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1306	1306	1306	1306	1306	
5°	1269	1269	1271	1273	1278	115
15°	649	642	641	646	644	171
25°	71	76	78	77	74	41
35°	8	10	14	10	8	6
45°	0	1	2	1	0	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1310987
 CATALOG NUMBER: LDSQA3D02R309040DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1306.0	1306.0	1306.0	1306.0	1306.0
1°	1306.6	1305.5	1305.5	1303.9	1306.8
2°	1301.8	1300.8	1302.6	1301.3	1305.0
3°	1294.8	1293.5	1296.1	1296.9	1298.7
4°	1284.3	1283.2	1286.1	1287.7	1292.7
5°	1269.3	1268.8	1270.9	1273.0	1278.0
6°	1248.9	1248.1	1249.4	1252.0	1255.2
7°	1219.3	1217.7	1218.8	1219.3	1220.1
8°	1181.8	1179.4	1178.1	1181.0	1182.6
9°	1133.6	1131.0	1128.1	1127.0	1130.7
10°	1071.7	1067.8	1066.7	1064.1	1060.4
11°	999.9	996.8	996.0	991.3	989.2
12°	917.6	916.0	917.9	915.0	913.9
13°	838.7	828.8	827.4	821.9	819.1
14°	745.4	736.2	736.0	733.1	737.0
15°	648.7	642.4	641.1	646.1	643.5
17.5°	413.6	417.8	416.7	414.1	409.7
20°	238.5	235.6	239.8	240.9	239.6
22.5°	127.1	128.2	129.0	132.1	134.2
25°	70.8	75.5	77.6	77.3	73.9
27.5°	44.0	46.9	50.8	48.2	45.3
30°	27.3	29.6	34.6	29.9	28.3
32.5°	14.7	18.6	22.3	18.6	15.2
35°	7.6	10.0	13.9	10.2	7.9
37.5°	5.0	5.8	8.9	5.8	5.0
40°	2.9	3.7	5.2	3.7	2.9
42.5°	1.3	2.1	2.9	2.1	1.3
45°	0.5	0.8	1.6	1.0	0.5
47.5°	0.0	0.3	0.8	0.3	0.0
50°	0.0	0.0	0.3	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1310987
CATALOG NUMBER: LDSQA3D02R309040DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)