

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1312188

Luminaire Tested: LDSQA3D05R129050DE010 3LSQPHRLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1312188
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R129050DE010 3LSQPHRLP1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 5000K CCT AND, 90CRI , 3LSQPHRLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 670.0 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1312188

CATALOG NUMBER: LDSQA3D05R129050DE010 3LSQPHRLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1312188

CATALOG NUMBER: LDSQA3D05R129050DE010 3LSQPHRLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98			
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	97			
3	110	107	104	102	109	105	103	101	103	101	99	101	99	98	99	98	96	95			
4	108	104	101	98	107	103	100	98	101	99	97	99	97	96	98	96	95	94			
5	106	102	98	96	105	101	98	96	99	97	95	98	96	94	97	95	93	92			
6	104	99	96	94	103	99	96	94	98	95	93	96	94	93	95	93	92	91			
7	102	98	94	92	101	97	94	92	96	93	92	95	93	91	94	92	91	90			
8	101	96	93	91	100	95	93	90	95	92	90	94	92	90	93	91	90	89			
9	99	94	91	89	98	94	91	89	93	91	89	93	90	89	92	90	88	88			
10	98	93	90	88	97	93	90	88	92	90	88	91	89	88	91	89	87	87			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1699958
5°	1098396
10°	309904
15°	87633
20°	36637
25°	16228
30°	8273
35°	4373
40°	1866
45°	511
50°	563
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 563 cd/sqm

TEST NUMBER: P1312188

CATALOG NUMBER: LDSQA3D05R129050DE010 3LSQPHRLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	447.6	66.8
10°-20°	162.4	24.2
20°-30°	43.5	6.5
30°-40°	13.7	2.0
40°-50°	2.6	0.4
50°-60°	0.2	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	653.5	97.5
0°-40°	667.2	99.6
0°-60°	670.0	100.0
0°-90°	670.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	670.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9871	
5°	6354	448
15°	492	162
25°	85	43
35°	21	14
45°	2	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1312188

CATALOG NUMBER: LDSQA3D05R129050DE010 3LSQPHRLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	9870.7
1°	9704.1
2°	9235.6
3°	8433.8
4°	7438.4
5°	6353.5
6°	5222.7
7°	4210.7
8°	3240.3
9°	2411.4
10°	1772.1
11°	1305.7
12°	982.9
13°	762.2
14°	603.9
15°	491.5
17.5°	312.4
20°	199.9
22.5°	129.1
25°	85.4
27.5°	58.3
30°	41.6
32.5°	29.2
35°	20.8
37.5°	14.6
40°	8.3
42.5°	4.2
45°	2.1
47.5°	2.1
50°	2.1
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1312188

CATALOG NUMBER: LDSQA3D05R129050DE010 3LSQPHRLP1MW

CANDELA DISTRIBUTION (continued):



(END OF REPORT)