

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1312305

Luminaire Tested: LDSQA3D05R559050DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1312305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R559050DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 713.0 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.81
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1312305
CATALOG NUMBER: LDSQA3D05R559050DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1312305

CATALOG NUMBER: LDSQA3D05R559050DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	86	86	86	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	81	81	81	80
5	96	88	83	79	94	87	82	79	85	81	78	84	80	77	82	79	77	77	77	77	75
6	91	83	78	74	90	83	78	74	81	77	74	80	76	73	79	75	73	73	73	73	71
7	87	79	74	70	86	79	73	70	77	73	69	76	72	69	75	72	69	69	69	69	67
8	84	75	70	66	83	75	70	66	74	69	66	73	69	65	72	68	65	65	65	65	64
9	80	72	66	63	79	71	66	63	70	66	62	69	65	62	69	65	62	62	62	62	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	59	59	59	58

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	161510	161510	161510
5°	159672	159206	158341
10°	167360	165349	164194
15°	164587	162822	162233
20°	149901	150506	150011
25°	120268	122130	120268
30°	69026	70776	71313
35°	19679	23716	20268
40°	5036	7262	5171
45°	536	2533	390
50°	0	429	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 2533 cd/sqm



TEST NUMBER: P1312305

CATALOG NUMBER: LDSQA3D05R559050DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.0	12.5
10°-20°	254.1	35.6
20°-30°	279.9	39.3
30°-40°	83.5	11.7
40°-50°	6.4	0.9
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	623.0	87.4
0°-40°	706.5	99.1
0°-60°	713.0	100.0
0°-90°	713.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	713.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	938	938	938	938	938	
5°	924	922	921	917	916	90
15°	923	916	913	909	910	256
25°	633	633	643	642	633	277
35°	94	100	113	103	96	77
45°	2	6	10	6	2	4
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1312305
 CATALOG NUMBER: LDSQA3D05R559050DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	937.8	937.8	937.8	937.8	937.8
1°	937.3	937.3	936.2	935.7	937.3
2°	934.6	934.6	931.8	931.3	932.9
3°	928.5	928.0	925.8	924.2	925.2
4°	923.6	922.5	920.9	918.1	918.7
5°	923.6	922.0	920.9	917.0	915.9
6°	928.0	926.9	924.7	920.9	919.8
7°	935.7	933.5	931.3	926.3	925.2
8°	943.9	942.2	937.8	932.9	930.7
9°	952.1	948.2	942.8	937.8	937.3
10°	957.0	951.5	945.5	939.5	938.9
11°	956.5	951.5	944.4	938.9	938.4
12°	954.3	947.1	941.1	934.6	935.1
13°	946.6	940.0	934.0	929.1	928.0
14°	936.2	930.2	924.7	919.8	920.3
15°	923.1	916.5	913.2	909.4	909.9
17.5°	876.5	874.9	876.5	872.1	873.8
20°	817.9	816.3	821.2	819.0	818.5
22.5°	736.4	738.6	747.9	745.1	740.2
25°	632.9	632.9	642.7	641.7	632.9
27.5°	498.2	502.0	508.1	510.8	504.2
30°	347.1	355.9	355.9	361.3	358.6
32.5°	193.8	212.4	216.8	219.5	208.6
35°	93.6	99.6	112.8	102.9	96.4
37.5°	44.9	47.6	60.8	49.3	46.0
40°	22.4	25.7	32.3	26.8	23.0
42.5°	9.3	13.7	17.0	13.7	9.3
45°	2.2	5.5	10.4	5.5	1.6
47.5°	0.0	0.5	4.9	1.1	0.0
50°	0.0	0.0	1.6	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1312305
CATALOG NUMBER: LDSQA3D05R559050DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)