

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1313198

Luminaire Tested: LDSQA3D02R359727DE010 3LSQCA45R 1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1313198  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-77)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D02R359727DE010 3LSQCA45R 1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , 3LSQCA45R 1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 226.0 lumens  
Efficiency: N/A  
Efficacy: 62.8 lumens/watt  
Spacing Criteria (0/90/45): 4.01 / 0.66 / 1.41  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1313198  
CATALOG NUMBER: LDSQA3D02R359727DE010 3LSQCA45R 1MW

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P1313198

CATALOG NUMBER: LDSQA3D02R359727DE010 3LSQCA45R 1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	99	107	104	100	97	100	97	94	96	93	91	92	90	89	89	89	89	87
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	75	75	73
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	67	63	63	63	63	61
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	52	52	52	52	50
5	75	62	52	46	73	61	52	45	58	51	45	56	50	44	55	49	44	44	44	44	42
6	68	54	45	38	66	53	44	38	51	43	38	50	43	37	48	42	37	37	37	37	35
7	62	48	38	32	60	47	38	32	45	37	32	44	37	31	42	36	31	31	31	31	29
8	57	42	33	27	55	41	33	27	40	32	27	39	32	26	38	31	26	26	26	26	24
9	52	38	29	23	50	37	29	23	36	28	23	35	28	22	34	27	22	22	22	22	20
10	48	34	25	19	46	33	25	19	32	25	19	31	24	19	30	24	19	19	19	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	1791	1791	1791	1791	1791
5°	1936	1902	1763	1591	1556
10°	2029	1854	1574	1364	1364
15°	2906	1819	1266	1159	1195
20°	7294	1943	1008	1008	1118
25°	33844	2489	779	931	1045
30°	102893	3361	616	855	1054
35°	173894	3911	505	820	1030
40°	203822	3844	405	832	1102
45°	214649	2728	341	901	1193
50°	204324	1634	322	938	1313
55°	171209	661	360	1051	1531
60°	95859	138	413	1206	1688
65°	16545	82	408	1345	1915
70°	302	101	504	1460	2165
75°	266	133	665	1597	2462
80°	198	198	793	1785	2876
85°	0	395	1581	1976	3162

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 46°  
 Luminance: 216190 cd/sqm



TEST NUMBER: P1313198

CATALOG NUMBER: LDSQA3D02R359727DE010 3LSQCA45R 1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.9	0.4
10°-20°	2.7	1.2
20°-30°	13.9	6.1
30°-40°	59.9	26.5
40°-50°	85.4	37.8
50°-60°	52.9	23.4
60°-70°	8.0	3.6
70°-80°	1.5	0.7
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	17.5	7.7
0°-40°	77.4	34.2
0°-60°	215.7	95.4
0°-90°	226.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	226.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	10	10	10	10	10	
5°	11	11	10	9	9	1
15°	16	10	7	6	7	6
25°	178	13	4	5	6	107
35°	827	19	2	4	5	497
45°	881	11	1	4	5	666
55°	570	2	1	4	5	486
65°	41	0	1	3	5	83
75°	0	0	1	2	4	0
85°	0	0	1	1	2	0
90°	0	0	0	0	0	



TEST NUMBER: P1313198

CATALOG NUMBER: LDSQA3D02R359727DE010 3LSQCA45R 1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
0°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4
2.5°	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.8	10.4	10.2
5°	11.2	11.2	11.0	11.0	11.0	11.0	11.0	11.0	10.6	10.2	9.6
7.5°	11.4	11.4	11.2	11.2	11.2	11.2	11.0	10.8	10.4	9.6	9.0
10°	11.6	11.6	11.6	11.6	11.4	11.2	11.0	10.6	10.0	9.0	8.4
12.5°	13.1	13.1	12.9	12.4	12.0	11.6	11.2	10.4	9.2	8.2	7.5
15°	16.3	16.1	15.7	15.1	14.3	13.3	12.4	10.2	8.4	7.1	6.7
17.5°	22.8	22.4	21.8	19.8	18.0	16.1	14.5	10.2	7.5	6.3	5.9
20°	39.8	40.0	35.7	30.8	26.7	22.2	18.2	10.6	6.7	5.5	5.3
22.5°	83.0	79.8	69.6	57.7	44.1	34.1	25.7	11.6	5.9	4.7	4.7
25°	178.1	165.7	141.0	106.5	75.1	53.2	37.3	13.1	5.3	4.1	4.3
27.5°	325.2	314.0	264.4	199.1	132.2	80.4	50.6	14.9	4.7	3.5	3.9
30°	517.4	486.4	421.7	326.4	220.9	123.0	67.9	16.9	3.9	3.1	3.7
31°	577.4	563.1	484.3	377.6	258.9	146.1	75.3	17.5	3.7	3.1	3.5
32°	648.6	623.3	552.7	433.7	297.5	166.7	84.1	18.2	3.5	2.7	3.5
33°	712.2	687.7	601.8	483.1	336.4	190.1	93.4	18.4	3.1	2.7	3.3
34°	779.1	745.7	660.6	534.7	376.4	215.4	102.0	18.6	2.9	2.4	3.3
35°	827.1	793.6	711.2	575.5	410.9	237.9	111.8	18.6	2.7	2.4	3.1
36°	864.2	834.8	754.8	617.5	445.2	258.1	119.6	18.6	2.2	2.2	3.1
37°	889.7	861.8	784.2	653.7	471.3	276.0	126.5	18.6	2.0	2.2	3.1
38°	902.1	878.9	812.6	680.0	496.6	290.1	132.0	18.2	1.8	2.0	2.9
39°	907.5	888.5	829.9	702.2	515.5	302.3	136.1	17.7	1.6	2.0	2.9
40°	906.6	890.1	839.7	717.5	530.8	310.7	138.3	17.1	1.4	1.8	2.9
41°	901.9	887.7	844.8	730.6	540.0	316.4	138.9	16.5	1.2	1.8	2.7
42°	896.6	883.6	846.5	737.5	545.9	318.3	137.3	15.7	1.2	1.6	2.7
43°	891.1	879.1	846.5	739.8	547.4	317.0	134.6	14.3	1.0	1.6	2.7
44°	886.6	875.2	843.8	739.1	544.3	312.3	129.8	12.6	0.8	1.6	2.7
45°	881.3	870.1	840.3	735.3	538.4	304.4	123.6	11.2	0.6	1.4	2.7
46°	872.0	863.2	834.2	727.3	529.0	293.4	115.9	10.2	0.4	1.4	2.4
47°	853.8	846.2	822.4	715.5	516.6	280.3	107.9	9.2	0.4	1.4	2.4
48°	817.3	817.1	798.7	693.4	496.8	264.0	99.6	8.2	0.4	1.4	2.4
49°	782.0	778.3	755.5	654.7	468.4	244.4	90.8	7.3	0.2	1.4	2.4
50°	762.6	754.6	717.1	609.0	432.1	217.3	81.4	6.1	0.2	1.2	2.4
51°	742.4	731.0	686.7	567.8	388.8	191.2	71.2	4.9	0.2	1.2	2.2
52°	705.9	695.1	645.5	528.4	346.8	164.4	61.4	4.1	0.2	1.2	2.4
53°	666.5	651.0	597.1	485.1	309.9	140.8	51.4	3.5	0.2	1.2	2.2
54°	616.9	610.0	548.2	432.1	266.6	117.9	42.2	2.9	0.2	1.2	2.2
55°	570.2	560.0	495.8	377.8	227.5	96.7	35.3	2.2	0.2	1.2	2.2
56°	510.6	495.3	435.2	328.1	187.7	77.9	29.8	1.8	0.2	1.2	2.2
57°	439.6	423.3	375.8	272.8	147.3	59.4	24.9	1.4	0.2	1.2	2.2
58°	371.9	357.8	306.8	210.5	111.0	41.2	20.6	1.0	0.2	1.0	2.2
59°	321.3	305.8	255.2	162.0	77.1	30.4	15.5	0.8	0.2	1.2	2.2
60°	278.3	258.3	205.4	125.5	55.1	21.8	11.4	0.4	0.4	1.2	2.2
62.5°	160.4	141.6	98.1	51.0	22.6	11.2	5.5	0.2	0.4	1.2	2.2
65°	40.6	36.1	23.5	11.0	6.3	3.9	2.0	0.2	0.4	1.0	2.0



TEST NUMBER: P1313198

CATALOG NUMBER: LDSQA3D02R359727DE010 3LSQCA45R 1MW

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
67.5°	1.4	1.4	1.4	1.2	1.0	0.8	0.4	0.2	0.4	1.0	2.0
70°	0.6	0.6	0.6	0.4	0.4	0.2	0.2	0.2	0.4	1.0	1.8
72.5°	0.4	0.4	0.4	0.4	0.2	0.2	0.2	0.2	0.6	1.0	1.6
75°	0.4	0.4	0.4	0.4	0.2	0.2	0.2	0.2	0.6	1.0	1.6
77.5°	0.4	0.4	0.2	0.2	0.2	0.2	0.2	0.2	0.6	0.8	1.4
80°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.6	0.8	1.2
82.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.6	0.8	1.0
85°	0.0	0.0	0.0	0.0	0.0	0.2	0.0	0.2	0.6	0.8	0.8
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.2	0.6	0.8	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1313198

CATALOG NUMBER: LDSQA3D02R359727DE010 3LSQCA45R 1MW

**CANDELA DISTRIBUTION (continued):**

	135°	157.5°	180°
0°	10.4	10.4	10.4
2.5°	9.8	9.8	9.8
5°	9.2	9.2	9.0
7.5°	8.6	8.4	8.4
10°	7.8	7.8	7.8
12.5°	7.1	7.1	7.1
15°	6.5	6.7	6.7
17.5°	5.9	6.3	6.3
20°	5.5	5.9	6.1
22.5°	5.1	5.5	5.7
25°	4.9	5.3	5.5
27.5°	4.5	5.1	5.5
30°	4.3	4.9	5.3
31°	4.3	4.9	5.1
32°	4.1	4.9	5.1
33°	4.1	4.9	5.1
34°	4.1	4.7	5.1
35°	3.9	4.7	4.9
36°	3.9	4.7	4.9
37°	3.9	4.7	5.1
38°	3.9	4.7	4.9
39°	3.7	4.7	4.9
40°	3.7	4.7	4.9
41°	3.7	4.7	4.9
42°	3.7	4.7	4.9
43°	3.7	4.7	4.9
44°	3.7	4.5	4.9
45°	3.7	4.5	4.9
46°	3.7	4.7	4.9
47°	3.7	4.7	5.1
48°	3.7	4.5	4.9
49°	3.5	4.5	4.9
50°	3.5	4.5	4.9
51°	3.5	4.7	5.1
52°	3.5	4.7	5.1
53°	3.5	4.7	5.1
54°	3.5	4.7	4.9
55°	3.5	4.7	5.1
56°	3.5	4.7	4.9
57°	3.5	4.7	4.9
58°	3.5	4.5	4.9
59°	3.5	4.5	4.9
60°	3.5	4.5	4.9
62.5°	3.3	4.5	4.9
65°	3.3	4.3	4.7



TEST NUMBER: P1313198

CATALOG NUMBER: LDSQA3D02R359727DE010 3LSQCA45R 1MW

**CANDELA DISTRIBUTION (continued):**

	135°	157.5°	180°
67.5°	3.1	4.3	4.5
70°	2.9	4.1	4.3
72.5°	2.7	3.9	4.1
75°	2.4	3.5	3.7
77.5°	2.0	3.1	3.5
80°	1.8	2.7	2.9
82.5°	1.4	2.2	2.4
85°	1.0	1.6	1.6
87.5°	0.4	0.8	0.8
90°	0.0	0.0	0.0

(END OF REPORT)