

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1313222

Luminaire Tested: LDSQA3D02R459727DE010 3LSQCA45R 1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1313222
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-84)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R459727DE010 3LSQCA45R 1MB
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 97CRI , 3LSQCA45R 1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 247.0 lumens
Efficiency: N/A
Efficacy: 68.6 lumens/watt
Spacing Criteria (0/90/45): 3.81 / 0.82 / 1.83
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1313222
CATALOG NUMBER: LDSQA3D02R459727DE010 3LSQCA45R 1MB

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ····· 90°-270°



TEST NUMBER: P1313222

CATALOG NUMBER: LDSQA3D02R459727DE010 3LSQCA45R 1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	88	88	88	86
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	75	75	73
3	91	81	73	67	89	80	72	66	77	70	65	74	69	64	71	67	63	63	63	63	61
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	53	53	53	51
5	76	63	53	47	73	61	53	46	59	52	46	57	51	45	55	50	45	45	45	45	43
6	69	55	46	39	67	54	46	39	52	45	39	51	44	39	49	43	38	38	38	38	36
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	33	33	33	31
8	58	44	35	29	56	43	35	29	42	34	29	40	33	28	39	33	28	28	28	28	26
9	53	39	31	25	52	39	30	25	38	30	25	36	29	25	35	29	24	24	24	24	22
10	49	36	27	22	48	35	27	22	34	27	21	33	26	21	32	26	21	21	21	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	2463	2463	2463	2463	2463
5°	2922	2714	2438	2265	2265
10°	4669	3183	2291	2134	2134
15°	11643	4261	2068	1997	2068
20°	30680	6360	1796	1906	2016
25°	61588	9425	1558	1786	1976
30°	90782	12628	1253	1750	2028
35°	114520	14801	1072	1724	2102
40°	122190	14951	967	1799	2248
45°	126943	12470	901	1948	2436
50°	126758	8708	884	2090	2733
55°	107734	3873	931	2342	3003
60°	72402	758	930	2618	3444
65°	19194	326	897	2812	3912
70°	504	403	906	3072	4431
75°	399	399	932	3261	5057
80°	397	595	992	3471	5653
85°	395	790	1581	3557	5730

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 10°
 Vertical Angle: 47.5°
 Luminance: 130214 cd/sqm



TEST NUMBER: P1313222

CATALOG NUMBER: LDSQA3D02R459727DE010 3LSQCA45R 1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1.4	0.6
10°-20°	7.0	2.8
20°-30°	28.7	11.6
30°-40°	60.6	24.5
40°-50°	74.7	30.3
50°-60°	56.0	22.7
60°-70°	14.4	5.8
70°-80°	3.0	1.2
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	37.1	15.0
0°-40°	97.7	39.5
0°-60°	228.4	92.5
0°-90°	247.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	247.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	14	14	14	14	14	
5°	17	16	14	13	13	2
15°	65	24	12	11	12	24
25°	324	50	8	9	10	151
35°	545	70	5	8	10	332
45°	521	51	4	8	10	399
55°	359	13	3	8	10	310
65°	47	1	2	7	10	68
75°	1	1	1	5	8	1
85°	0	0	1	2	3	0
90°	0	0	0	0	0	



TEST NUMBER: P1313222

CATALOG NUMBER: LDSQA3D02R459727DE010 3LSQCA45R 1MB

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
0°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
2.5°	15.1	15.1	15.1	15.1	15.1	15.1	15.1	14.9	14.7	14.3	13.9
5°	16.9	16.7	16.7	16.7	16.5	16.3	16.3	15.7	14.9	14.1	13.5
7.5°	20.0	20.0	19.8	19.4	19.2	18.8	18.4	16.7	14.9	13.7	12.9
10°	26.7	26.3	25.7	25.3	24.3	22.9	21.8	18.2	14.7	13.1	12.4
12.5°	40.0	40.8	38.8	36.7	33.9	31.2	28.0	20.6	14.7	12.4	11.8
15°	65.3	66.7	62.9	58.8	51.8	45.3	39.2	23.9	14.3	11.6	11.0
17.5°	106.7	108.6	102.0	92.5	81.6	68.6	57.3	28.4	13.9	10.8	10.4
20°	167.4	167.1	154.5	142.5	121.6	102.5	81.4	34.7	13.3	9.8	9.8
22.5°	241.8	242.7	227.2	205.5	175.9	145.1	111.6	42.0	12.4	9.0	9.2
25°	324.1	317.2	298.8	272.5	234.7	192.0	148.0	49.6	11.6	8.2	8.6
27.5°	392.7	385.9	364.9	333.7	293.1	242.5	184.9	57.1	10.6	7.3	8.0
30°	456.5	448.0	422.7	387.4	339.0	284.3	219.6	63.5	9.4	6.3	7.3
32.5°	509.2	501.4	472.7	431.7	379.0	320.2	249.0	68.4	8.2	5.7	6.9
35°	544.7	536.8	510.2	465.1	407.8	346.3	272.9	70.4	7.1	5.1	6.7
37.5°	552.9	548.6	529.6	487.4	427.6	363.1	288.2	69.8	5.9	4.7	6.3
40°	543.5	544.5	535.5	500.4	438.2	370.2	294.5	66.5	4.9	4.3	6.1
42.5°	531.5	534.1	533.5	505.7	442.7	370.6	291.8	60.0	3.9	3.9	5.9
45°	521.2	523.9	527.6	503.5	439.6	365.3	283.5	51.2	2.9	3.7	5.9
47.5°	502.7	505.5	510.8	485.5	424.1	351.6	268.4	41.6	2.0	3.5	5.7
50°	473.1	474.5	473.1	444.7	394.3	329.6	243.9	32.5	1.4	3.3	5.7
52.5°	442.7	439.8	428.0	392.1	347.0	294.7	213.1	23.1	1.0	3.1	5.5
55°	358.8	354.3	345.5	323.5	297.8	251.8	172.3	12.9	1.0	3.1	5.3
57.5°	250.0	252.5	255.5	251.0	239.2	198.4	130.8	5.7	1.0	2.9	5.3
60°	210.2	208.2	208.4	205.5	185.9	144.7	90.0	2.2	1.0	2.7	5.1
62.5°	125.5	126.9	129.6	130.2	110.8	80.8	47.1	1.0	1.0	2.4	4.9
65°	47.1	49.4	43.3	37.6	29.8	21.8	11.0	0.8	1.2	2.2	4.5
67.5°	1.4	1.6	2.0	1.8	1.8	1.6	1.2	0.8	1.2	2.0	4.3
70°	1.0	1.0	1.0	1.0	1.0	0.8	0.8	0.8	1.0	1.8	3.9
72.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.0	1.6	3.5
75°	0.6	0.8	0.6	0.6	0.6	0.6	0.6	0.6	1.0	1.4	2.9
77.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.8	1.2	2.4
80°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.6	0.8	1.0	2.0
82.5°	0.4	0.4	0.4	0.2	0.4	0.4	0.4	0.4	0.8	0.8	1.6
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.4	0.6	0.8	1.0
87.5°	0.0	0.0	0.0	0.0	0.2	0.2	0.2	0.4	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1313222

CATALOG NUMBER: LDSQA3D02R459727DE010 3LSQCA45R 1MB

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
0°	14.3	14.3	14.3
2.5°	13.5	13.5	13.5
5°	13.1	13.1	13.1
7.5°	12.7	12.7	12.7
10°	12.2	12.2	12.2
12.5°	11.8	11.8	12.0
15°	11.2	11.6	11.6
17.5°	10.8	11.2	11.4
20°	10.4	10.8	11.0
22.5°	9.8	10.4	10.8
25°	9.4	10.2	10.4
27.5°	9.0	10.0	10.4
30°	8.8	9.8	10.2
32.5°	8.4	9.6	10.0
35°	8.2	9.6	10.0
37.5°	8.2	9.4	10.0
40°	8.0	9.4	10.0
42.5°	8.0	9.4	10.0
45°	8.0	9.4	10.0
47.5°	7.8	9.4	10.2
50°	7.8	9.6	10.2
52.5°	7.8	9.6	10.2
55°	7.8	9.6	10.0
57.5°	7.6	9.4	10.0
60°	7.6	9.4	10.0
62.5°	7.1	9.2	9.8
65°	6.9	9.0	9.6
67.5°	6.5	8.8	9.2
70°	6.1	8.2	8.8
72.5°	5.5	7.8	8.4
75°	4.9	7.1	7.6
77.5°	4.3	6.3	6.7
80°	3.5	5.3	5.7
82.5°	2.7	4.1	4.3
85°	1.8	2.7	2.9
87.5°	0.8	1.2	1.4
90°	0.0	0.0	0.0

(END OF REPORT)