

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1312118

Luminaire Tested: LDSQA3D02R409050DE010 3LSQCA45R 1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1312118
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-78)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R409050DE010 3LSQCA45R 1MMS
Description: 3in Adjustable LED luminaire with, R40 optic, 5000K CCT AND, 90CRI , 3LSQCA45R 1MMS TRII
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 290.0 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 3.99 / 0.74 / 1.54
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1312118
CATALOG NUMBER: LDSQA3D02R409050DE010 3LSQCA45R 1MMS

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ····· 90°-270°



TEST NUMBER: P1312118
 CATALOG NUMBER: LDSQA3D02R409050DE010 3LSQCA45R 1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|---|
| RF | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | 20 | | | | | |
| RC | 80 | | | | | 70 | | | | | 50 | | | | | 30 | | | | | 10 | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | | |
| 1 | 110 | 106 | 102 | 99 | 107 | 104 | 100 | 97 | 99 | 97 | 94 | 96 | 93 | 91 | 92 | 90 | 88 | 86 | 86 | 86 | 86 | 86 | 86 | 86 | | |
| 2 | 100 | 93 | 86 | 81 | 98 | 91 | 85 | 80 | 87 | 82 | 78 | 84 | 80 | 76 | 81 | 78 | 75 | 72 | 72 | 72 | 72 | 72 | 72 | 72 | | |
| 3 | 91 | 81 | 73 | 66 | 89 | 79 | 72 | 66 | 76 | 70 | 65 | 73 | 68 | 64 | 71 | 66 | 62 | 60 | 60 | 60 | 60 | 60 | 60 | 60 | | |
| 4 | 82 | 70 | 62 | 55 | 80 | 69 | 61 | 54 | 67 | 59 | 54 | 64 | 58 | 53 | 62 | 57 | 52 | 50 | 50 | 50 | 50 | 50 | 50 | 50 | | |
| 5 | 75 | 62 | 52 | 46 | 73 | 60 | 52 | 45 | 58 | 51 | 45 | 56 | 50 | 44 | 54 | 49 | 44 | 42 | 42 | 42 | 42 | 42 | 42 | 42 | | |
| 6 | 68 | 54 | 45 | 38 | 66 | 53 | 44 | 38 | 51 | 43 | 38 | 50 | 43 | 37 | 48 | 42 | 37 | 35 | 35 | 35 | 35 | 35 | 35 | 35 | | |
| 7 | 62 | 48 | 39 | 32 | 60 | 47 | 38 | 32 | 45 | 37 | 32 | 44 | 37 | 31 | 42 | 36 | 31 | 29 | 29 | 29 | 29 | 29 | 29 | 29 | | |
| 8 | 57 | 42 | 33 | 27 | 55 | 42 | 33 | 27 | 40 | 32 | 27 | 39 | 32 | 27 | 38 | 31 | 26 | 24 | 24 | 24 | 24 | 24 | 24 | 24 | | |
| 9 | 52 | 38 | 29 | 23 | 51 | 37 | 29 | 23 | 36 | 28 | 23 | 35 | 28 | 23 | 34 | 27 | 23 | 21 | 21 | 21 | 21 | 21 | 21 | 21 | | |
| 10 | 48 | 34 | 25 | 20 | 47 | 33 | 25 | 20 | 32 | 25 | 20 | 31 | 24 | 20 | 30 | 24 | 19 | 18 | 18 | 18 | 18 | 18 | 18 | 18 | | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 45° | 90° | 135° | 180° |
|-----|--------|------|------|------|------|
| 0° | 2566 | 2566 | 2566 | 2566 | 2566 |
| 5° | 2853 | 2766 | 2524 | 2299 | 2247 |
| 10° | 3445 | 2938 | 2326 | 2099 | 2046 |
| 15° | 5652 | 3174 | 1997 | 1854 | 1908 |
| 20° | 14937 | 3757 | 1668 | 1668 | 1814 |
| 25° | 57597 | 4656 | 1311 | 1520 | 1767 |
| 30° | 124251 | 6205 | 1054 | 1491 | 1750 |
| 35° | 187013 | 7338 | 904 | 1451 | 1787 |
| 40° | 210702 | 7374 | 787 | 1506 | 1911 |
| 45° | 225926 | 5699 | 706 | 1559 | 2070 |
| 50° | 222061 | 3563 | 643 | 1634 | 2277 |
| 55° | 195350 | 1772 | 631 | 1832 | 2552 |
| 60° | 123656 | 379 | 723 | 2032 | 2859 |
| 65° | 25307 | 122 | 774 | 2160 | 3138 |
| 70° | 554 | 151 | 806 | 2417 | 3626 |
| 75° | 532 | 333 | 865 | 2662 | 4059 |
| 80° | 496 | 298 | 1091 | 2876 | 4761 |
| 85° | 593 | 593 | 2174 | 3162 | 5335 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 47°
 Luminance: 230001 cd/sqm



TEST NUMBER: P1312118

CATALOG NUMBER: LDSQA3D02R409050DE010 3LSQCA45R 1MMS

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------------|--------------|--------------|
| 0°-10° | 1.4 | 0.5 |
| 10°-20° | 4.6 | 1.6 |
| 20°-30° | 22.5 | 7.8 |
| 30°-40° | 73.3 | 25.3 |
| 40°-50° | 101.0 | 34.8 |
| 50°-60° | 70.4 | 24.3 |
| 60°-70° | 13.3 | 4.6 |
| 70°-80° | 2.4 | 0.8 |
| 80°-90° | 1.1 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 28.5 | 9.8 |
| 0°-40° | 101.8 | 35.1 |
| 0°-60° | 273.1 | 94.2 |
| 0°-90° | 290.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 290.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 45° | 90° | 135° | 180° | Flux |
|-----|-----|-----|-----|------|------|------|
| 0° | 15 | 15 | 15 | 15 | 15 | |
| 5° | 16 | 16 | 15 | 13 | 13 | 2 |
| 15° | 32 | 18 | 11 | 10 | 11 | 12 |
| 25° | 303 | 24 | 7 | 8 | 9 | 156 |
| 35° | 890 | 35 | 4 | 7 | 8 | 538 |
| 45° | 928 | 23 | 3 | 6 | 8 | 705 |
| 55° | 651 | 6 | 2 | 6 | 8 | 556 |
| 65° | 62 | 0 | 2 | 5 | 8 | 110 |
| 75° | 1 | 0 | 1 | 4 | 6 | 1 |
| 85° | 0 | 0 | 1 | 2 | 3 | 0 |
| 90° | 0 | 0 | 0 | 0 | 0 | |



TEST NUMBER: P1312118
 CATALOG NUMBER: LDSQA3D02R409050DE010 3LSQCA45R 1MMS

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 45° | 67.5° | 90° |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|------|-------|------|
| 0° | 14.9 | 14.9 | 14.9 | 14.9 | 14.9 | 14.9 | 14.9 | 14.9 | 14.9 | 14.9 | 14.9 |
| 2.5° | 15.4 | 15.4 | 15.4 | 15.4 | 15.4 | 15.4 | 15.4 | 15.4 | 15.4 | 15.2 | 14.9 |
| 5° | 16.5 | 16.5 | 16.5 | 16.5 | 16.2 | 16.2 | 16.2 | 16.0 | 16.0 | 15.4 | 14.6 |
| 7.5° | 17.6 | 17.6 | 17.6 | 17.6 | 17.3 | 17.0 | 16.8 | 16.8 | 16.5 | 15.2 | 14.1 |
| 10° | 19.7 | 19.7 | 19.4 | 19.2 | 18.9 | 18.4 | 18.1 | 17.6 | 16.8 | 14.9 | 13.3 |
| 12.5° | 24.0 | 23.4 | 23.2 | 22.6 | 21.8 | 20.8 | 19.7 | 18.9 | 17.0 | 14.4 | 12.5 |
| 15° | 31.7 | 31.2 | 30.1 | 28.5 | 26.9 | 24.8 | 22.9 | 21.0 | 17.8 | 13.6 | 11.2 |
| 17.5° | 45.3 | 43.7 | 42.1 | 39.4 | 35.4 | 31.7 | 27.7 | 24.2 | 18.9 | 12.8 | 10.1 |
| 20° | 81.5 | 80.4 | 70.8 | 63.4 | 51.4 | 42.9 | 34.9 | 29.0 | 20.5 | 12.0 | 9.1 |
| 22.5° | 168.1 | 156.9 | 141.2 | 115.6 | 90.0 | 66.3 | 48.2 | 36.5 | 22.1 | 10.9 | 8.0 |
| 25° | 303.1 | 285.5 | 251.7 | 202.4 | 149.4 | 105.7 | 69.8 | 47.7 | 24.5 | 9.9 | 6.9 |
| 27.5° | 458.9 | 441.0 | 388.6 | 320.7 | 234.1 | 159.5 | 99.6 | 63.1 | 27.7 | 8.8 | 6.1 |
| 30° | 624.8 | 609.6 | 543.0 | 449.0 | 330.0 | 223.4 | 133.4 | 78.8 | 31.2 | 7.7 | 5.3 |
| 31° | 691.6 | 672.2 | 600.3 | 500.2 | 375.0 | 249.8 | 147.0 | 85.5 | 32.5 | 7.5 | 5.1 |
| 32° | 753.2 | 731.1 | 656.5 | 549.2 | 411.5 | 278.3 | 161.9 | 91.3 | 33.6 | 6.9 | 4.8 |
| 33° | 806.2 | 780.3 | 708.4 | 595.5 | 451.7 | 304.9 | 177.4 | 96.9 | 34.4 | 6.4 | 4.5 |
| 34° | 851.2 | 828.8 | 751.6 | 642.1 | 487.4 | 330.5 | 192.6 | 102.5 | 34.9 | 6.1 | 4.3 |
| 35° | 889.5 | 869.3 | 792.8 | 677.5 | 522.3 | 355.3 | 206.4 | 107.9 | 34.9 | 5.6 | 4.3 |
| 36° | 915.4 | 897.8 | 828.5 | 713.8 | 551.6 | 376.3 | 218.1 | 112.7 | 34.9 | 5.1 | 4.0 |
| 37° | 929.5 | 912.4 | 852.0 | 743.6 | 580.3 | 397.1 | 228.8 | 116.4 | 34.6 | 4.8 | 3.7 |
| 38° | 936.7 | 921.7 | 869.3 | 767.8 | 600.3 | 412.0 | 238.1 | 119.3 | 34.4 | 4.3 | 3.7 |
| 39° | 938.5 | 926.0 | 880.2 | 785.4 | 619.7 | 426.9 | 244.8 | 120.9 | 33.6 | 4.0 | 3.5 |
| 40° | 937.2 | 926.3 | 886.1 | 801.1 | 634.7 | 438.6 | 249.5 | 121.4 | 32.8 | 3.5 | 3.5 |
| 41° | 934.5 | 926.0 | 890.3 | 812.0 | 646.6 | 446.1 | 251.4 | 120.4 | 31.7 | 2.9 | 3.2 |
| 42° | 932.1 | 922.8 | 892.2 | 819.5 | 654.9 | 449.8 | 251.1 | 118.2 | 30.1 | 2.7 | 3.2 |
| 43° | 932.1 | 921.5 | 892.5 | 824.3 | 658.9 | 450.1 | 247.9 | 114.3 | 28.0 | 2.4 | 2.9 |
| 44° | 930.5 | 920.7 | 893.8 | 827.5 | 660.0 | 447.7 | 242.9 | 110.0 | 25.6 | 2.1 | 2.9 |
| 45° | 927.6 | 917.2 | 893.5 | 827.7 | 658.1 | 441.8 | 234.6 | 104.4 | 23.4 | 1.6 | 2.9 |
| 46° | 922.0 | 912.7 | 891.1 | 825.9 | 652.5 | 433.3 | 224.8 | 98.8 | 21.0 | 1.3 | 2.7 |
| 47° | 910.8 | 903.6 | 884.7 | 819.5 | 644.0 | 420.8 | 213.1 | 92.4 | 19.2 | 1.1 | 2.7 |
| 48° | 891.7 | 886.6 | 873.8 | 805.4 | 627.7 | 405.3 | 200.5 | 85.5 | 17.3 | 1.1 | 2.7 |
| 49° | 856.5 | 852.5 | 845.0 | 782.7 | 607.0 | 386.4 | 187.0 | 77.8 | 15.4 | 0.8 | 2.7 |
| 50° | 828.8 | 824.5 | 809.4 | 744.6 | 577.1 | 362.5 | 172.0 | 70.0 | 13.3 | 0.5 | 2.4 |
| 51° | 810.4 | 803.5 | 779.5 | 700.4 | 533.7 | 330.5 | 155.8 | 62.3 | 11.2 | 0.5 | 2.4 |
| 52° | 787.3 | 776.9 | 747.0 | 660.8 | 494.0 | 298.5 | 138.2 | 54.6 | 9.9 | 0.5 | 2.4 |
| 53° | 738.8 | 735.1 | 705.5 | 618.1 | 454.3 | 267.9 | 120.1 | 48.2 | 8.5 | 0.5 | 2.4 |
| 54° | 696.4 | 690.8 | 650.6 | 559.0 | 411.2 | 233.8 | 101.5 | 42.6 | 7.2 | 0.5 | 2.4 |
| 55° | 650.6 | 639.7 | 604.0 | 509.2 | 360.6 | 202.4 | 83.6 | 36.8 | 5.9 | 0.5 | 2.1 |
| 56° | 592.8 | 583.3 | 544.9 | 455.9 | 314.0 | 170.4 | 70.0 | 30.1 | 4.5 | 0.5 | 2.1 |
| 57° | 522.5 | 513.7 | 484.2 | 390.4 | 265.5 | 139.3 | 57.0 | 24.2 | 3.5 | 0.5 | 2.1 |
| 58° | 454.6 | 444.8 | 410.9 | 327.6 | 214.4 | 110.5 | 47.7 | 19.7 | 2.7 | 0.5 | 2.1 |
| 59° | 402.4 | 389.1 | 345.4 | 275.1 | 167.8 | 83.9 | 37.8 | 15.7 | 1.9 | 0.5 | 2.1 |
| 60° | 359.0 | 348.1 | 302.8 | 229.0 | 131.6 | 61.8 | 28.0 | 12.0 | 1.1 | 0.5 | 2.1 |
| 62.5° | 208.0 | 205.1 | 164.3 | 118.0 | 62.1 | 28.8 | 13.8 | 5.6 | 0.5 | 0.8 | 2.1 |
| 65° | 62.1 | 54.1 | 42.1 | 25.0 | 16.0 | 9.6 | 5.1 | 1.9 | 0.3 | 0.8 | 1.9 |



TEST NUMBER: P1312118
 CATALOG NUMBER: LDSQA3D02R409050DE010 3LSQCA45R 1MMS

CANDELA DISTRIBUTION (continued):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 45° | 67.5° | 90° |
|-------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-------|-----|
| 67.5° | 1.9 | 1.9 | 1.9 | 1.9 | 1.9 | 1.9 | 1.1 | 0.5 | 0.3 | 0.8 | 1.9 |
| 70° | 1.1 | 0.8 | 0.8 | 0.8 | 0.8 | 0.5 | 0.5 | 0.3 | 0.3 | 0.8 | 1.6 |
| 72.5° | 0.8 | 0.8 | 0.8 | 0.8 | 0.5 | 0.5 | 0.5 | 0.3 | 0.5 | 0.8 | 1.3 |
| 75° | 0.8 | 0.5 | 0.5 | 0.5 | 0.5 | 0.3 | 0.3 | 0.3 | 0.5 | 0.8 | 1.3 |
| 77.5° | 0.5 | 0.5 | 0.5 | 0.5 | 0.3 | 0.3 | 0.3 | 0.3 | 0.5 | 0.8 | 1.3 |
| 80° | 0.5 | 0.5 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.8 | 1.1 |
| 82.5° | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.8 | 1.1 |
| 85° | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.8 | 1.1 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.3 | 0.3 | 0.8 | 0.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



TEST NUMBER: P1312118
 CATALOG NUMBER: LDSQA3D02R409050DE010 3LSQCA45R 1MMS

CANDELA DISTRIBUTION (continued):

| | 112.5° | 135° | 157.5° | 180° |
|-------|--------|------|--------|------|
| 0° | 14.9 | 14.9 | 14.9 | 14.9 |
| 2.5° | 14.4 | 14.1 | 13.8 | 13.8 |
| 5° | 13.8 | 13.3 | 13.3 | 13.0 |
| 7.5° | 13.0 | 12.5 | 12.5 | 12.5 |
| 10° | 12.3 | 12.0 | 12.0 | 11.7 |
| 12.5° | 11.2 | 11.2 | 11.2 | 11.2 |
| 15° | 10.4 | 10.4 | 10.7 | 10.7 |
| 17.5° | 9.3 | 9.6 | 10.1 | 10.4 |
| 20° | 8.5 | 9.1 | 9.6 | 9.9 |
| 22.5° | 8.0 | 8.5 | 9.3 | 9.6 |
| 25° | 7.2 | 8.0 | 9.1 | 9.3 |
| 27.5° | 6.7 | 7.7 | 8.5 | 9.1 |
| 30° | 6.1 | 7.5 | 8.3 | 8.8 |
| 31° | 6.1 | 7.2 | 8.3 | 8.8 |
| 32° | 5.9 | 6.9 | 8.3 | 8.5 |
| 33° | 5.9 | 6.9 | 8.3 | 8.5 |
| 34° | 5.6 | 6.9 | 8.0 | 8.5 |
| 35° | 5.6 | 6.9 | 8.0 | 8.5 |
| 36° | 5.3 | 6.7 | 8.0 | 8.5 |
| 37° | 5.3 | 6.7 | 8.0 | 8.5 |
| 38° | 5.1 | 6.7 | 8.0 | 8.5 |
| 39° | 5.1 | 6.7 | 8.0 | 8.5 |
| 40° | 5.1 | 6.7 | 8.0 | 8.5 |
| 41° | 4.8 | 6.7 | 8.0 | 8.5 |
| 42° | 4.8 | 6.7 | 8.0 | 8.5 |
| 43° | 4.8 | 6.4 | 8.0 | 8.5 |
| 44° | 4.8 | 6.4 | 8.0 | 8.5 |
| 45° | 4.5 | 6.4 | 8.0 | 8.5 |
| 46° | 4.5 | 6.4 | 8.0 | 8.5 |
| 47° | 4.5 | 6.4 | 8.0 | 8.5 |
| 48° | 4.5 | 6.4 | 8.0 | 8.5 |
| 49° | 4.5 | 6.4 | 8.0 | 8.5 |
| 50° | 4.3 | 6.1 | 8.0 | 8.5 |
| 51° | 4.3 | 6.1 | 8.0 | 8.5 |
| 52° | 4.3 | 6.1 | 8.0 | 8.5 |
| 53° | 4.3 | 6.1 | 8.0 | 8.5 |
| 54° | 4.0 | 6.1 | 8.0 | 8.5 |
| 55° | 4.0 | 6.1 | 8.0 | 8.5 |
| 56° | 4.0 | 6.1 | 8.0 | 8.3 |
| 57° | 4.0 | 6.1 | 7.7 | 8.3 |
| 58° | 4.0 | 5.9 | 7.7 | 8.3 |
| 59° | 4.0 | 5.9 | 7.7 | 8.3 |
| 60° | 4.0 | 5.9 | 7.7 | 8.3 |
| 62.5° | 3.7 | 5.9 | 7.5 | 8.0 |
| 65° | 3.5 | 5.3 | 7.5 | 7.7 |



TEST NUMBER: P1312118
CATALOG NUMBER: LDSQA3D02R409050DE010 3LSQCA45R 1MMS

CANDELA DISTRIBUTION (continued):

| | 112.5° | 135° | 157.5° | 180° |
|-------|--------|------|--------|------|
| 67.5° | 3.5 | 5.1 | 6.9 | 7.5 |
| 70° | 3.2 | 4.8 | 6.7 | 7.2 |
| 72.5° | 2.7 | 4.5 | 6.1 | 6.7 |
| 75° | 2.4 | 4.0 | 5.6 | 6.1 |
| 77.5° | 2.1 | 3.5 | 5.1 | 5.3 |
| 80° | 1.9 | 2.9 | 4.3 | 4.8 |
| 82.5° | 1.3 | 2.1 | 3.5 | 3.7 |
| 85° | 1.1 | 1.6 | 2.4 | 2.7 |
| 87.5° | 0.8 | 0.8 | 1.3 | 1.3 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)