

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1313366

Luminaire Tested: LDSQA3D05R359727DE010 3LSQCA45R 1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1313366
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-77)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R359727DE010 3LSQCA45R 1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , 3LSQCA45R 1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 464.0 lumens
Efficiency: N/A
Efficacy: 64.4 lumens/watt
Spacing Criteria (0/90/45): 4.01 / 0.66 / 1.41
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1313366
CATALOG NUMBER: LDSQA3D05R359727DE010 3LSQCA45R 1MW

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1313366

CATALOG NUMBER: LDSQA3D05R359727DE010 3LSQCA45R 1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	100	
1	110	106	102	99	107	104	100	97	100	97	94	96	93	91	92	90	89	89	87	
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	73	
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	67	63	63	61	
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	52	52	50	
5	75	62	52	46	73	61	52	45	58	51	45	56	50	44	55	49	44	44	42	
6	68	54	45	38	66	53	44	38	51	43	38	50	43	37	48	42	37	37	35	
7	62	48	38	32	60	47	38	32	45	37	32	44	37	31	42	36	31	31	29	
8	57	42	33	27	55	41	33	27	40	32	27	39	32	26	38	31	26	26	24	
9	52	38	29	23	50	37	29	23	36	28	23	35	28	22	34	27	22	22	20	
10	48	34	25	19	46	33	25	19	32	25	19	31	24	19	30	24	19	19	17	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	3686	3686	3686	3686	3686
5°	3976	3907	3613	3250	3181
10°	4180	3812	3218	2781	2781
15°	5973	3726	2621	2389	2461
20°	14974	3995	2071	2071	2309
25°	69493	5093	1596	1919	2147
30°	211235	6921	1253	1750	2168
35°	357017	8010	1051	1682	2123
40°	418481	7914	854	1686	2271
45°	440721	5602	706	1827	2460
50°	419499	3376	670	1902	2706
55°	351516	1381	751	2132	3153
60°	196782	276	861	2446	3479
65°	33987	163	856	2730	3912
70°	655	201	1057	2971	4431
75°	532	266	1397	3327	4991
80°	397	397	1686	3769	5852
85°	0	790	3359	4150	6719

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 46°
 Luminance: 443834 cd/sqm



TEST NUMBER: P1313366

CATALOG NUMBER: LDSQA3D05R359727DE010 3LSQCA45R 1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1.9	0.4
10°-20°	5.5	1.2
20°-30°	28.5	6.1
30°-40°	123.0	26.5
40°-50°	175.4	37.8
50°-60°	108.6	23.4
60°-70°	16.5	3.6
70°-80°	3.1	0.7
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	35.9	7.7
0°-40°	158.8	34.2
0°-60°	442.8	95.4
0°-90°	464.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	464.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	21	21	21	21	21	
5°	23	23	21	19	18	2
15°	34	21	15	13	14	12
25°	366	27	8	10	11	219
35°	1698	38	5	8	10	1020
45°	1810	23	3	8	10	1367
55°	1171	5	2	7	10	997
65°	83	0	2	7	10	170
75°	1	0	2	5	8	1
85°	0	0	2	2	3	0
90°	0	0	0	0	0	



TEST NUMBER: P1313366

CATALOG NUMBER: LDSQA3D05R359727DE010 3LSQCA45R 1MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
0°	21.4	21.4	21.4	21.4	21.4	21.4	21.4	21.4	21.4	21.4	21.4
2.5°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	21.4	20.9
5°	23.0	23.0	22.6	22.6	22.6	22.6	22.6	22.6	21.8	20.9	19.7
7.5°	23.5	23.5	23.0	23.0	23.0	23.0	22.6	22.2	21.4	19.7	18.4
10°	23.9	23.9	23.9	23.9	23.5	23.0	22.6	21.8	20.5	18.4	17.2
12.5°	26.8	26.8	26.4	25.6	24.7	23.9	23.0	21.4	18.8	16.8	15.5
15°	33.5	33.1	32.3	31.0	29.3	27.2	25.6	20.9	17.2	14.7	13.8
17.5°	46.9	46.1	44.8	40.6	36.9	33.1	29.7	20.9	15.5	13.0	12.1
20°	81.7	82.1	73.3	63.2	54.9	45.7	37.3	21.8	13.8	11.3	10.9
22.5°	170.5	163.8	142.8	118.5	90.5	69.9	52.8	23.9	12.1	9.6	9.6
25°	365.7	340.1	289.4	218.6	154.1	109.3	76.7	26.8	10.9	8.4	8.8
27.5°	667.7	644.6	542.8	408.8	271.4	165.0	103.9	30.6	9.6	7.1	8.0
30°	1062.2	998.6	865.8	670.2	453.6	252.6	139.5	34.8	8.0	6.3	7.5
31°	1185.4	1156.1	994.4	775.3	531.5	299.9	154.6	36.0	7.5	6.3	7.1
32°	1331.6	1279.6	1134.7	890.5	610.7	342.2	172.6	37.3	7.1	5.4	7.1
33°	1462.2	1412.0	1235.6	991.9	690.7	390.4	191.8	37.7	6.3	5.4	6.7
34°	1599.6	1530.9	1356.3	1097.8	772.8	442.3	209.4	38.1	5.9	5.0	6.7
35°	1698.1	1629.4	1460.1	1181.6	843.6	488.4	229.5	38.1	5.4	5.0	6.3
36°	1774.3	1714.0	1549.8	1267.9	914.0	529.9	245.5	38.1	4.6	4.6	6.3
37°	1826.6	1769.3	1610.1	1342.0	967.6	566.7	259.7	38.1	4.2	4.6	6.3
38°	1852.2	1804.4	1668.3	1396.1	1019.5	595.6	271.0	37.3	3.8	4.2	5.9
39°	1863.1	1824.1	1703.9	1441.7	1058.5	620.7	279.4	36.4	3.4	4.2	5.9
40°	1861.4	1827.5	1724.0	1473.1	1089.9	637.9	284.0	35.2	2.9	3.8	5.9
41°	1851.8	1822.5	1734.5	1499.9	1108.7	649.7	285.2	33.9	2.5	3.8	5.4
42°	1840.9	1814.1	1737.8	1514.2	1120.9	653.4	281.9	32.3	2.5	3.4	5.4
43°	1829.6	1804.9	1737.8	1518.8	1123.8	650.9	276.4	29.3	2.1	3.4	5.4
44°	1820.4	1796.9	1732.4	1517.5	1117.5	641.3	266.4	26.0	1.7	3.4	5.4
45°	1809.5	1786.4	1725.3	1509.6	1105.4	624.9	253.8	23.0	1.3	2.9	5.4
46°	1790.2	1772.2	1712.7	1493.2	1086.1	602.3	237.9	20.9	0.8	2.9	5.0
47°	1752.9	1737.4	1688.4	1468.9	1060.6	575.5	221.6	18.8	0.8	2.9	5.0
48°	1678.0	1677.5	1639.8	1423.7	1019.9	542.0	204.4	16.8	0.8	2.9	5.0
49°	1605.5	1597.9	1551.0	1344.1	961.7	501.8	186.4	15.1	0.4	2.9	5.0
50°	1565.7	1549.4	1472.3	1250.3	887.1	446.1	167.1	12.6	0.4	2.5	5.0
51°	1524.2	1500.8	1409.9	1165.7	798.3	392.5	146.2	10.1	0.4	2.5	4.6
52°	1449.3	1427.1	1325.3	1084.8	712.1	337.6	126.1	8.4	0.4	2.5	5.0
53°	1368.4	1336.6	1226.0	996.0	636.2	289.0	105.6	7.1	0.4	2.5	4.6
54°	1266.6	1252.4	1125.5	887.1	547.4	242.1	86.7	5.9	0.4	2.5	4.6
55°	1170.7	1149.8	1017.8	775.7	467.0	198.5	72.5	4.6	0.4	2.5	4.6
56°	1048.4	1017.0	893.4	673.5	385.4	160.0	61.2	3.8	0.4	2.5	4.6
57°	902.6	869.1	771.5	560.0	302.4	121.9	51.1	2.9	0.4	2.5	4.6
58°	763.6	734.7	630.0	432.3	227.9	84.6	42.3	2.1	0.4	2.1	4.6
59°	659.7	627.9	524.0	332.6	158.3	62.4	31.8	1.7	0.4	2.5	4.6
60°	571.3	530.3	421.8	257.6	113.1	44.8	23.5	0.8	0.8	2.5	4.6
62.5°	329.2	290.7	201.5	104.7	46.5	23.0	11.3	0.4	0.8	2.5	4.6
65°	83.4	74.1	48.2	22.6	13.0	8.0	4.2	0.4	0.8	2.1	4.2



TEST NUMBER: P1313366

CATALOG NUMBER: LDSQA3D05R359727DE010 3LSQCA45R 1MW

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
67.5°	2.9	2.9	2.9	2.5	2.1	1.7	0.8	0.4	0.8	2.1	4.2
70°	1.3	1.3	1.3	0.8	0.8	0.4	0.4	0.4	0.8	2.1	3.8
72.5°	0.8	0.8	0.8	0.8	0.4	0.4	0.4	0.4	1.3	2.1	3.4
75°	0.8	0.8	0.8	0.8	0.4	0.4	0.4	0.4	1.3	2.1	3.4
77.5°	0.8	0.8	0.4	0.4	0.4	0.4	0.4	0.4	1.3	1.7	2.9
80°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	1.3	1.7	2.5
82.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	1.3	1.7	2.1
85°	0.0	0.0	0.0	0.0	0.0	0.4	0.0	0.4	1.3	1.7	1.7
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.4	1.3	1.7	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1313366
 CATALOG NUMBER: LDSQA3D05R359727DE010 3LSQCA45R 1MW

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
0°	21.4	21.4	21.4
2.5°	20.1	20.1	20.1
5°	18.8	18.8	18.4
7.5°	17.6	17.2	17.2
10°	15.9	15.9	15.9
12.5°	14.7	14.7	14.7
15°	13.4	13.8	13.8
17.5°	12.1	13.0	13.0
20°	11.3	12.1	12.6
22.5°	10.5	11.3	11.7
25°	10.1	10.9	11.3
27.5°	9.2	10.5	11.3
30°	8.8	10.1	10.9
31°	8.8	10.1	10.5
32°	8.4	10.1	10.5
33°	8.4	10.1	10.5
34°	8.4	9.6	10.5
35°	8.0	9.6	10.1
36°	8.0	9.6	10.1
37°	8.0	9.6	10.5
38°	8.0	9.6	10.1
39°	7.5	9.6	10.1
40°	7.5	9.6	10.1
41°	7.5	9.6	10.1
42°	7.5	9.6	10.1
43°	7.5	9.6	10.1
44°	7.5	9.2	10.1
45°	7.5	9.2	10.1
46°	7.5	9.6	10.1
47°	7.5	9.6	10.5
48°	7.5	9.2	10.1
49°	7.1	9.2	10.1
50°	7.1	9.2	10.1
51°	7.1	9.6	10.5
52°	7.1	9.6	10.5
53°	7.1	9.6	10.5
54°	7.1	9.6	10.1
55°	7.1	9.6	10.5
56°	7.1	9.6	10.1
57°	7.1	9.6	10.1
58°	7.1	9.2	10.1
59°	7.1	9.2	10.1
60°	7.1	9.2	10.1
62.5°	6.7	9.2	10.1
65°	6.7	8.8	9.6



TEST NUMBER: P1313366
CATALOG NUMBER: LDSQA3D05R359727DE010 3LSQCA45R 1MW

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
67.5°	6.3	8.8	9.2
70°	5.9	8.4	8.8
72.5°	5.4	8.0	8.4
75°	5.0	7.1	7.5
77.5°	4.2	6.3	7.1
80°	3.8	5.4	5.9
82.5°	2.9	4.6	5.0
85°	2.1	3.4	3.4
87.5°	0.8	1.7	1.7
90°	0.0	0.0	0.0

(END OF REPORT)