

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1313385

Luminaire Tested: LDSQA3D05R409727DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1313385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R409727DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 97CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 595.0 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.69 / 0.6
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1313385
CATALOG NUMBER: LDSQA3D05R409727DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1313385

CATALOG NUMBER: LDSQA3D05R409727DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	94	94	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	92	92	92	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	87	88	88	87	85
5	100	93	89	86	98	93	88	85	91	87	85	89	86	84	88	85	83	85	85	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	82	82	80	79
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	80	77	77	77	77	76
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	77	77	75	73
9	87	80	76	73	86	80	75	73	79	75	72	78	75	72	77	74	72	77	74	72	71
10	85	77	73	70	84	77	73	70	76	72	70	76	72	70	75	72	70	75	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	243678	243678	243678
5°	241566	243087	244246
10°	234688	234251	237923
15°	204169	207450	209999
20°	133993	136614	138373
25°	47773	50566	47526
30°	10421	14080	10500
35°	3343	5824	3259
40°	1034	1799	944
45°	97	609	97
50°	0	107	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 609 cd/sqm



TEST NUMBER: P1313385

CATALOG NUMBER: LDSQA3D05R409727DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.3	22.2
10°-20°	308.2	51.8
20°-30°	138.2	23.2
30°-40°	14.9	2.5
40°-50°	1.4	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	578.7	97.3
0°-40°	593.6	99.8
0°-60°	595.0	100.0
0°-90°	595.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	595.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1415	1415	1415	1415	1415	
5°	1397	1401	1406	1408	1413	132
15°	1145	1154	1164	1170	1178	304
25°	251	259	266	271	250	134
35°	16	18	28	18	16	12
45°	0	1	2	1	0	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1313385

CATALOG NUMBER: LDSQA3D05R409727DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1414.9	1414.9	1414.9	1414.9	1414.9
1°	1412.0	1414.9	1417.4	1415.3	1418.3
2°	1410.7	1414.1	1417.9	1415.8	1418.3
3°	1407.4	1411.6	1415.8	1414.5	1417.0
4°	1402.8	1406.1	1412.4	1412.4	1416.2
5°	1397.3	1401.1	1406.1	1408.2	1412.8
6°	1391.5	1393.6	1397.3	1401.5	1407.8
7°	1383.9	1383.9	1388.5	1392.7	1401.1
8°	1373.4	1372.6	1376.0	1381.4	1388.9
9°	1360.5	1357.5	1360.0	1368.0	1379.3
10°	1342.0	1339.5	1339.5	1349.6	1360.5
11°	1318.1	1317.3	1317.7	1327.4	1342.0
12°	1285.9	1286.7	1286.7	1297.6	1315.6
13°	1249.4	1249.0	1252.8	1264.9	1277.1
14°	1205.0	1207.5	1211.3	1222.2	1234.8
15°	1145.1	1153.5	1163.5	1170.2	1177.8
17.5°	962.8	971.2	985.0	990.5	992.2
20°	731.1	743.3	745.4	756.3	755.0
22.5°	490.2	489.4	491.1	492.3	492.7
25°	251.4	258.9	266.1	270.7	250.1
27.5°	109.4	122.3	131.6	119.4	110.6
30°	52.4	59.5	70.8	59.9	52.8
32.5°	28.5	33.1	44.8	32.7	28.1
35°	15.9	18.4	27.7	18.0	15.5
37.5°	9.2	10.1	15.1	10.1	8.8
40°	4.6	5.9	8.0	5.9	4.2
42.5°	1.7	2.9	4.2	2.9	1.7
45°	0.4	0.8	2.5	0.8	0.4
47.5°	0.0	0.0	1.3	0.0	0.0
50°	0.0	0.0	0.4	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1313385
CATALOG NUMBER: LDSQA3D05R409727DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)