

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1313391

Luminaire Tested: LDSQA3D05R459727DE010 3LSQCA45R 1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1313391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-84)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R459727DE010 3LSQCA45R 1MMS
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 97CRI , 3LSQCA45R 1MMS TRII
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 507.0 lumens
Efficiency: N/A
Efficacy: 70.4 lumens/watt
Spacing Criteria (0/90/45): 3.81 / 0.82 / 1.83
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1313391
CATALOG NUMBER: LDSQA3D05R459727DE010 3LSQCA45R 1MMS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1313391

CATALOG NUMBER: LDSQA3D05R459727DE010 3LSQCA45R 1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	88	88	88	86
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	75	75	73
3	91	81	73	67	89	80	72	66	77	70	65	74	69	64	71	67	63	63	63	63	61
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	53	53	53	51
5	76	63	53	47	73	61	53	46	59	52	46	57	51	45	55	50	45	45	45	45	43
6	69	55	46	39	67	54	46	39	52	45	39	51	44	39	49	43	38	38	38	38	36
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	33	33	33	31
8	58	44	35	29	56	43	35	29	42	34	29	40	33	28	39	33	28	28	28	28	26
9	53	39	31	25	52	39	30	25	38	30	25	36	29	25	35	29	24	24	24	24	22
10	49	36	27	22	48	35	27	22	34	27	21	33	26	21	32	26	21	21	21	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	5046	5046	5046	5046	5046
5°	6016	5584	4996	4633	4633
10°	9601	6523	4687	4389	4389
15°	23910	8737	4261	4101	4261
20°	62955	13049	3684	3922	4142
25°	126406	19345	3192	3668	4067
30°	186357	25912	2585	3580	4156
35°	235075	30380	2208	3532	4310
40°	250810	30711	1978	3665	4609
45°	260584	25598	1827	3970	4993
50°	260188	17844	1795	4260	5600
55°	221142	7927	1892	4774	6155
60°	148628	1584	1860	5339	7061
65°	39447	693	1875	5787	8028
70°	1057	856	1913	6345	9064
75°	865	865	1930	6721	10314
80°	793	1289	2083	7042	11604
85°	790	1581	3359	7509	11659

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 10°
 Vertical Angle: 47.5°
 Luminance: 267311 cd/sqm



TEST NUMBER: P1313391

CATALOG NUMBER: LDSQA3D05R459727DE010 3LSQCA45R 1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2.9	0.6
10°-20°	14.3	2.8
20°-30°	59.0	11.6
30°-40°	124.3	24.5
40°-50°	153.4	30.2
50°-60°	114.9	22.7
60°-70°	29.6	5.8
70°-80°	6.1	1.2
80°-90°	2.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	76.2	15.0
0°-40°	200.5	39.5
0°-60°	468.8	92.5
0°-90°	507.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	507.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	29	29	29	29	29	
5°	35	32	29	27	27	4
15°	134	49	24	23	24	49
25°	665	102	17	19	21	310
35°	1118	144	10	17	20	681
45°	1070	105	8	16	20	819
55°	736	26	6	16	20	636
65°	97	2	5	14	20	140
75°	1	1	3	10	16	2
85°	0	1	2	4	6	0
90°	0	0	0	0	0	



TEST NUMBER: P1313391
 CATALOG NUMBER: LDSQA3D05R459727DE010 3LSQCA45R 1MMS

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
0°	29.3	29.3	29.3	29.3	29.3	29.3	29.3	29.3	29.3	29.3	29.3
2.5°	31.0	31.0	31.0	31.0	31.0	31.0	31.0	30.6	30.2	29.3	28.5
5°	34.8	34.4	34.4	34.4	33.9	33.5	33.5	32.3	30.6	28.9	27.6
7.5°	41.1	41.1	40.6	39.8	39.4	38.5	37.7	34.4	30.6	28.1	26.4
10°	54.9	54.0	52.8	51.9	49.9	46.9	44.8	37.3	30.2	26.8	25.6
12.5°	82.1	83.8	79.6	75.4	69.5	64.1	57.4	42.3	30.2	25.6	24.3
15°	134.1	137.0	129.0	120.6	106.4	93.0	80.4	49.0	29.3	23.9	22.6
17.5°	219.1	222.9	209.5	189.8	167.6	140.8	117.7	58.2	28.5	22.2	21.4
20°	343.5	343.1	317.1	292.4	249.7	210.3	167.1	71.2	27.2	20.1	20.1
22.5°	496.4	498.1	466.3	421.9	361.1	297.9	229.2	86.3	25.6	18.4	18.9
25°	665.2	651.0	613.3	559.3	481.8	394.2	303.7	101.8	23.9	16.8	17.6
27.5°	806.0	792.2	749.0	684.9	601.6	497.7	379.5	117.3	21.8	15.1	16.3
30°	937.1	919.5	867.6	795.1	695.8	583.6	450.8	130.3	19.3	13.0	15.1
32.5°	1045.2	1029.3	970.2	886.0	777.9	657.3	511.1	140.3	16.8	11.7	14.2
35°	1118.1	1101.8	1047.3	954.7	837.0	710.9	560.1	144.5	14.7	10.5	13.8
37.5°	1134.9	1126.1	1087.1	1000.4	877.6	745.3	591.5	143.3	12.1	9.6	13.0
40°	1115.6	1117.7	1099.3	1027.2	899.4	759.9	604.5	136.6	10.1	8.8	12.6
42.5°	1090.9	1096.3	1095.1	1038.1	908.6	760.8	599.1	123.2	8.0	8.0	12.1
45°	1069.9	1075.4	1082.9	1033.5	902.4	749.9	581.9	105.1	5.9	7.5	12.1
47.5°	1031.8	1037.7	1048.6	996.6	870.5	721.8	550.9	85.5	4.2	7.1	11.7
50°	971.1	974.0	971.1	912.8	809.4	676.6	500.6	66.6	2.9	6.7	11.7
52.5°	908.6	902.8	878.5	804.7	712.2	604.9	437.4	47.3	2.1	6.3	11.3
55°	736.5	727.2	709.2	664.0	611.2	516.9	353.6	26.4	2.1	6.3	10.9
57.5°	513.2	518.2	524.5	515.3	491.0	407.2	268.5	11.7	2.1	5.9	10.9
60°	431.5	427.3	427.7	421.9	381.6	297.0	184.7	4.6	2.1	5.4	10.5
62.5°	257.6	260.6	266.0	267.3	227.5	165.9	96.8	2.1	2.1	5.0	10.1
65°	96.8	101.4	88.8	77.1	61.2	44.8	22.6	1.7	2.5	4.6	9.2
67.5°	2.9	3.4	4.2	3.8	3.8	3.4	2.5	1.7	2.5	4.2	8.8
70°	2.1	2.1	2.1	2.1	2.1	1.7	1.7	1.7	2.1	3.8	8.0
72.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.1	3.4	7.1
75°	1.3	1.7	1.3	1.3	1.3	1.3	1.3	1.3	2.1	2.9	5.9
77.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.7	2.5	5.0
80°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	1.3	1.7	2.1	4.2
82.5°	0.8	0.8	0.8	0.4	0.8	0.8	0.8	0.8	1.7	1.7	3.4
85°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.8	1.3	1.7	2.1
87.5°	0.0	0.0	0.0	0.0	0.4	0.4	0.4	0.8	1.3	1.3	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1313391
 CATALOG NUMBER: LDSQA3D05R459727DE010 3LSQCA45R 1MMS

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
0°	29.3	29.3	29.3
2.5°	27.6	27.6	27.6
5°	26.8	26.8	26.8
7.5°	26.0	26.0	26.0
10°	25.1	25.1	25.1
12.5°	24.3	24.3	24.7
15°	23.0	23.9	23.9
17.5°	22.2	23.0	23.5
20°	21.4	22.2	22.6
22.5°	20.1	21.4	22.2
25°	19.3	20.9	21.4
27.5°	18.4	20.5	21.4
30°	18.0	20.1	20.9
32.5°	17.2	19.7	20.5
35°	16.8	19.7	20.5
37.5°	16.8	19.3	20.5
40°	16.3	19.3	20.5
42.5°	16.3	19.3	20.5
45°	16.3	19.3	20.5
47.5°	15.9	19.3	20.9
50°	15.9	19.7	20.9
52.5°	15.9	19.7	20.9
55°	15.9	19.7	20.5
57.5°	15.5	19.3	20.5
60°	15.5	19.3	20.5
62.5°	14.7	18.9	20.1
65°	14.2	18.4	19.7
67.5°	13.4	18.0	18.9
70°	12.6	16.8	18.0
72.5°	11.3	15.9	17.2
75°	10.1	14.7	15.5
77.5°	8.8	13.0	13.8
80°	7.1	10.9	11.7
82.5°	5.4	8.4	8.8
85°	3.8	5.4	5.9
87.5°	1.7	2.5	2.9
90°	0.0	0.0	0.0

(END OF REPORT)