

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1313421

Luminaire Tested: LDSQA3D05R609727DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1313421
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R609727DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 97CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 526.0 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.93 / 0.9
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1313421
CATALOG NUMBER: LDSQA3D05R609727DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1313421

CATALOG NUMBER: LDSQA3D05R609727DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	97	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82	82	82	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77
5	93	85	80	76	92	84	79	75	83	78	75	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67	67	67	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	102231	102231	102231
5°	96813	97314	97470
10°	100503	100346	100940
15°	102165	102022	102771
20°	90410	90410	90556
25°	77474	75175	75802
30°	61986	59719	60654
35°	38454	39253	38370
40°	16884	18570	17356
45°	195	6016	511
50°	0	670	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 6016 cd/sqm



TEST NUMBER: P1313421

CATALOG NUMBER: LDSQA3D05R609727DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	10.3
10°-20°	157.1	29.9
20°-30°	182.4	34.7
30°-40°	114.9	21.8
40°-50°	17.2	3.3
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	393.8	74.9
0°-40°	508.7	96.7
0°-60°	526.0	100.0
0°-90°	526.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	526.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	594	594	594	594	594	
5°	560	562	563	564	564	54
15°	573	571	572	576	576	157
25°	408	403	396	397	399	185
35°	183	183	187	183	182	114
45°	1	8	25	10	2	11
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1313421

CATALOG NUMBER: LDSQA3D05R609727DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	593.6	593.6	593.6	593.6	593.6
1°	588.9	590.6	590.6	591.0	590.6
2°	581.0	583.5	583.5	584.7	583.9
3°	573.0	575.1	575.5	577.2	576.8
4°	564.2	567.5	568.8	569.6	569.2
5°	560.0	562.1	562.9	564.2	563.8
6°	558.3	560.0	560.8	562.1	562.1
7°	559.6	560.8	562.1	562.9	562.1
8°	563.3	564.6	564.6	566.3	565.0
9°	568.8	569.2	569.2	571.3	570.1
10°	574.7	573.8	573.8	576.8	577.2
11°	579.7	578.9	578.5	581.4	582.2
12°	582.6	581.0	581.0	584.7	585.2
13°	583.1	581.0	581.0	584.7	586.0
14°	579.7	577.2	577.6	581.8	583.1
15°	573.0	570.9	572.2	575.9	576.4
17.5°	541.1	539.9	540.7	543.2	543.6
20°	493.3	492.5	493.3	493.3	494.1
22.5°	445.9	443.8	439.6	442.1	442.5
25°	407.7	403.1	395.6	397.2	398.9
27.5°	365.8	359.9	351.9	354.0	354.5
30°	311.7	308.7	300.3	302.4	305.0
32.5°	240.8	248.7	243.7	243.3	243.7
35°	182.9	183.3	186.7	182.9	182.5
37.5°	127.9	128.4	130.9	126.7	127.1
40°	75.1	80.5	82.6	81.0	77.2
42.5°	23.5	41.5	47.0	40.7	26.0
45°	0.8	8.0	24.7	10.5	2.1
47.5°	0.0	0.4	11.7	0.8	0.0
50°	0.0	0.0	2.5	0.0	0.0
52.5°	0.0	0.0	0.4	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1313421
CATALOG NUMBER: LDSQA3D05R609727DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)