

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1313528

Luminaire Tested: LDSQA3D09R359727DE010 3LSQPHR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1313528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D09R359727DE010 3LSQPHR1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , 3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 711.0 lumens
Efficiency: N/A
Efficacy: 64.1 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1313528
CATALOG NUMBER: LDSQA3D09R359727DE010 3LSQPHR1MMS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1313528

CATALOG NUMBER: LDSQA3D09R359727DE010 3LSQPHR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	403432	403432	403432
5°	396501	395654	394807
10°	363382	352470	343900
15°	260208	251899	248851
20°	120650	124811	129191
25°	28637	40723	42471
30°	8412	9625	10838
35°	1934	3091	2838
40°	405	832	540
45°	146	146	146
50°	161	0	161
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 170 cd/sqm



TEST NUMBER: P1313528

CATALOG NUMBER: LDSQA3D09R359727DE010 3LSQPHR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.3	29.6
10°-20°	376.0	52.9
20°-30°	113.1	15.9
30°-40°	10.8	1.5
40°-50°	0.7	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.4	98.4
0°-40°	710.2	99.9
0°-60°	711.0	100.0
0°-90°	711.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	711.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2342	2342	2342	2342	2342	
5°	2294	2293	2289	2286	2284	213
15°	1459	1448	1413	1407	1396	385
25°	151	166	214	224	224	97
35°	9	12	15	16	14	8
45°	1	1	1	1	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1313528
 CATALOG NUMBER: LDSQA3D09R359727DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2342.5	2342.5	2342.5	2342.5	2342.5
1°	2341.3	2341.3	2340.0	2340.0	2337.6
2°	2335.8	2336.4	2333.9	2333.3	2331.5
3°	2327.2	2325.4	2325.4	2324.1	2322.9
4°	2313.7	2310.0	2308.8	2309.4	2307.0
5°	2293.5	2292.9	2288.6	2285.5	2283.7
6°	2271.5	2267.2	2258.0	2250.0	2248.2
7°	2238.4	2229.2	2221.2	2204.7	2202.3
8°	2198.0	2183.3	2166.1	2142.9	2141.6
9°	2148.4	2124.5	2100.6	2069.4	2058.3
10°	2077.9	2055.9	2015.5	1987.9	1966.5
11°	1990.4	1962.8	1915.6	1882.6	1864.8
12°	1891.1	1865.4	1810.3	1780.3	1755.2
13°	1763.8	1742.3	1690.9	1657.8	1638.2
14°	1616.2	1600.2	1551.3	1536.6	1529.8
15°	1459.4	1448.4	1412.8	1406.7	1395.7
17.5°	1074.2	1055.8	1035.6	1039.3	1042.9
20°	658.3	684.1	681.0	694.5	704.9
22.5°	328.3	361.3	399.9	423.2	434.8
25°	150.7	166.0	214.3	223.5	223.5
27.5°	75.9	79.6	101.0	102.9	107.8
30°	42.3	45.3	48.4	53.9	54.5
32.5°	21.4	25.1	26.3	29.4	28.2
35°	9.2	12.2	14.7	15.9	13.5
37.5°	4.3	5.5	8.0	7.3	5.5
40°	1.8	2.4	3.7	3.1	2.4
42.5°	1.2	1.2	1.8	1.2	1.2
45°	0.6	0.6	0.6	0.6	0.6
47.5°	0.6	0.6	0.0	0.6	0.6
50°	0.6	0.0	0.0	0.0	0.6
52.5°	0.6	0.0	0.0	0.0	0.6
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1313528
CATALOG NUMBER: LDSQA3D09R359727DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)