

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1312406

Luminaire Tested: LDSQA3D09R359050DE010 3LSQCDR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1312406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D09R359050DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R35 optic, 5000K CCT AND, 90CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1009.0 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.58 / 0.52
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1312406
CATALOG NUMBER: LDSQA3D09R359050DE010 3LSQCDR1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1312406
 CATALOG NUMBER: LDSQA3D09R359050DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96	96
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	96	94	93	93	93	93
3	107	102	99	96	105	101	98	95	99	96	94	96	94	92	94	92	91	89	89	89	89
4	104	98	94	91	102	97	93	90	95	92	89	93	91	88	92	89	87	86	86	86	86
5	100	94	90	87	99	93	90	87	92	88	86	90	87	85	89	86	84	83	83	83	83
6	97	91	86	83	96	90	86	83	89	85	83	88	84	82	86	84	82	80	80	80	80
7	94	88	83	80	93	87	83	80	86	82	80	85	82	79	84	81	79	78	78	78	78
8	91	85	80	77	91	84	80	77	83	80	77	82	79	77	81	79	76	75	75	75	75
9	89	82	78	75	88	81	77	75	81	77	74	80	77	74	79	76	74	73	73	73	73
10	86	79	75	72	85	79	75	72	78	75	72	78	74	72	77	74	72	71	71	71	71

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	521921	521921	521921
5°	506090	509669	512435
10°	462469	472244	480359
15°	332579	347111	349963
20°	169310	177814	178254
25°	64229	65597	63792
30°	24958	28915	24321
35°	8578	13435	8073
40°	2878	5216	2698
45°	195	1754	195
50°	0	214	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 1754 cd/sqm



TEST NUMBER: P1312406

CATALOG NUMBER: LDSQA3D09R359050DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.3	27.2
10°-20°	511.1	50.7
20°-30°	183.7	18.2
30°-40°	35.9	3.6
40°-50°	4.0	0.4
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	969.1	96.0
0°-40°	1005.0	99.6
0°-60°	1009.0	100.0
0°-90°	1009.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1009.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3030	3030	3030	3030	3030	
5°	2927	2935	2948	2962	2964	271
15°	1865	1896	1947	1960	1963	496
25°	338	341	345	343	336	177
35°	41	46	64	47	38	30
45°	1	2	7	2	1	2
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1312406
 CATALOG NUMBER: LDSQA3D09R359050DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3030.5	3030.5	3030.5	3030.5	3030.5
1°	3021.7	3025.7	3026.5	3032.1	3025.7
2°	3008.9	3011.3	3014.5	3019.3	3016.1
3°	2984.1	2988.9	2996.1	3002.5	3002.5
4°	2957.7	2964.1	2972.9	2984.1	2983.3
5°	2927.4	2935.4	2948.1	2961.7	2964.1
6°	2889.0	2898.6	2919.4	2938.6	2941.8
7°	2848.3	2862.6	2882.6	2910.6	2917.8
8°	2800.3	2811.5	2840.3	2873.0	2881.0
9°	2730.0	2746.8	2783.5	2813.9	2818.7
10°	2644.5	2656.4	2700.4	2732.4	2746.8
11°	2534.2	2551.8	2594.9	2627.7	2637.3
12°	2393.5	2419.1	2469.4	2493.4	2501.4
13°	2241.7	2263.3	2302.4	2332.0	2338.4
14°	2070.7	2091.4	2132.2	2156.2	2150.6
15°	1865.3	1896.4	1946.8	1960.4	1962.8
17.5°	1377.8	1397.8	1442.5	1464.1	1479.3
20°	923.8	943.0	970.2	984.6	972.6
22.5°	561.8	577.8	592.2	591.4	587.4
25°	338.0	341.2	345.2	342.8	335.7
27.5°	197.4	206.2	218.2	210.2	198.2
30°	125.5	132.7	145.4	131.9	122.3
32.5°	66.3	83.9	97.5	79.1	69.5
35°	40.8	46.4	63.9	47.2	38.4
37.5°	24.8	28.8	40.0	28.0	22.4
40°	12.8	18.4	23.2	16.8	12.0
42.5°	4.0	8.8	12.8	8.0	4.0
45°	0.8	2.4	7.2	2.4	0.8
47.5°	0.0	0.0	3.2	0.8	0.0
50°	0.0	0.0	0.8	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1312406
CATALOG NUMBER: LDSQA3D09R359050DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)