

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1313542

Luminaire Tested: LDSQA3D09R409727DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1313542
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D09R409727DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 97CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 870.0 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.69 / 0.6
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1313542
CATALOG NUMBER: LDSQA3D09R409727DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1313542

CATALOG NUMBER: LDSQA3D09R409727DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	94	94	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	90	90	90	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	87	87	87	87	85
5	100	93	89	86	98	93	88	85	91	87	85	89	86	84	88	85	83	83	83	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	80	80	80	79
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	80	77	77	77	77	76
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	75	75	75	73
9	87	80	76	73	86	80	75	73	79	75	72	78	75	72	77	74	72	72	72	72	71
10	85	77	73	70	84	77	73	70	76	72	70	76	72	70	75	72	70	70	70	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	356311	356311	356311
5°	353229	355442	357137
10°	343166	342519	347870
15°	298524	303338	307047
20°	195940	199752	202336
25°	69854	73920	69493
30°	15233	20583	15352
35°	4899	8494	4773
40°	1506	2608	1371
45°	146	901	146
50°	0	161	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 901 cd/sqm



TEST NUMBER: P1313542

CATALOG NUMBER: LDSQA3D09R409727DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.5	22.2
10°-20°	450.6	51.8
20°-30°	202.1	23.2
30°-40°	21.8	2.5
40°-50°	2.0	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	846.1	97.3
0°-40°	868.0	99.8
0°-60°	870.0	100.0
0°-90°	870.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	870.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2069	2069	2069	2069	2069	
5°	2043	2049	2056	2059	2066	193
15°	1674	1687	1701	1711	1722	445
25°	368	379	389	396	366	196
35°	23	27	40	26	23	18
45°	1	1	4	1	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1313542

CATALOG NUMBER: LDSQA3D09R409727DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2068.9	2068.9	2068.9	2068.9	2068.9
1°	2064.6	2068.9	2072.6	2069.5	2073.8
2°	2062.8	2067.7	2073.2	2070.1	2073.8
3°	2057.9	2064.0	2070.1	2068.3	2071.9
4°	2051.1	2056.0	2065.2	2065.2	2070.7
5°	2043.2	2048.7	2056.0	2059.1	2065.8
6°	2034.6	2037.6	2043.2	2049.3	2058.5
7°	2023.5	2023.5	2030.3	2036.4	2048.7
8°	2008.2	2007.0	2011.9	2019.9	2030.9
9°	1989.2	1985.0	1988.6	2000.3	2016.8
10°	1962.3	1958.6	1958.6	1973.3	1989.2
11°	1927.4	1926.1	1926.8	1940.8	1962.3
12°	1880.2	1881.4	1881.4	1897.3	1923.7
13°	1826.9	1826.3	1831.8	1849.6	1867.3
14°	1762.0	1765.6	1771.1	1787.1	1805.4
15°	1674.3	1686.6	1701.3	1711.1	1722.1
17.5°	1407.8	1420.1	1440.3	1448.3	1450.7
20°	1069.1	1086.8	1089.9	1105.8	1104.0
22.5°	716.8	715.6	718.0	719.9	720.5
25°	367.6	378.6	389.0	395.8	365.7
27.5°	159.9	178.9	192.4	174.6	161.7
30°	76.6	87.0	103.5	87.6	77.2
32.5°	41.7	48.4	65.6	47.8	41.0
35°	23.3	27.0	40.4	26.3	22.7
37.5°	13.5	14.7	22.1	14.7	12.9
40°	6.7	8.6	11.6	8.6	6.1
42.5°	2.5	4.3	6.1	4.3	2.5
45°	0.6	1.2	3.7	1.2	0.6
47.5°	0.0	0.0	1.8	0.0	0.0
50°	0.0	0.0	0.6	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1313542
CATALOG NUMBER: LDSQA3D09R409727DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)