

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1313214

Luminaire Tested: LDSQA3D02R409727DE010 3LSQCA45R 1MMS

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1313214  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-78)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D02R409727DE010 3LSQCA45R 1MMS  
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 97CRI , 3LSQCA45R 1MMS TRII  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 222.0 lumens  
Efficiency: N/A  
Efficacy: 61.7 lumens/watt  
Spacing Criteria (0/90/45): 3.99 / 0.73 / 1.55  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1313214  
CATALOG NUMBER: LDSQA3D02R409727DE010 3LSQCA45R 1MMS

### Luminous Intensity Polar Plot



— 0°-180°    - - - 45°-225°    ····· 90°-270°



TEST NUMBER: P1313214  
 CATALOG NUMBER: LDSQA3D02R409727DE010 3LSQCA45R 1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86					86			
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72					72			
3	91	81	73	66	89	79	72	66	76	70	65	73	68	64	71	66	62	60					60			
4	82	70	62	55	80	69	61	54	67	59	54	64	58	53	62	57	52	50					50			
5	75	62	52	46	73	60	52	45	58	51	45	56	50	44	54	49	44	42					42			
6	68	54	45	38	66	53	44	38	51	43	38	50	43	37	48	42	37	35					35			
7	62	48	39	32	60	47	38	32	45	37	32	44	37	31	42	36	31	29					29			
8	57	42	33	27	55	42	33	27	40	32	27	39	32	27	38	31	26	24					24			
9	52	38	29	23	51	37	29	23	36	28	23	35	28	23	34	27	23	21					21			
10	48	34	25	20	47	33	25	20	32	25	20	31	24	20	30	24	19	18					18			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	1963	1963	1963	1963	1963
5°	2178	2109	1936	1763	1729
10°	2641	2238	1784	1609	1574
15°	4333	2443	1533	1426	1462
20°	11436	2877	1265	1265	1375
25°	44086	3573	1007	1159	1349
30°	95117	4753	815	1134	1332
35°	143156	5614	694	1114	1367
40°	161286	5643	607	1147	1461
45°	172952	4360	536	1193	1583
50°	170002	2733	482	1259	1742
55°	149560	1351	480	1411	1952
60°	94654	276	551	1550	2170
65°	19357	82	571	1671	2404
70°	403	101	604	1863	2769
75°	399	266	665	2063	3127
80°	397	198	793	2182	3670
85°	395	395	1581	2371	3952

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 47°  
 Luminance: 176087 cd/sqm



TEST NUMBER: P1313214

CATALOG NUMBER: LDSQA3D02R409727DE010 3LSQCA45R 1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1.1	0.5
10°-20°	3.5	1.6
20°-30°	17.2	7.8
30°-40°	56.1	25.3
40°-50°	77.3	34.8
50°-60°	53.9	24.3
60°-70°	10.2	4.6
70°-80°	1.8	0.8
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	21.8	9.8
0°-40°	77.9	35.1
0°-60°	209.1	94.2
0°-90°	222.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	222.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	11	11	11	11	11	
5°	13	12	11	10	10	1
15°	24	14	9	8	8	9
25°	232	19	5	6	7	119
35°	681	27	3	5	6	411
45°	710	18	2	5	6	540
55°	498	4	2	5	6	426
65°	48	0	1	4	6	84
75°	1	0	1	3	5	1
85°	0	0	1	1	2	0
90°	0	0	0	0	0	



TEST NUMBER: P1313214  
 CATALOG NUMBER: LDSQA3D02R409727DE010 3LSQCA45R 1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	45°	67.5°	90°
0°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4
2.5°	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.6	11.4
5°	12.6	12.6	12.6	12.6	12.4	12.4	12.4	12.2	12.2	11.8	11.2
7.5°	13.5	13.5	13.5	13.5	13.3	13.0	12.8	12.8	12.6	11.6	10.8
10°	15.1	15.1	14.9	14.7	14.5	14.1	13.9	13.5	12.8	11.4	10.2
12.5°	18.3	17.9	17.7	17.3	16.7	15.9	15.1	14.5	13.0	11.0	9.6
15°	24.3	23.9	23.0	21.8	20.6	19.0	17.5	16.1	13.7	10.4	8.6
17.5°	34.7	33.4	32.2	30.2	27.1	24.3	21.2	18.6	14.5	9.8	7.7
20°	62.4	61.6	54.2	48.5	39.3	32.8	26.7	22.2	15.7	9.2	6.9
22.5°	128.6	120.1	108.1	88.5	68.9	50.8	36.9	27.9	16.9	8.4	6.1
25°	232.0	218.6	192.7	154.9	114.4	80.9	53.4	36.5	18.8	7.5	5.3
27.5°	351.3	337.6	297.5	245.5	179.2	122.1	76.2	48.3	21.2	6.7	4.7
30°	478.3	466.7	415.7	343.7	252.6	171.1	102.1	60.3	23.9	5.9	4.1
31°	529.5	514.6	459.5	382.9	287.1	191.2	112.5	65.4	24.9	5.7	3.9
32°	576.6	559.6	502.6	420.4	315.0	213.1	124.0	69.9	25.7	5.3	3.7
33°	617.1	597.4	542.3	455.9	345.8	233.4	135.8	74.2	26.3	4.9	3.5
34°	651.6	634.5	575.3	491.5	373.1	253.0	147.4	78.5	26.7	4.7	3.3
35°	680.9	665.5	606.9	518.7	399.8	272.0	158.0	82.6	26.7	4.3	3.3
36°	700.7	687.3	634.3	546.4	422.2	288.1	167.0	86.2	26.7	3.9	3.1
37°	711.5	698.5	652.2	569.2	444.2	304.0	175.1	89.1	26.5	3.7	2.9
38°	717.0	705.6	665.5	587.8	459.5	315.4	182.3	91.3	26.3	3.3	2.9
39°	718.5	708.9	673.8	601.2	474.4	326.8	187.4	92.6	25.7	3.1	2.7
40°	717.4	709.1	678.3	613.3	485.8	335.8	191.0	93.0	25.1	2.7	2.7
41°	715.4	708.9	681.6	621.6	495.0	341.5	192.5	92.2	24.3	2.2	2.4
42°	713.6	706.4	683.0	627.3	501.3	344.3	192.3	90.5	23.0	2.0	2.4
43°	713.6	705.4	683.2	631.0	504.4	344.6	189.8	87.5	21.4	1.8	2.2
44°	712.3	704.8	684.2	633.4	505.2	342.7	185.9	84.2	19.6	1.6	2.2
45°	710.1	702.1	684.0	633.6	503.8	338.2	179.6	79.9	17.9	1.2	2.2
46°	705.8	698.7	682.2	632.2	499.5	331.7	172.1	75.6	16.1	1.0	2.0
47°	697.3	691.8	677.3	627.3	493.0	322.1	163.1	70.7	14.7	0.8	2.0
48°	682.6	678.7	668.9	616.5	480.5	310.3	153.5	65.4	13.3	0.8	2.0
49°	655.7	652.6	646.9	599.2	464.6	295.8	143.1	59.5	11.8	0.6	2.0
50°	634.5	631.2	619.6	570.0	441.8	277.5	131.7	53.6	10.2	0.4	1.8
51°	620.4	615.1	596.7	536.2	408.6	253.0	119.3	47.7	8.6	0.4	1.8
52°	602.7	594.7	571.9	505.8	378.2	228.5	105.8	41.8	7.5	0.4	1.8
53°	565.6	562.7	540.1	473.2	347.8	205.1	91.9	36.9	6.5	0.4	1.8
54°	533.1	528.9	498.1	427.9	314.8	179.0	77.7	32.6	5.5	0.4	1.8
55°	498.1	489.7	462.4	389.8	276.0	154.9	64.0	28.1	4.5	0.4	1.6
56°	453.8	446.5	417.1	349.0	240.4	130.5	53.6	23.0	3.5	0.4	1.6
57°	400.0	393.3	370.6	298.9	203.3	106.6	43.6	18.6	2.7	0.4	1.6
58°	348.0	340.5	314.6	250.8	164.1	84.6	36.5	15.1	2.0	0.4	1.6
59°	308.1	297.9	264.4	210.6	128.4	64.2	29.0	12.0	1.4	0.4	1.6
60°	274.8	266.5	231.8	175.3	100.7	47.3	21.4	9.2	0.8	0.4	1.6
62.5°	159.2	157.0	125.8	90.3	47.5	22.0	10.6	4.3	0.4	0.6	1.6
65°	47.5	41.4	32.2	19.2	12.2	7.3	3.9	1.4	0.2	0.6	1.4



TEST NUMBER: P1313214  
 CATALOG NUMBER: LDSQA3D02R409727DE010 3LSQCA45R 1MMS

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	45°	67.5°	90°
67.5°	1.4	1.4	1.4	1.4	1.4	1.4	0.8	0.4	0.2	0.6	1.4
70°	0.8	0.6	0.6	0.6	0.6	0.4	0.4	0.2	0.2	0.6	1.2
72.5°	0.6	0.6	0.6	0.6	0.4	0.4	0.4	0.2	0.4	0.6	1.0
75°	0.6	0.4	0.4	0.4	0.4	0.2	0.2	0.2	0.4	0.6	1.0
77.5°	0.4	0.4	0.4	0.4	0.2	0.2	0.2	0.2	0.4	0.6	1.0
80°	0.4	0.4	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.6	0.8
82.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.6	0.8
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.6	0.8
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.2	0.2	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1313214  
 CATALOG NUMBER: LDSQA3D02R409727DE010 3LSQCA45R 1MMS

**CANDELA DISTRIBUTION (continued):**

	112.5°	135°	157.5°	180°
0°	11.4	11.4	11.4	11.4
2.5°	11.0	10.8	10.6	10.6
5°	10.6	10.2	10.2	10.0
7.5°	10.0	9.6	9.6	9.6
10°	9.4	9.2	9.2	9.0
12.5°	8.6	8.6	8.6	8.6
15°	8.0	8.0	8.2	8.2
17.5°	7.1	7.3	7.7	8.0
20°	6.5	6.9	7.3	7.5
22.5°	6.1	6.5	7.1	7.3
25°	5.5	6.1	6.9	7.1
27.5°	5.1	5.9	6.5	6.9
30°	4.7	5.7	6.3	6.7
31°	4.7	5.5	6.3	6.7
32°	4.5	5.3	6.3	6.5
33°	4.5	5.3	6.3	6.5
34°	4.3	5.3	6.1	6.5
35°	4.3	5.3	6.1	6.5
36°	4.1	5.1	6.1	6.5
37°	4.1	5.1	6.1	6.5
38°	3.9	5.1	6.1	6.5
39°	3.9	5.1	6.1	6.5
40°	3.9	5.1	6.1	6.5
41°	3.7	5.1	6.1	6.5
42°	3.7	5.1	6.1	6.5
43°	3.7	4.9	6.1	6.5
44°	3.7	4.9	6.1	6.5
45°	3.5	4.9	6.1	6.5
46°	3.5	4.9	6.1	6.5
47°	3.5	4.9	6.1	6.5
48°	3.5	4.9	6.1	6.5
49°	3.5	4.9	6.1	6.5
50°	3.3	4.7	6.1	6.5
51°	3.3	4.7	6.1	6.5
52°	3.3	4.7	6.1	6.5
53°	3.3	4.7	6.1	6.5
54°	3.1	4.7	6.1	6.5
55°	3.1	4.7	6.1	6.5
56°	3.1	4.7	6.1	6.3
57°	3.1	4.7	5.9	6.3
58°	3.1	4.5	5.9	6.3
59°	3.1	4.5	5.9	6.3
60°	3.1	4.5	5.9	6.3
62.5°	2.9	4.5	5.7	6.1
65°	2.7	4.1	5.7	5.9



TEST NUMBER: P1313214  
CATALOG NUMBER: LDSQA3D02R409727DE010 3LSQCA45R 1MMS

**CANDELA DISTRIBUTION (continued):**

	112.5°	135°	157.5°	180°
67.5°	2.7	3.9	5.3	5.7
70°	2.4	3.7	5.1	5.5
72.5°	2.0	3.5	4.7	5.1
75°	1.8	3.1	4.3	4.7
77.5°	1.6	2.7	3.9	4.1
80°	1.4	2.2	3.3	3.7
82.5°	1.0	1.6	2.7	2.9
85°	0.8	1.2	1.8	2.0
87.5°	0.6	0.6	1.0	1.0
90°	0.0	0.0	0.0	0.0

(END OF REPORT)