

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1313412

Luminaire Tested: LDSQA3D05R559727DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1313412
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R559727DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 97CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 546.0 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.81
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1313412
CATALOG NUMBER: LDSQA3D05R559727DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1313412
 CATALOG NUMBER: LDSQA3D05R559727DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	86	86	86	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	81	81	81	80
5	96	88	83	79	94	87	82	79	85	81	78	84	80	77	82	79	77	77	77	77	75
6	91	83	78	74	90	83	78	74	81	77	74	80	76	73	79	75	73	73	73	73	71
7	87	79	74	70	86	79	73	70	77	73	69	76	72	69	75	72	69	69	69	69	67
8	84	75	70	66	83	75	70	66	74	69	66	73	69	65	72	68	65	65	65	65	64
9	80	72	66	63	79	71	66	63	70	66	62	69	65	62	69	65	62	62	62	62	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	59	59	59	58

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	123690	123690	123690
5°	122278	121915	121258
10°	128169	126613	125738
15°	126039	124684	124238
20°	114804	115262	114877
25°	92106	93531	92106
30°	52858	54191	54608
35°	15075	18165	15516
40°	3867	5553	3957
45°	414	1948	317
50°	0	348	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 1948 cd/sqm



TEST NUMBER: P1313412

CATALOG NUMBER: LDSQA3D05R559727DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.2	12.5
10°-20°	194.6	35.6
20°-30°	214.3	39.3
30°-40°	64.0	11.7
40°-50°	4.9	0.9
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	477.1	87.4
0°-40°	541.1	99.1
0°-60°	546.0	100.0
0°-90°	546.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	546.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	718	718	718	718	718	
5°	707	706	705	702	701	69
15°	707	702	699	696	697	196
25°	485	485	492	491	485	212
35°	72	76	86	79	74	59
45°	2	4	8	4	1	3
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1313412
 CATALOG NUMBER: LDSQA3D05R559727DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	718.2	718.2	718.2	718.2	718.2
1°	717.8	717.8	716.9	716.5	717.8
2°	715.7	715.7	713.6	713.1	714.4
3°	711.1	710.6	709.0	707.7	708.5
4°	707.3	706.4	705.2	703.1	703.5
5°	707.3	706.0	705.2	702.2	701.4
6°	710.6	709.8	708.1	705.2	704.3
7°	716.5	714.8	713.1	709.4	708.5
8°	722.8	721.5	718.2	714.4	712.7
9°	729.1	726.1	722.0	718.2	717.8
10°	732.9	728.7	724.0	719.4	719.0
11°	732.4	728.7	723.2	719.0	718.6
12°	730.8	725.3	720.7	715.7	716.1
13°	724.9	719.9	715.2	711.5	710.6
14°	716.9	712.3	708.1	704.3	704.8
15°	706.9	701.8	699.3	696.4	696.8
17.5°	671.2	670.0	671.2	667.9	669.1
20°	626.4	625.1	628.9	627.2	626.8
22.5°	563.9	565.6	572.7	570.6	566.8
25°	484.7	484.7	492.2	491.4	484.7
27.5°	381.5	384.5	389.1	391.2	386.1
30°	265.8	272.5	272.5	276.7	274.6
32.5°	148.4	162.7	166.0	168.1	159.7
35°	71.7	76.3	86.4	78.8	73.8
37.5°	34.4	36.5	46.5	37.7	35.2
40°	17.2	19.7	24.7	20.5	17.6
42.5°	7.1	10.5	13.0	10.5	7.1
45°	1.7	4.2	8.0	4.2	1.3
47.5°	0.0	0.4	3.8	0.8	0.0
50°	0.0	0.0	1.3	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1313412

CATALOG NUMBER: LDSQA3D05R559727DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)