

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1313619

Luminaire Tested: LDSQA3D13R129727DE010 3LSQPHRLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1313619
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D13R129727DE010 3LSQPHRLD1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 2700K CCT AND, 97CRI , 3LSQPHRLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 950.0 lumens
Efficiency: N/A
Efficacy: 61.3 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1313619

CATALOG NUMBER: LDSQA3D13R129727DE010 3LSQPHRLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1313619

CATALOG NUMBER: LDSQA3D13R129727DE010 3LSQPHRLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	100	100	98
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	98	98	97
3	110	107	104	102	109	105	103	101	103	101	99	101	99	98	99	98	96	96	96	95
4	108	104	101	98	107	103	100	98	101	99	97	99	97	96	98	96	95	95	95	94
5	106	102	98	96	105	101	98	96	99	97	95	98	96	94	97	95	93	93	93	92
6	104	99	96	94	103	99	96	94	98	95	93	96	94	93	95	93	92	92	92	91
7	102	98	94	92	101	97	94	92	96	93	92	95	93	91	94	92	91	91	91	90
8	101	96	93	91	100	95	93	90	95	92	90	94	92	90	93	91	90	90	90	89
9	99	94	91	89	98	94	91	89	93	91	89	93	90	89	92	90	88	88	88	88
10	98	93	90	88	97	93	90	88	92	90	88	91	89	88	91	89	87	87	87	87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2410394
5°	1557429
10°	439420
15°	124238
20°	51959
25°	23012
30°	11753
35°	6202
40°	2653
45°	731
50°	804
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 804 cd/sqm

TEST NUMBER: P1313619

CATALOG NUMBER: LDSQA3D13R129727DE010 3LSQPHRLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	634.7	66.8
10°-20°	230.3	24.2
20°-30°	61.7	6.5
30°-40°	19.4	2.0
40°-50°	3.7	0.4
50°-60°	0.3	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	926.7	97.5
0°-40°	946.1	99.6
0°-60°	950.0	100.0
0°-90°	950.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	950.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13996	
5°	9009	635
15°	697	230
25°	121	62
35°	30	19
45°	3	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1313619

CATALOG NUMBER: LDSQA3D13R129727DE010 3LSQPHRLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	13995.8
1°	13759.5
2°	13095.2
3°	11958.4
4°	10547.0
5°	9008.7
6°	7405.3
7°	5970.3
8°	4594.4
9°	3419.2
10°	2512.7
11°	1851.3
12°	1393.7
13°	1080.7
14°	856.3
15°	696.8
17.5°	442.9
20°	283.5
22.5°	183.1
25°	121.1
27.5°	82.7
30°	59.1
32.5°	41.3
35°	29.5
37.5°	20.7
40°	11.8
42.5°	5.9
45°	3.0
47.5°	3.0
50°	3.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1313619

CATALOG NUMBER: LDSQA3D13R129727DE010 3LSQPHRLD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)