

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1313680

Luminaire Tested: LDSQA3D13R309727DE010 3LSQPHR1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1313680
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D13R309727DE010 3LSQPHR1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 97CRI , 3LSQPHR1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 944.0 lumens
Efficiency: N/A
Efficacy: 64.7 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.49 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1313680
CATALOG NUMBER: LDSQA3D13R309727DE010 3LSQPHR1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1313680

CATALOG NUMBER: LDSQA3D13R309727DE010 3LSQPHR1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	99	99	99	97
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96	96	96	96	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	96	94	93	92
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	94	92	90	89
5	102	97	93	90	101	96	93	90	95	91	89	93	90	88	92	89	88	92	89	88	87
6	100	94	90	87	99	93	90	87	92	89	86	91	88	86	90	87	85	90	87	85	84
7	97	91	87	84	96	91	87	84	90	86	84	88	86	83	88	85	83	88	85	83	82
8	95	89	85	82	94	88	84	82	87	84	82	86	83	81	86	83	81	86	83	81	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	82	79	77	76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	670962	670962	670962
5°	653696	649184	643842
10°	551657	534729	526037
15°	332437	323165	329102
20°	112769	130217	150213
25°	20732	32476	38347
30°	7119	7935	8909
35°	2060	2565	2733
40°	540	922	742
45°	195	195	195
50°	214	0	214
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 226 cd/sqm



TEST NUMBER: P1313680

CATALOG NUMBER: LDSQA3D13R309727DE010 3LSQPHR1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	336.9	35.7
10°-20°	492.4	52.2
20°-30°	104.2	11.0
30°-40°	9.6	1.0
40°-50°	0.9	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	933.4	98.9
0°-40°	943.0	99.9
0°-60°	944.0	100.0
0°-90°	944.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	944.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3896	3896	3896	3896	3896	
5°	3781	3774	3755	3744	3724	341
15°	1864	1858	1812	1855	1846	492
25°	109	122	171	201	202	80
35°	10	12	12	15	13	8
45°	1	1	1	1	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1313680
 CATALOG NUMBER: LDSQA3D13R309727DE010 3LSQPHR1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3895.9	3895.9	3895.9	3895.9	3895.9
1°	3896.7	3892.7	3887.0	3895.1	3889.4
2°	3888.6	3878.8	3870.7	3878.8	3876.4
3°	3864.2	3856.0	3850.3	3854.4	3854.4
4°	3827.6	3818.6	3813.7	3814.5	3802.3
5°	3781.2	3773.8	3755.1	3743.7	3724.2
6°	3712.8	3694.9	3672.1	3653.4	3628.2
7°	3620.0	3592.4	3559.8	3527.2	3495.5
8°	3471.1	3458.1	3414.1	3392.1	3360.4
9°	3331.1	3299.4	3252.2	3216.4	3199.3
10°	3154.5	3107.3	3057.7	3029.2	3008.0
11°	2945.3	2897.3	2857.4	2815.9	2783.4
12°	2699.6	2658.9	2613.3	2585.6	2547.4
13°	2408.2	2402.5	2351.2	2342.3	2337.4
14°	2158.3	2135.6	2085.1	2098.9	2102.2
15°	1864.5	1858.0	1812.5	1854.8	1845.8
17.5°	1167.9	1170.3	1198.8	1265.5	1286.7
20°	615.3	634.0	710.5	791.1	819.6
22.5°	249.0	290.5	368.7	423.2	459.8
25°	109.1	122.1	170.9	201.0	201.8
27.5°	61.9	62.7	82.2	85.5	87.1
30°	35.8	36.6	39.9	42.3	44.8
32.5°	19.5	21.2	22.0	25.2	25.2
35°	9.8	12.2	12.2	14.6	13.0
37.5°	5.7	6.5	7.3	7.3	6.5
40°	2.4	3.3	4.1	4.1	3.3
42.5°	0.8	1.6	1.6	1.6	2.4
45°	0.8	0.8	0.8	0.8	0.8
47.5°	0.8	0.8	0.0	0.8	0.8
50°	0.8	0.0	0.0	0.0	0.8
52.5°	0.8	0.0	0.0	0.0	0.8
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1313680
CATALOG NUMBER: LDSQA3D13R309727DE010 3LSQPHR1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)