

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1314172

Luminaire Tested: LDSQA3D02R359730DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1314172
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R359730DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 276.0 lumens
Efficiency: N/A
Efficacy: 76.7 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.58 / 0.52
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1314172
CATALOG NUMBER: LDSQA3D02R359730DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1314172

CATALOG NUMBER: LDSQA3D02R359730DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	98	98	98	96
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	96	94	94	94	94	93
3	107	102	99	96	105	101	98	95	99	96	94	96	94	92	94	92	91	94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89	93	91	88	92	89	87	92	89	87	86
5	100	94	90	87	99	93	90	87	92	88	86	90	87	85	89	86	84	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	83	88	84	82	86	84	82	86	84	82	80
7	94	88	83	80	93	87	83	80	86	82	80	85	82	79	84	81	79	84	81	79	78
8	91	85	80	77	91	84	80	77	83	80	77	82	79	77	81	79	76	81	79	76	75
9	89	82	78	75	88	81	77	75	81	77	74	80	77	74	79	76	74	79	76	74	73
10	86	79	75	72	85	79	75	72	78	75	72	78	74	72	77	74	72	77	74	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	142755	142755	142755
5°	138425	139411	140172
10°	126508	129183	131387
15°	90968	94944	95728
20°	46314	48641	48751
25°	17577	17939	17444
30°	6821	7915	6642
35°	2334	3679	2208
40°	787	1416	742
45°	49	487	49
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 487 cd/sqm



TEST NUMBER: P1314172

CATALOG NUMBER: LDSQA3D02R359730DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.0	27.2
10°-20°	139.8	50.7
20°-30°	50.3	18.2
30°-40°	9.8	3.6
40°-50°	1.1	0.4
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	265.1	96.0
0°-40°	274.9	99.6
0°-60°	276.0	100.0
0°-90°	276.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	276.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	829	829	829	829	829	
5°	801	803	806	810	811	74
15°	510	519	532	536	537	136
25°	92	93	94	94	92	48
35°	11	13	18	13	10	8
45°	0	1	2	1	0	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1314172

CATALOG NUMBER: LDSQA3D02R359730DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	828.9	828.9	828.9	828.9	828.9
1°	826.5	827.6	827.9	829.4	827.6
2°	823.0	823.7	824.6	825.9	825.0
3°	816.3	817.6	819.5	821.3	821.3
4°	809.1	810.8	813.2	816.3	816.0
5°	800.7	802.9	806.4	810.1	810.8
6°	790.3	792.9	798.6	803.8	804.7
7°	779.1	783.0	788.5	796.2	798.1
8°	766.0	769.0	776.9	785.9	788.1
9°	746.8	751.3	761.4	769.7	771.0
10°	723.4	726.6	738.7	747.4	751.3
11°	693.2	698.0	709.8	718.8	721.4
12°	654.7	661.7	675.5	682.0	684.2
13°	613.2	619.1	629.8	637.9	639.6
14°	566.4	572.1	583.2	589.8	588.3
15°	510.2	518.7	532.5	536.2	536.9
17.5°	376.9	382.3	394.6	400.5	404.6
20°	252.7	258.0	265.4	269.3	266.0
22.5°	153.7	158.1	162.0	161.8	160.7
25°	92.5	93.3	94.4	93.8	91.8
27.5°	54.0	56.4	59.7	57.5	54.2
30°	34.3	36.3	39.8	36.1	33.4
32.5°	18.1	23.0	26.7	21.6	19.0
35°	11.1	12.7	17.5	12.9	10.5
37.5°	6.8	7.9	10.9	7.7	6.1
40°	3.5	5.0	6.3	4.6	3.3
42.5°	1.1	2.4	3.5	2.2	1.1
45°	0.2	0.7	2.0	0.7	0.2
47.5°	0.0	0.0	0.9	0.2	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1314172
CATALOG NUMBER: LDSQA3D02R359730DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)