

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1314308

Luminaire Tested: LDSQA3D05R259730DE010 3LSQPHR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1314308
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R259730DE010 3LSQPHR1MB
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , 3LSQPHR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 504.0 lumens
Efficiency: N/A
Efficacy: 70.0 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1314308
CATALOG NUMBER: LDSQA3D05R259730DE010 3LSQPHR1MB

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ···· 90°-270°



TEST NUMBER: P1314308
 CATALOG NUMBER: LDSQA3D05R259730DE010 3LSQPHR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	99	99	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	97	96	96	96	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	94	94	93
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92	92	92	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	89	89	88
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	91	89	87	87	87	86
7	99	93	89	87	98	93	89	87	92	89	86	91	88	86	90	87	86	86	86	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	86	84	84	84	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	82	82	81
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	470323	470323	470323
5°	426202	430092	432184
10°	320414	322688	324174
15°	158650	153925	164177
20°	44811	45544	46039
25°	7772	14689	9216
30°	3043	3122	3222
35°	946	1030	1030
40°	292	405	292
45°	219	97	219
50°	107	0	107
55°	120	0	120
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 219 cd/sqm



TEST NUMBER: P1314308

CATALOG NUMBER: LDSQA3D05R259730DE010 3LSQPHR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.9	43.0
10°-20°	244.7	48.5
20°-30°	38.0	7.5
30°-40°	3.8	0.8
40°-50°	0.5	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	499.5	99.1
0°-40°	503.4	99.9
0°-60°	504.0	100.0
0°-90°	504.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	504.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2731	2731	2731	2731	2731	
5°	2465	2470	2488	2498	2500	215
15°	890	884	863	902	921	244
25°	41	61	77	59	48	34
35°	4	5	5	5	5	4
45°	1	0	0	0	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1314308
 CATALOG NUMBER: LDSQA3D05R259730DE010 3LSQPHR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2730.9	2730.9	2730.9	2730.9	2730.9
1°	2719.7	2723.3	2719.3	2723.7	2723.3
2°	2691.4	2695.0	2690.0	2692.7	2692.7
3°	2633.4	2641.1	2645.6	2648.7	2651.4
4°	2557.0	2565.6	2572.3	2580.4	2580.4
5°	2465.3	2469.8	2487.8	2497.7	2499.9
6°	2356.1	2374.1	2387.6	2407.4	2395.2
7°	2246.9	2261.8	2280.6	2283.8	2292.3
8°	2122.9	2138.6	2156.2	2153.0	2145.8
9°	1971.9	1994.8	2015.5	2008.8	2017.8
10°	1832.2	1846.1	1845.2	1838.4	1853.7
11°	1669.9	1673.1	1655.5	1683.0	1666.3
12°	1477.6	1480.3	1457.8	1484.8	1501.9
13°	1293.3	1287.0	1256.0	1291.5	1313.1
14°	1081.2	1083.5	1043.9	1112.7	1107.3
15°	889.8	883.5	863.3	901.9	920.8
17.5°	474.1	478.1	473.2	492.5	504.7
20°	244.5	251.2	248.5	256.6	251.2
22.5°	126.7	136.2	138.9	132.6	115.5
25°	40.9	60.7	77.3	58.9	48.5
27.5°	24.7	24.3	37.7	26.1	26.5
30°	15.3	14.8	15.7	15.7	16.2
32.5°	8.5	9.0	8.5	9.4	9.0
35°	4.5	4.9	4.9	5.4	4.9
37.5°	2.7	3.1	3.1	3.1	2.7
40°	1.3	1.8	1.8	1.3	1.3
42.5°	0.9	0.9	0.9	0.9	0.9
45°	0.9	0.4	0.4	0.4	0.9
47.5°	0.4	0.4	0.0	0.4	0.4
50°	0.4	0.4	0.0	0.4	0.4
52.5°	0.4	0.0	0.0	0.0	0.4
55°	0.4	0.0	0.0	0.0	0.4
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1314308
CATALOG NUMBER: LDSQA3D05R259730DE010 3LSQPHR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)