

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1314207

Luminaire Tested: LDSQA3D02R509730DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1314207
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R509730DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 305.0 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.78
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1314207
CATALOG NUMBER: LDSQA3D02R509730DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1314207

CATALOG NUMBER: LDSQA3D02R509730DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	64	70	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	81565	81565	81565
5°	80147	79923	79698
10°	77297	76457	76615
15°	71105	70214	70410
20°	63487	62900	63248
25°	49426	51497	48875
30°	26767	29889	26290
35°	8431	10050	8263
40°	1866	2608	1776
45°	49	804	49
50°	0	107	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 804 cd/sqm



TEST NUMBER: P1314207

CATALOG NUMBER: LDSQA3D02R509730DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.4	14.2
10°-20°	110.3	36.1
20°-30°	116.1	38.1
30°-40°	33.2	10.9
40°-50°	2.1	0.7
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	269.8	88.4
0°-40°	302.9	99.3
0°-60°	305.0	100.0
0°-90°	305.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	305.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	474	474	474	474	474	
5°	464	463	462	462	461	44
15°	399	396	394	394	395	111
25°	260	270	271	268	257	114
35°	40	43	48	41	39	31
45°	0	1	3	1	0	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1314207

CATALOG NUMBER: LDSQA3D02R509730DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	473.6	473.6	473.6	473.6	473.6
1°	473.9	474.1	473.6	474.1	473.0
2°	473.2	472.8	472.3	472.5	471.9
3°	470.8	470.6	469.7	469.9	469.1
4°	467.7	467.1	466.4	466.0	465.1
5°	463.6	463.2	462.3	461.9	461.0
6°	460.1	459.2	457.7	457.3	456.4
7°	455.5	455.1	453.1	452.7	452.3
8°	452.0	450.7	448.3	448.5	447.5
9°	447.5	445.7	443.3	443.3	443.5
10°	442.0	439.4	437.2	437.9	438.1
11°	434.8	433.1	429.8	431.3	431.3
12°	427.0	424.8	422.4	423.7	424.6
13°	417.8	416.0	413.9	415.2	414.7
14°	408.8	405.6	404.0	405.8	405.1
15°	398.8	396.2	393.8	394.4	394.9
17.5°	372.0	369.1	367.4	367.6	369.6
20°	346.4	345.4	343.2	344.0	345.1
22.5°	316.3	316.8	314.2	314.8	317.4
25°	260.1	269.7	271.0	267.9	257.2
27.5°	192.6	207.0	211.4	204.4	191.3
30°	134.6	138.5	150.3	137.0	132.2
32.5°	79.0	84.9	91.2	82.0	78.8
35°	40.1	43.0	47.8	40.6	39.3
37.5°	18.5	19.9	21.8	18.5	17.5
40°	8.3	9.8	11.6	9.4	7.9
42.5°	2.6	4.6	6.1	4.1	2.4
45°	0.2	1.1	3.3	1.1	0.2
47.5°	0.0	0.2	1.3	0.2	0.0
50°	0.0	0.0	0.4	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1314207

CATALOG NUMBER: LDSQA3D02R509730DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)