

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1314612

Luminaire Tested: LDSQA3D13R209730DE010 3LSQCA45R 1MB

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1314612  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-74)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D13R209730DE010 3LSQCA45R 1MB  
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , 3LSQCA45R 1MB TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 927.0 lumens  
Efficiency: N/A  
Efficacy: 63.5 lumens/watt  
Spacing Criteria (0/90/45): 3.39 / 0.51 / 1.13  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1314612  
CATALOG NUMBER: LDSQA3D13R209730DE010 3LSQCA45R 1MB

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P1314612

CATALOG NUMBER: LDSQA3D13R209730DE010 3LSQCA45R 1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	99	108	104	101	97	100	97	94	96	94	92	92	91	89	89	89	89	87
2	101	93	87	82	98	91	86	81	88	83	79	85	81	77	82	78	75	75	75	75	73
3	92	81	74	67	89	80	73	67	77	71	66	74	69	65	72	67	63	63	63	63	61
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	53	53	53	51
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	45	45	45	42
6	68	55	45	39	66	54	45	38	52	44	38	50	43	38	48	42	37	37	37	37	35
7	62	48	39	32	60	47	38	32	46	38	32	44	37	32	43	36	31	31	31	31	29
8	57	42	33	27	55	42	33	27	40	33	27	39	32	27	38	31	27	27	27	27	25
9	52	38	29	23	51	37	29	23	36	28	23	35	28	23	34	27	23	23	23	23	21
10	48	34	25	20	47	33	25	20	32	25	19	31	24	19	30	24	19	19	19	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	11108	11108	11108	11108	11108
5°	12949	12050	10390	9042	8730
10°	12801	10965	8219	7013	6855
15°	11179	8380	6062	5599	5902
20°	16605	7019	4472	4783	5260
25°	71507	7278	3477	4314	5131
30°	270437	8830	2943	4156	5031
35°	819808	10617	2754	4205	5319
40°	1359423	10567	2361	4496	5688
45°	1580093	7209	2119	4676	6162
50°	1226588	3965	2090	4903	6993
55°	709907	2612	2102	5495	7597
60°	120039	586	1791	5718	8404
65°	9251	0	2119	6398	9577
70°	1309	0	2618	6999	10977
75°	1131	599	2928	8118	12776
80°	893	893	4364	8629	14679
85°	1778	1778	6916	8695	15413

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1580093 cd/sqm



TEST NUMBER: P1314612

CATALOG NUMBER: LDSQA3D13R209730DE010 3LSQCA45R 1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	5.5	0.6
10°-20°	11.6	1.3
20°-30°	37.0	4.0
30°-40°	236.4	25.5
40°-50°	432.7	46.7
50°-60°	177.8	19.2
60°-70°	15.0	1.6
70°-80°	7.5	0.8
80°-90°	3.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	54.2	5.8
0°-40°	290.5	31.3
0°-60°	901.0	97.2
0°-90°	927.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	927.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	64	64	64	64	64	
5°	75	70	60	52	50	7
15°	63	47	34	31	33	20
25°	376	38	18	23	27	247
35°	3899	50	13	20	25	2468
45°	6488	30	9	19	25	4658
55°	2364	9	7	18	25	2067
65°	23	0	5	16	24	74
75°	2	1	4	12	19	2
85°	1	1	4	4	8	1
90°	0	0	0	0	0	



TEST NUMBER: P1314612  
 CATALOG NUMBER: LDSQA3D13R209730DE010 3LSQCA45R 1MB

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	45°
0°	64.5	64.5	64.5	64.5	64.5	64.5	64.5	64.5	64.5	64.5	64.5
2.5°	70.6	70.6	70.6	69.7	69.7	70.6	69.7	69.7	69.7	69.7	68.8
5°	74.9	74.9	74.9	74.9	74.9	74.9	74.9	74.0	74.0	73.2	69.7
7.5°	76.7	76.7	76.7	76.7	75.8	75.8	75.8	75.8	74.9	74.0	68.0
10°	73.2	73.2	73.2	72.3	72.3	72.3	71.4	71.4	70.6	69.7	62.7
12.5°	66.2	66.2	66.2	66.2	65.3	65.3	64.5	64.5	63.6	62.7	54.9
15°	62.7	62.7	62.7	61.9	61.9	61.0	60.1	59.2	58.4	56.6	47.0
17.5°	68.0	68.0	67.1	67.1	65.3	63.6	62.7	60.1	58.4	55.8	41.8
20°	90.6	91.5	88.0	85.4	83.6	78.4	75.8	71.4	68.0	63.6	38.3
22.5°	182.9	179.5	173.4	163.8	152.5	142.9	125.4	111.5	101.9	88.9	37.5
25°	376.3	372.9	356.3	342.4	307.5	280.5	243.1	212.6	181.2	150.7	38.3
27.5°	715.2	691.7	687.3	623.8	575.0	505.3	433.0	372.0	316.2	254.4	40.9
30°	1359.9	1332.9	1237.9	1142.1	1010.5	861.6	719.6	587.2	476.5	376.3	44.4
31°	1725.8	1751.9	1640.4	1447.9	1253.6	1062.8	868.5	700.4	557.5	433.0	46.2
32°	2268.5	2154.4	2036.8	1839.0	1556.8	1312.8	1068.9	826.7	638.6	493.9	47.9
33°	2781.6	2714.5	2535.1	2288.5	1949.7	1607.3	1291.1	975.7	737.9	568.0	48.8
34°	3328.7	3254.7	3109.2	2755.5	2383.5	1934.9	1513.2	1147.3	856.4	640.3	49.7
35°	3899.3	3868.0	3587.4	3280.8	2823.4	2282.4	1780.7	1335.5	972.2	706.5	50.5
36°	4473.4	4372.4	4152.8	3705.1	3227.7	2603.9	2061.2	1510.6	1089.8	784.9	50.5
37°	4905.5	4882.9	4591.9	4155.4	3594.4	2947.1	2303.4	1704.9	1208.3	852.0	50.5
38°	5382.0	5292.3	4997.0	4552.7	3939.4	3261.6	2556.9	1873.9	1320.7	913.0	49.7
39°	5783.6	5650.4	5352.4	4913.4	4240.8	3500.3	2758.1	2037.6	1420.0	963.5	48.8
40°	6046.7	5954.4	5643.4	5149.4	4514.4	3726.0	2962.0	2172.7	1494.0	1001.8	47.0
41°	6336.8	6183.5	5876.0	5379.4	4713.0	3924.6	3090.0	2261.5	1551.5	1027.1	45.3
42°	6510.2	6384.7	6019.7	5533.6	4855.0	4037.8	3194.6	2329.5	1586.4	1040.2	41.8
43°	6672.2	6501.5	6146.1	5623.4	4949.1	4118.0	3242.5	2360.9	1594.2	1040.2	37.5
44°	6650.5	6488.4	6119.9	5635.5	4970.0	4141.5	3262.5	2361.7	1582.0	1027.1	33.1
45°	6487.5	6326.4	5994.5	5529.3	4895.1	4095.3	3222.4	2326.9	1548.1	1004.5	29.6
46°	6188.7	6028.4	5774.1	5351.6	4755.7	3990.8	3129.2	2251.1	1491.4	967.9	26.1
47°	5863.8	5707.9	5447.4	5064.9	4517.8	3804.4	2994.2	2144.8	1412.2	914.7	23.5
48°	5392.5	5294.9	5033.6	4706.9	4187.7	3512.5	2757.2	1971.4	1305.9	845.9	20.0
49°	4976.1	4873.3	4644.2	4293.1	3757.3	3172.8	2474.1	1760.6	1167.4	769.2	17.4
50°	4578.0	4488.2	4276.5	3880.2	3368.8	2762.5	2091.7	1494.9	993.1	674.3	14.8
51°	4188.5	4121.5	3905.4	3541.3	3022.1	2447.1	1812.0	1244.9	820.6	559.3	13.9
52°	3797.4	3789.6	3555.2	3186.7	2684.9	2132.6	1540.2	1050.6	696.1	469.6	13.1
53°	3376.6	3326.1	3121.4	2790.3	2308.6	1805.0	1305.9	886.0	599.4	399.9	11.3
54°	2897.5	2840.9	2621.3	2322.5	1886.1	1478.4	1052.4	716.1	499.2	338.0	10.5
55°	2364.3	2267.6	2108.2	1801.6	1473.1	1128.2	812.8	567.1	399.0	281.4	8.7
56°	1793.7	1697.0	1607.3	1381.7	1081.1	841.5	605.5	434.7	311.9	222.1	7.8
57°	1247.5	1242.3	1095.1	921.7	723.1	573.2	414.7	306.6	220.4	172.5	6.1
58°	809.3	782.3	688.2	588.0	473.0	358.0	266.6	208.2	149.8	117.6	5.2
59°	567.1	513.1	462.6	392.0	297.9	225.6	171.6	133.3	103.7	81.9	3.5
60°	348.5	337.1	303.2	238.7	193.4	159.4	128.1	98.4	75.8	58.4	1.7
62.5°	99.3	101.1	91.5	81.0	69.7	60.1	54.0	46.2	38.3	30.5	0.0
65°	22.7	21.8	23.5	21.8	20.0	20.0	17.4	15.7	13.9	13.1	0.0



TEST NUMBER: P1314612

CATALOG NUMBER: LDSQA3D13R209730DE010 3LSQCA45R 1MB

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	45°
67.5°	7.0	7.0	6.1	6.1	6.1	5.2	5.2	4.4	4.4	3.5	0.0
70°	2.6	2.6	2.6	2.6	2.6	1.7	1.7	1.7	0.9	0.9	0.0
72.5°	2.6	2.6	2.6	1.7	1.7	1.7	1.7	1.7	0.9	0.9	0.9
75°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	0.9	0.9	0.9	0.9
77.5°	1.7	1.7	1.7	1.7	1.7	0.9	1.7	0.9	0.9	0.9	0.9
80°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
82.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
85°	0.9	0.9	0.9	0.9	0.0	0.0	0.9	0.9	0.9	0.0	0.9
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1314612

CATALOG NUMBER: LDSQA3D13R209730DE010 3LSQCA45R 1MB

**CANDELA DISTRIBUTION (continued):**

	67.5°	90°	112.5°	135°	157.5°	180°
0°	64.5	64.5	64.5	64.5	64.5	64.5
2.5°	67.1	63.6	61.0	58.4	57.5	57.5
5°	65.3	60.1	54.9	52.3	50.5	50.5
7.5°	60.1	54.0	48.8	46.2	45.3	45.3
10°	54.0	47.0	41.8	40.1	40.1	39.2
12.5°	47.0	40.1	36.6	35.7	35.7	35.7
15°	39.2	34.0	31.4	31.4	32.2	33.1
17.5°	33.1	27.9	27.0	28.7	30.5	30.5
20°	27.9	24.4	24.4	26.1	27.9	28.7
22.5°	23.5	20.9	21.8	24.4	27.0	27.9
25°	20.9	18.3	20.0	22.7	25.3	27.0
27.5°	17.4	16.6	18.3	21.8	25.3	26.1
30°	14.8	14.8	17.4	20.9	24.4	25.3
31°	13.9	13.9	17.4	20.9	24.4	25.3
32°	13.1	13.9	16.6	20.9	24.4	25.3
33°	12.2	13.1	16.6	20.0	24.4	25.3
34°	11.3	13.1	16.6	20.0	24.4	25.3
35°	10.5	13.1	16.6	20.0	24.4	25.3
36°	9.6	12.2	15.7	20.0	24.4	25.3
37°	8.7	12.2	15.7	20.0	24.4	25.3
38°	7.8	11.3	15.7	20.0	24.4	25.3
39°	7.8	11.3	14.8	20.0	23.5	25.3
40°	7.0	10.5	14.8	20.0	23.5	25.3
41°	6.1	10.5	14.8	19.2	23.5	25.3
42°	5.2	9.6	13.9	19.2	23.5	25.3
43°	4.4	9.6	13.9	19.2	23.5	25.3
44°	4.4	8.7	13.9	19.2	23.5	25.3
45°	3.5	8.7	13.9	19.2	23.5	25.3
46°	2.6	8.7	13.9	19.2	23.5	25.3
47°	2.6	7.8	13.1	19.2	23.5	25.3
48°	1.7	7.8	13.1	19.2	23.5	25.3
49°	1.7	7.8	13.1	19.2	23.5	26.1
50°	1.7	7.8	13.1	18.3	23.5	26.1
51°	0.9	7.8	13.1	18.3	23.5	26.1
52°	0.9	7.8	12.2	18.3	24.4	26.1
53°	0.9	7.0	12.2	18.3	24.4	26.1
54°	0.9	7.0	12.2	18.3	24.4	25.3
55°	0.9	7.0	12.2	18.3	23.5	25.3
56°	0.9	6.1	12.2	18.3	23.5	25.3
57°	0.9	6.1	11.3	17.4	23.5	24.4
58°	0.9	6.1	11.3	17.4	23.5	24.4
59°	0.9	6.1	11.3	17.4	22.7	24.4
60°	1.7	5.2	10.5	16.6	22.7	24.4
62.5°	1.7	5.2	10.5	16.6	21.8	23.5
65°	1.7	5.2	9.6	15.7	21.8	23.5



TEST NUMBER: P1314612

CATALOG NUMBER: LDSQA3D13R209730DE010 3LSQCA45R 1MB

**CANDELA DISTRIBUTION (continued):**

	67.5°	90°	112.5°	135°	157.5°	180°
67.5°	1.7	4.4	8.7	14.8	20.9	22.7
70°	1.7	5.2	8.7	13.9	20.0	21.8
72.5°	2.6	4.4	7.8	13.1	19.2	20.9
75°	2.6	4.4	7.8	12.2	18.3	19.2
77.5°	3.5	4.4	7.0	10.5	16.6	17.4
80°	3.5	4.4	6.1	8.7	13.9	14.8
82.5°	3.5	4.4	4.4	7.0	10.5	11.3
85°	2.6	3.5	3.5	4.4	7.0	7.8
87.5°	2.6	3.5	2.6	1.7	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)