

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1314465

Luminaire Tested: LDSQA3D09R259730DE010 3LSQPHR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1314465
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D09R259730DE010 3LSQPHR1MB
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , 3LSQPHR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 736.0 lumens
Efficiency: N/A
Efficacy: 66.3 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1314465
CATALOG NUMBER: LDSQA3D09R259730DE010 3LSQPHR1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1314465

CATALOG NUMBER: LDSQA3D09R259730DE010 3LSQPHR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	99	99	99	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	97	96	96	96	96	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	94	94	94	93
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92	92	92	92	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	89	89	89	88
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	91	89	87	87	87	87	86
7	99	93	89	87	98	93	89	87	92	89	86	91	88	86	90	87	86	86	86	86	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	85	84	84	84	84	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	82	82	82	81
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	686824	686824	686824
5°	622404	628075	631135
10°	467890	471230	473399
15°	231680	224780	239757
20°	65429	66511	67225
25°	11345	21454	13473
30°	4435	4574	4693
35°	1388	1514	1514
40°	450	585	450
45°	317	170	317
50°	188	0	188
55°	210	0	210
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 317 cd/sqm



TEST NUMBER: P1314465

CATALOG NUMBER: LDSQA3D09R259730DE010 3LSQPHR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	316.8	43.0
10°-20°	357.3	48.5
20°-30°	55.4	7.5
30°-40°	5.6	0.8
40°-50°	0.8	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	729.5	99.1
0°-40°	735.1	99.9
0°-60°	736.0	100.0
0°-90°	736.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	736.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3988	3988	3988	3988	3988	
5°	3600	3607	3633	3647	3651	314
15°	1299	1290	1261	1317	1345	356
25°	60	89	113	86	71	50
35°	7	7	7	8	7	5
45°	1	1	1	1	1	1
55°	1	0	0	0	1	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1314465
 CATALOG NUMBER: LDSQA3D09R259730DE010 3LSQPHR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3988.0	3988.0	3988.0	3988.0	3988.0
1°	3971.6	3976.9	3971.0	3977.5	3976.9
2°	3930.3	3935.5	3928.3	3932.3	3932.3
3°	3845.6	3856.8	3863.3	3867.9	3871.9
4°	3734.1	3746.5	3756.4	3768.2	3768.2
5°	3600.2	3606.8	3633.0	3647.4	3650.7
6°	3440.7	3467.0	3486.7	3515.5	3497.8
7°	3281.3	3302.9	3330.5	3335.1	3347.5
8°	3100.1	3123.1	3148.7	3144.1	3133.6
9°	2879.6	2913.1	2943.3	2933.4	2946.6
10°	2675.5	2695.9	2694.6	2684.7	2707.0
11°	2438.6	2443.2	2417.6	2457.7	2433.4
12°	2157.8	2161.7	2128.9	2168.3	2193.2
13°	1888.7	1879.5	1834.2	1886.1	1917.6
14°	1578.9	1582.2	1524.5	1624.9	1617.0
15°	1299.4	1290.2	1260.7	1317.1	1344.7
17.5°	692.3	698.3	691.0	719.3	737.0
20°	357.0	366.8	362.9	374.7	366.8
22.5°	185.1	198.8	202.8	193.6	168.7
25°	59.7	88.6	112.9	86.0	70.9
27.5°	36.1	35.4	55.1	38.1	38.7
30°	22.3	21.7	23.0	23.0	23.6
32.5°	12.5	13.1	12.5	13.8	13.1
35°	6.6	7.2	7.2	7.9	7.2
37.5°	3.9	4.6	4.6	4.6	3.9
40°	2.0	2.6	2.6	2.0	2.0
42.5°	1.3	1.3	1.3	1.3	1.3
45°	1.3	0.7	0.7	0.7	1.3
47.5°	0.7	0.7	0.0	0.7	0.7
50°	0.7	0.7	0.0	0.7	0.7
52.5°	0.7	0.0	0.0	0.0	0.7
55°	0.7	0.0	0.0	0.0	0.7
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1314465
CATALOG NUMBER: LDSQA3D09R259730DE010 3LSQPHR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)