

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1314815

Luminaire Tested: LDSQA3D17R359730DE010 3LSQPHR1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1314815
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D17R359730DE010 3LSQPHR1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , 3LSQPHR1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1340.0 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1314815
CATALOG NUMBER: LDSQA3D17R359730DE010 3LSQPHR1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1314815

CATALOG NUMBER: LDSQA3D17R359730DE010 3LSQPHR1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93	92	91
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90	89	87
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87	85	82
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85	83	80
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82	80	77
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80	78	75
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77	75	73
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	75	73	71
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	73	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	760329	760329	760329
5°	747276	745685	744078
10°	684863	664280	648138
15°	490409	474772	468995
20°	227408	235234	243482
25°	53949	76771	80058
30°	15830	18137	20423
35°	3637	5824	5340
40°	787	1551	1034
45°	292	292	292
50°	322	0	322
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 339 cd/sqm



TEST NUMBER: P1314815

CATALOG NUMBER: LDSQA3D17R359730DE010 3LSQPHR1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	396.4	29.6
10°-20°	708.6	52.9
20°-30°	213.2	15.9
30°-40°	20.4	1.5
40°-50°	1.4	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1318.1	98.4
0°-40°	1338.5	99.9
0°-60°	1340.0	100.0
0°-90°	1340.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1340.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4415	4415	4415	4415	4415	
5°	4322	4321	4313	4308	4304	401
15°	2750	2730	2663	2651	2630	726
25°	284	313	404	421	421	183
35°	17	23	28	30	25	16
45°	1	1	1	1	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1314815
 CATALOG NUMBER: LDSQA3D17R359730DE010 3LSQPHR1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4414.8	4414.8	4414.8	4414.8	4414.8
1°	4412.5	4412.5	4410.2	4410.2	4405.6
2°	4402.1	4403.3	4398.7	4397.5	4394.1
3°	4386.0	4382.5	4382.5	4380.2	4377.9
4°	4360.6	4353.7	4351.4	4352.5	4347.9
5°	4322.5	4321.3	4313.3	4307.5	4304.0
6°	4280.9	4272.9	4255.6	4240.6	4237.1
7°	4218.6	4201.3	4186.3	4155.1	4150.5
8°	4142.4	4114.7	4082.4	4038.6	4036.3
9°	4049.0	4003.9	3958.9	3900.1	3879.3
10°	3916.2	3874.7	3798.5	3746.6	3706.2
11°	3751.2	3699.2	3610.4	3548.0	3514.6
12°	3564.2	3515.7	3411.8	3355.3	3308.0
13°	3324.1	3283.7	3186.8	3124.4	3087.5
14°	3045.9	3015.9	2923.6	2895.9	2883.2
15°	2750.5	2729.7	2662.8	2651.2	2630.4
17.5°	2024.5	1989.9	1951.8	1958.7	1965.6
20°	1240.8	1289.2	1283.5	1308.9	1328.5
22.5°	618.7	681.0	753.7	797.6	819.5
25°	283.9	312.8	404.0	421.3	421.3
27.5°	143.1	150.0	190.4	193.9	203.1
30°	79.6	85.4	91.2	101.6	102.7
32.5°	40.4	47.3	49.6	55.4	53.1
35°	17.3	23.1	27.7	30.0	25.4
37.5°	8.1	10.4	15.0	13.9	10.4
40°	3.5	4.6	6.9	5.8	4.6
42.5°	2.3	2.3	3.5	2.3	2.3
45°	1.2	1.2	1.2	1.2	1.2
47.5°	1.2	1.2	0.0	1.2	1.2
50°	1.2	0.0	0.0	0.0	1.2
52.5°	1.2	0.0	0.0	0.0	1.2
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1314815
CATALOG NUMBER: LDSQA3D17R359730DE010 3LSQPHR1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)